



Metal Film Resistors, Axial, Non-Magnetic, Industrial, Precision



FEATURES

- Small size - conformal coated
- Flame retardant epoxy coating
- Controlled temperature coefficient
- Excellent high frequency characteristics
- Exceptionally low noise; typically 0.10 μV/V
- Low voltage coefficient to ± 5 ppm/V
- Utilizes non-magnetic brass or nickel silver end caps (as appropriate for value and tolerance)
- Tested using magnets to ensure parts are non-magnetic
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



Note

\* This datasheet provides information about parts that are RoHS-compliant and /or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS							
GLOBAL MODEL	HISTORICAL MODEL	MAXIMUM WORKING VOLTAGE (1) V	POWER RATING P <sub>70 °C</sub> (2) W	POWER RATING P <sub>125 °C</sub> (2) W	RESISTANCE RANGE Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
CMF50..143	CMF-50-143	200	0.25	0.125	10 to 2.5M	0.1, 0.25, 0.5, 1	25
					10 to 2.5M	0.1, 0.25, 0.5, 1, 2, 5	50
					10 to 2.5M	1, 2, 5	100
					10 to 22M	1, 2, 5	150, 200
CMF55..143	CMF-55-143	250	0.5	0.25	10 to 2.5M	0.1, 0.25, 0.5, 1	25
					10 to 2.5M	0.1, 0.25, 0.5	50
					10 to 5M	1, 2, 5	50
					1 to 22.1M	1, 2, 5	100
					0.5 to 50M	1, 2, 5	150
					0.5 to 50M	1	200
CMF60..143	CMF-60-143	500	1	0.5	10 to 2.5M	0.1, 0.25, 0.5, 1	25
					10 to 2.5M	0.1, 0.25, 0.5	50
					10 to 10M	1, 2, 5	50
					1 to 10M	1, 2, 5	100
					0.5 to 10M	1, 2, 5	150
					0.5 to 10M	1	200
					0.1 to 10M	2, 5	200
CMF65..143	CMF-65-143	500	1.5	1	10 to 2.5M	0.1, 0.25, 0.5, 1	25
					10 to 2.5M	0.1, 0.25, 0.5	50
					10 to 10M	1, 2, 5	50
					1 to 15M	1, 2, 5	100
					0.5 to 22M	1, 2, 5	150
					0.5 to 22M	1	200
					0.1 to 22M	2, 5	200
CMF70..143	CMF-70-143	500	1.75	1.25	10 to 2.5M	0.1, 0.25, 0.5, 1	25
					10 to 2.5M	0.1, 0.25, 0.5	50
					10 to 10M	1, 2, 5	50
					1 to 15M	1, 2, 5	100
					1 to 22M	1, 2, 5	150, 200
CMF07..143	CMF-07-143	250	0.5	-	5 to 5M	2, 5	100
					1 to 5M	2, 5	150, 200
CMF20..143	CMF-20-143	500	1	-	5 to 10M	2, 5	100
					1 to 10M	2, 5	150, 200


Notes

- (1) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less
- (2) See the load life shift due to power and derating table for a summary of the more common combinations of power rating, case size and ambient operating temperature that prevail in various industrial and military resistor specifications. The "performance" table quantifies the load life stability under these combinations.

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: <b>CMF5510K000FKRE143</b> (preferred part numbering format)																	
<b>C</b>	<b>M</b>	<b>F</b>	<b>5</b>	<b>5</b>	<b>1</b>	<b>0</b>	<b>K</b>	<b>0</b>	<b>0</b>	<b>0</b>	<b>F</b>	<b>K</b>	<b>R</b>	<b>E</b>	<b>1</b>	<b>4</b>	<b>3</b>
GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMPERATURE COEFFICIENT (1)	PACKAGING				SPECIAL									
(See Standard Electrical Specifications table)	<b>R</b> = Ω <b>K</b> = kΩ <b>M</b> = MΩ <b>R10000</b> = 0.1 Ω <b>680K00</b> = 680 kΩ <b>1M0000</b> = 1.0 MΩ	<b>B</b> = ± 0.1 % <b>C</b> = ± 0.25 % <b>D</b> = ± 0.5 % <b>F</b> = ± 1 % <b>G</b> = ± 2 % <b>J</b> = ± 5 %	<b>E</b> = 25 ppm <b>H</b> = 50 ppm <b>K</b> = 100 ppm <b>L</b> = 150 ppm <b>N</b> = 200 ppm	<b>EK</b> = lead (Pb)-free, bulk <b>EA</b> = lead (Pb)-free, T/R (full) <b>EB</b> = lead (Pb)-free, T/R (1000 pieces)  <b>BF</b> = tin/lead, bulk <b>RE</b> = tin/lead, T/R (full) <b>R6</b> = tin/lead, T/R (1000 pieces)				<b>143</b> = non-magnetic									
Historical Part Number Example: <b>CMF-55-1431002FT-1</b> (will continue to be accepted)																	
<b>CMF-55-143</b>		<b>1002</b>		<b>F</b>		<b>T-1</b>		<b>R36</b>									
HISTORICAL MODEL		RESISTANCE VALUE		TOLERANCE CODE		TEMP. COEFFICIENT		PACKAGING									

**Notes**

- For additional information on packaging, refer to the Through-Hole Resistor Packaging document ([www.vishay.com/doc?31544](http://www.vishay.com/doc?31544)).
- (1) Tolerance of ± 0.5 % (D), ± 0.25 % (C), and ± 0.1 % (B) are available only in 50 ppm and 25 ppm temperature coefficients.

**DIMENSIONS** in inches (millimeters)


GLOBAL MODEL	A	B	C (Max.)	D
CMF07..143	0.240 ± 0.020 (6.10 ± 0.51)	0.090 ± 0.008 (2.29 ± 0.20)	0.290 (7.37)	0.025 ± 0.002 (0.64 ± 0.05)
CMF20..143	0.375 ± 0.040 (9.53 ± 1.02)	0.145 ± 0.015 (3.68 ± 0.38)	0.425 (10.80)	0.032 ± 0.002 (0.81 ± 0.05)
CMF50..143	0.150 ± 0.020 (3.81 ± 0.51)	0.065 ± 0.015 (1.65 ± 0.38)	0.187 (4.75)	0.016 ± 0.002 (0.41 ± 0.05)
CMF55..143	0.240 ± 0.020 (2) (6.10 ± 0.51)	0.090 ± 0.008 (2.29 ± 0.20)	0.290 (7.37)	0.025 ± 0.002 (0.64 ± 0.05)
CMF60..143	0.344 ± 0.031 (8.74 ± 0.79)	0.145 ± 0.015 (3.68 ± 0.38)	0.425 (10.80)	0.025 ± 0.002 (0.64 ± 0.05)
CMF65..143	0.562 ± 0.031 (14.27 ± 0.79)	0.180 ± 0.015 (4.57 ± 0.38)	0.687 (17.45)	0.025 ± 0.002 (0.64 ± 0.05)
CMF70..143	0.562 ± 0.031 (14.27 ± 0.79)	0.180 ± 0.015 (4.57 ± 0.38)	0.687 (17.45)	0.032 ± 0.002 (0.81 ± 0.05)

**Notes**

- (1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim.
- (2) 0.260" ± 0.020" (6.60 mm ± 0.51 mm) for values > 5 MΩ

TECHNICAL SPECIFICATIONS								
PARAMETER	UNIT	CMF07..143	CMF20..143	CMF50..143	CMF55..143	CMF60..143	CMF65..143	CMF70..143
Maximum Working Voltage	V <sub>≅</sub>	≤ 250	≤ 500	≤ 200	≤ 250	≤ 500	≤ 500	≤ 500
Insulation Voltage (1 Min)	V <sub>eff</sub>	> 500						
Voltage Coefficient (Max.)	ppm/V	± 5 (measured between 10 % and full rated voltage)						
Dielectric Strength	V <sub>AC</sub>	450	750	450	450	750	900	900
Insulation Resistance	Ω	≥ 10 <sup>11</sup>						
Operating Temp. Range	°C	-55 to +175						
Terminal Strength (Pull Test)	lb	5	5	2	2	2	2	5
Noise	dB	0.10 μV/V over a decade of frequency, with low and intermediate resistance values typically below 0.05 μV/V						
Weight (Max.)	g	0.28	0.60	0.12	0.28	0.50	1.00	1.10





TEMPERATURE COEFFICIENT CODES		
GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
E	T-9	25 ppm/°C
H	T-2	50 ppm/°C
K	T-1	100 ppm/°C
L	T-0	150 ppm/°C
N	T-00	200 ppm/°C

**LOAD LIFE SHIFT DUE TO POWER AND DERATING (AT +70 °C AND AT +125 °C)**

The power rating for the CMF parts is tied to the derating temperature, the heat rise of the parts, and the ΔR for the load life performance. When the tables/graphs below are used together they show that when the parts are run at their higher power ratings, the parts will run hotter, which has the potential of causing the resistance of the parts to shift more over the life of the part.

LOAD LIFE SHIFT VS. POWER RATING						
LOAD LIFE	MAXIMUM ΔR (TYPICAL TEST LOTS)					
	± 0.15 %	± 0.5 %	± 1.0 %	± 0.15 %	± 0.5 %	± 1.0 %
MODEL	POWER RATING AT +70 °C			POWER RATING AT +125 °C		
CMF50..143	1/20 W and 1/10 W	1/8 W	1/4 W	1/20 W	1/10 W	1/8 W
CMF55..143, CMF07..143	1/10 W and 1/8 W	1/4 W	1/2 W	1/10 W	1/8 W	1/4 W
CMF60..143, CMF20..143	1/8 W and 1/4 W	1/2 W	3/4 W and 1 W	1/8 W	1/4 W	1/2 W
CMF65..143	1/4 W and 1/2 W	3/4 W	1 W and 1-1/2 W	1/4 W	1/2 W	3/4 W and 1 W
CMF70..143	1/4 W and 1/2 W	3/4 W	1 W and 1-3/4 W	1/4 W	1/2 W	3/4 W and 1-1/4 W

CMF resistors have an operating temperature range of -55 °C to +175 °C. They must be derated at high ambient temperatures according to the derating curve.



**Example:**

When a CMF55..143 part is run at 1/8 W in a 70 °C ambient environment, the resistor will generate enough heat that the surface temperature of the part will reach about 19 °C over the ambient temperature, and over the life of the part this could cause the resistance value to shift up to ± 0.15 %.

If the same resistor was instead run at 1/4 W in a 70 °C environment, the element will heat up to about 30 °C over ambient, and over the life of the part the resistance value could shift roughly ± 0.5 %.

And if the resistor was run at its maximum power rating of 1/2 W in a 70 °C environment, it will heat up to about 58 °C over ambient, and you could see the resistance value shift roughly ± 1 % over the life of the part.

**MATERIAL SPECIFICATIONS**

<b>Element</b>	Vacuum-deposited nickel-chrome alloy	<b>Coating</b>	Flame retardant epoxy, formulated for superior moisture protection
<b>Core</b>	Fire-cleaned high purity ceramic	<b>Solderability</b>	Continuous satisfactory coverage when tested in accordance with MIL-R-10509



MARKING
<ul style="list-style-type: none"> <li>- Model</li> <li>- Value</li> <li>- Decade and tolerance</li> <li>- Date code</li> </ul>

PERFORMANCE		
TEST (TEST METHODS - MIL-STD-202)	AT +70 °C	AT +125 °C
	MAXIMUM ΔR (TYPICAL TEST LOTS)	
Short Time Overload	± 0.05 %	± 0.05 %
Low Temperature Operation	± 0.05 %	± 0.05 %
Moisture Resistance	± 0.05 %	± 0.05 %
Shock	± 0.01 %	± 0.01 %
Vibration	± 0.04 %	± 0.04 %
Temperature Cycling	± 0.15 %	± 0.15 %
Load Life	Varies based on power rating used; see load life shift due to power and derating table	
Dielectric Withstanding Voltage	± 0.01 %	± 0.01 %
Effect of Solder	± 0.03 %	± 0.03 %



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.