




Wirewound/Metal Film Resistors, Commercial Power, Vertical Mount



Please reference the Vishay Dale closest equivalent:

- CPCL, CPCC, CPCP, CPCF
(www.vishay.com/doc?30218)
- CPCC, CPCF High Volume
(www.vishay.com/doc?30116)

Notes

- There may be slight differences between the PCRC, PCRL, PCRM product and the applicable replacement.
- See the cross-reference file for a complete list of differences and part number crosses:
www.vishay.net/files/Cross-Reference%20Data%20-%20PTN-DR-022-2015%20Rev%200.pdf.

FEATURES

- Board space saving due to vertical design
- Meets or exceeds requirements of EIA standard RS-344
- High power to size ratio
- Special inorganic potting compound and ceramic case provide high thermal conductivity in a fireproof package
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING $P_{70^{\circ}\text{C}}$ W	TOLERANCE $\pm \%$	RESISTANCE RANGE Ω	WEIGHT (typical) g
PCRC05	PCRC-5	5	5, 10	0.1 to 800	6.9
PCRL05	PCRL-5	5	1, 5	0.01 to 0.1	6.9
PCRM05	PCRM-5	5	1, 5, 10	801 to 51K	6.9
PCRC07	PCRC-7	7	5, 10	0.1 to 50K	9.2
PCRC10	PCRC-10	10	5, 10	0.1 to 8K	14.3

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	PCRC	PCRL	PCRM
Temperature Coefficient	ppm/ $^{\circ}\text{C}$	$\pm 300 = 1.0 \Omega$ and above, $\pm 600 = 0.1 \Omega$ to 0.99Ω , ± 400 for PCRC07	$\pm 100 = 0.05 \Omega$ to 0.10Ω , $\pm 400 = 0.01 \Omega$ to 0.049Ω	± 50 all values
Short Time Overload	-	5 x rated power for 5 s		
Maximum Working Voltage	V	$(P \times R)^{1/2}$		
Operating Temperature Range	$^{\circ}\text{C}$	-65 to +275		-65 to +225
Terminal Strength	lb	10 minimum		
Dielectric Withstanding Voltage	V_{AC}	1000		

GLOBAL PART NUMBER INFORMATION

Global Part Numbering example: PCRC10500R0JE32 (Visit www.vishay.net SAP Parts Manual for all options)

P	C	R	C	1	0	5	0	0	R	0	J	E	3	2		
GLOBAL MODEL (6 digits)				VALUE (5 digits)			TOLERANCE (1 digit)		PACKAGING CODE (3 digits)				SPECIAL (up to 2 digits)			
PCRC05 PCRL05 PCRM05 PCRC07 PCRC10				R = Decimal K = Thousand 15R00 = 15 Ω 1K500 = 1.5 k Ω			F = $\pm 1 \%$ J = $\pm 5 \%$ K = $\pm 10 \%$		E01 = Lead (Pb)-free skin pack E32 = Lead (Pb)-free two layer bulk pack E66 = Lead (Pb)-free bulk (PCRC07 only)				(Dash Number) From 1 to 99 as applicable			

Historical Part Number example: PCRC-10-500-5 %

PCRC-10	500 Ω	5 %
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE



DIMENSIONS in inches [millimeters]



GLOBAL MODEL	DIMENSIONS in inches [millimeters]				
	H ± 0.031 [0.794]	L ± 0.031 [0.794]	W + 0.043 [1.09] - 0.012 [0.305]	LD ± 0.005 [0.127]	CC ± 0.040 [1.02]
PCRC05, PCRL05, PCRM05	1.003 [25.48]	0.512 [13.00]	0.354 [8.99]	0.032 [0.813]	0.197 [5.00]
PCRC07	1.535 ± 0.059 [39.00 ± 1.50]	0.512 ± 0.043 [13.00 ± 1.10]	0.354 ± 0.043 [9.00 ± 1.10]	0.032 ± 0.005 [0.813 ± 0.0127]	0.197 + 0.079/- 0.039 [5.00 + 2.0/- 1.0]
PCRC10	1.372 [34.85]	0.633 [16.08]	0.485 [12.32]	0.036 [0.914]	0.290 [7.37]

MATERIAL SPECIFICATIONS

Part Marking: HEI, model, wattage, value, tolerance, date code

PCRC

Element: copper-nickel alloy or nickel-chrome alloy, depending on resistance value

Core: woven fiberglass (PCRC07 is alumina ceramic)

Body: steatite ceramic case with inorganic potting compound

End Caps: tin plated steel

Terminals: tinned copper

PCRL

Element: self supporting copper-nickel alloy or nickel-chrome alloy, depending on resistance value

Body: steatite ceramic case with inorganic potting compound

Terminals: tinned copper

PCRM

Element: metal film - nickel-chrome alloy


Core: alumina ceramic

Body: steatite ceramic case with inorganic potting compound

End Caps: brass alloy

Terminals: solder-coated copper

DERATING



Note

- PCRC07 deratings begin at 40 °C in lieu of 70 °C.

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal Shock	-55 °C to +275 °C (+225 °C for PCRM)	± (5.0 % + 0.05 Ω) ΔR
Short Time Overload	5 x rated power for 5 s	± (4.0 % + 0.05 Ω) ΔR
Dielectric Withstanding Voltage	1000 V _{RMS} for 1 min	± (2.0 % + 0.05 Ω) ΔR
Low Temperature Storage	-65 °C, full rated working voltage for 45 min	± (3.0 % + 0.05 Ω) ΔR
Bias Humidity	75 °C, 90 % to 100 % RH, 240 h	± (5.0 % + 0.05 Ω) ΔR
Load Life	1000 h at rated power, + 40 °C, 1.5 h "ON", 0.5 h "OFF"	± (5.0 % + 0.05 Ω) ΔR
Terminal Strength	5 s to 10 s 10 pound pull test	± (1.0 % + 0.05 Ω) ΔR
Resistance to Solder Heat	Terminal immersed 3.5 s in molten solder up to body	± (4.0 % + 0.05 Ω) ΔR



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.