

Wirewound Resistors, Noise Suppressor, High Performance



FEATURES

- Coating increases body strength and improves high voltage performance up to 45 kV
- Ideal for reducing RFI during electrical discharges on gasoline engines
- Variety of resistance and inductance values available
- Capability to withstand high voltage pulses at high frequency
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

STANDARD ELECTRICAL SPECIFICATIONS		
MODEL	RESISTANCE RANGE ⁽¹⁾ Ω	TOLERANCE ⁽²⁾ ± %
NSRHP	1K to 15K	10, 20

Notes

- ⁽¹⁾ Special resistance values available upon request
- ⁽²⁾ Other tolerances available upon request

TECHNOLOGY

The resistor element is a resistive wire, which is wound in a single layer on a fiberglass core. Metallic caps are fixed to the ends of the resistive core. A coating protects the resistive element against moisture and mechanical shock, plus is able to withstand high temperatures. These products can be molded with epoxy resin, thermoplastic or thermo set materials. The resistors can be used in the spark plug leads, as well as in the spark plug caps itself.



Notes

- The image shows the resistor half coated and half un-coated
- The end caps are crimped onto the body of the resistor

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	NSRHP RESISTOR CHARACTERISTICS
Inductance Range, 2 MHz ⁽¹⁾	μH	9 to 78
Temperature Coefficient	ppm/°C	± 250
Operating Temperature Range	°C	-40 to +200
Dielectric Withstanding Voltage	V _{AC}	1000


Note

- ⁽¹⁾ Special inductance values available upon request

GLOBAL PART NUMBER INFORMATION																	
Part Number Example: NSRHP41051K25M19CE								Part Number Description: NSRHP-4105 1.25K 20% 19μH C E51									
N	S	R	H	P	4	1	0	5	1	K	2	5	M	1	9	C	E
MODEL (5 digits)		TYPE ⁽¹⁾ (4 digits)		RESISTANCE VALUE (4 digits)		TOLERANCE (1 digit)		INDUCTANCE VALUE ⁽¹⁾ (2 digits)		CONSTRUCTION TYPE (1 digit)		PACKAGE CODE (1 digit)					
NSRHP		Example: 4xxx 5xxx 6xxx 7xxx		1K25 = 1250 Ω 500R = 500 Ω		K = ± 10 % M = ± 20 %		19 = 19 μH 05 = 5 μH		C = crimped cap		E = standard bulk V = vacuum pack					

Note

- ⁽¹⁾ The “xxx” part numbers and inductance values will be assigned by Vishay Dale engineering after design / drawing review approval

ELECTRICAL AND DIMENSIONAL DATA							
							
NSRHP TYPE ⁽¹⁾	DIMENSIONS in millimeters (inches)				RESISTANCE RANGE ⁽²⁾	INDUCTANCE RANGE ⁽³⁾ (2 MHz, 1 V)	ESTIMATED POWER RATING ^{(4) (5)} $P_{40\text{ }^\circ\text{C}}$ W / 25.4 mm
	A Typ.	B Typ.	C Max.	L Typ.			
4xxx	3.15 (0.124)	1.80 (0.071)	3.45 (0.136)	11.00 to 30.00 (0.433 to 1.181)	1 k Ω to 15 k Ω	9.0 μ H to 51 μ H	2.0
5xxx	3.88 (0.153)	2.20 (0.087)	4.18 (0.165)	11.00 to 30.00 (0.433 to 1.181)	1 k Ω to 15 k Ω	10.0 μ H to 78 μ H	3.5
6xxx	4.35 (0.171)	2.20 (0.087)	4.65 (0.183)	11.00 to 30.00 (0.433 to 1.181)	1 k Ω to 15 k Ω	10.0 μ H to 78 μ H	4.0
7xxx	4.75 (0.187)	2.20 (0.087)	5.05 (0.199)	11.00 to 30.00 (0.433 to 1.181)	1 k Ω to 15 k Ω	9.0 μ H to 76 μ H	4.5


Notes

- (1) The “xxx” part numbers will be assigned by Vishay Dale engineering after design/drawing review approval
- (2) Resistance range will depend on the product length selection
- (3) Inductance value will depend on the product length and resistance range selection, contact factory for details
- (4) Estimated power rating is based on diameter and length of the body.
For example: a 6xxx part with 20.0 mm length would have estimated power rating of 4.0 W / 25.4 mm x 20.0 mm = 3.15 W
- (5) The power dissipation requirement depends on the current waveform and frequency that comes from the ignition coil. The current in the ignition circuit occurs only during discharge. Although the ignition voltage is quite high, it is not practical to specify a continuous power rating of the noise suppressor because most of the “power” dissipation ability will depend on the mass of the final application assembly and encasing material and not on the NSRHP itself

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Biased Humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 10 %
Operational Life	1000 h at rated power, $T_A = +125\text{ }^\circ\text{C} \pm 3\text{ }^\circ\text{C}$	± 5 %
Load Life	1000 h at rated power, $T_A = +40\text{ }^\circ\text{C} \pm 2\text{ }^\circ\text{C}$, 1.5 h “ON”, 0.5 h “OFF”	± 5 %
ESD (Electrostatic Discharge)	6 kV	± 5 %
Short Time Overload	Rated voltage x 2.5 or max. overload voltage for 5 s, whichever is less	± 2 %
Load Life at High Voltage Pulse	Continuous 250 h, 45 kV pulse on the test circuit	± 5 %
Rapid Change of Temperature	-55 °C to +155 °C, 500 cycles, 15 min at each extreme	± 5 %
Moisture Resistance	+40 °C ± 2 °C, 90 % to 95 % RH, 250 h, 1.5 h “ON”, 0.5 h “OFF”	± 5 %
Low Temperature Storage	-40 °C for 24 h	± 5 %
High Temperature Exposure	1000 h at +200 °C ± 3 °C	± 10 %
Resistance to Solvents	Add aqueous wash chemical - OKEM clean or equivalent. Do not use banned solvents.	Pass the test

DESIGN NOTES

Any connector (such as cap or spring) to the NSR HP end caps should have a minimum extraction (pull) force of 30N as illustrated in Fig. 1; also, to prevent electric arc and damages, this connector should not extend beyond 2/3 of the cap length as illustrated in Fig. 2.



Minimum extraction (pull) force is 30 N (3.05 kgf)

Fig. 1




Fig. 2



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.