




Metal Oxide Resistors, Special Purpose, High Power, Ultra High Value



FEATURES

- Wattages to 400 W at +25 °C
- Derated to 0 at +230 °C
- Voltage testing to 100 kV
- Tolerance: ± 1 %; ± 2 %; ± 5 %; ± 10 %
- Two terminal styles, style 3 - tab terminal and style 4 - ferrule terminal
- TCR: ± 200 ppm/°C and ± 100 ppm/°C available, measured between +25 °C and +125 °C
- Coating: blue flameproof
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS* Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING $P_{25\text{ }^\circ\text{C}}$ W	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V	RESISTANCE RANGE Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
RJU040	RJU-40	40	25K	1K to 1G	1, 2, 5, 10	100, 200
RJU050	RJU-50	50	33K	1K to 1G	1, 2, 5, 10	100, 200
RJU070	RJU-70	70	40K	1K to 1G	1, 2, 5, 10	100, 200
RJU095	RJU-95	95	35K	1K to 1G	1, 2, 5, 10	100, 200
RJU095..1	RJU-95-1	95	35K	1K to 1G	1, 2, 5, 10	100, 200
RJU140	RJU-140	140	65K	1K to 1G	1, 2, 5, 10	100, 200
RJU140..1	RJU-140-1	140	65K	1K to 1G	1, 2, 5, 10	100, 200
RJU275	RJU-275	275	90K	100K to 1G	1, 2, 5, 10	100, 200
RJU275..1	RJU-275-1	275	90K	100K to 1G	1, 2, 5, 10	100, 200
RJU150	RJU-150	150	40K	100K to 1G	1, 2, 5, 10	100, 200
RJU150..1	RJU-150-1	150	40K	100K to 1G	1, 2, 5, 10	100, 200
RJU400	RJU-400	400	125K	100K to 1G	1, 2, 5, 10	100, 200
RJU400..1	RJU-400-1	400	125K	100K to 1G	1, 2, 5, 10	100, 200

Notes

- All resistance values are calibrated at 100 V_{DC}. Calibration at other voltages upon request
- ⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: RJU0952M50KKF071 (preferred part numbering format)

R J U 0 9 5 2 M 5 0 K K F 0 7 1

GLOBAL MODEL (see Standard Electrical Specification table)	RESISTANCE VALUE K = kΩ M = MΩ G = GΩ 1K00 = 1.0 kΩ 10M0 = 10 MΩ 1G00 = 1.0 GΩ	TOLERANCE CODE F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 %	TEMP. COEFFICIENT K = 100 ppm N = 200 ppm	PACKAGING E07 = Lead (Pb)-free, foam F07 = Tin/lead, foam	SPECIAL Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable 1 = Ferrule terminal
---	--	---	---	---	--

Historical Part Number: RJU-95-12M50KK (will continue to be accepted)

RJU-95-1	2M50	K	K	F07
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING


Note

- For additional information on packaging, refer to the Through Hole Resistor Packaging document (www.vishay.com/doc?31544)




DIMENSIONS in inches (millimeters)

Style 3




Style 4



GLOBAL MODEL	STYLE	A	B ⁽¹⁾	C	D
RJU040	3	4.500 (114.30)	0.750 (19.05)	0.500 (12.70)	n/a
RJU050	3	6.000 (152.40)	0.750 (19.05)	0.500 (12.70)	n/a
RJU070	3	8.000 (203.20)	0.750 (19.05)	0.500 (12.70)	n/a
RJU095	3	6.500 (165.10)	1.130 (28.70)	0.750 (19.05)	n/a
RJU095..1	4	7.690 (195.33)	1.130 (28.70)	n/a	0.812 (20.62)
RJU140	3	10.500 (266.70)	1.130 (28.70)	0.750 (19.05)	n/a
RJU140..1	4	11.690 (296.93)	1.130 (28.70)	n/a	0.812 (20.62)
RJU275	3	14.500 (368.30)	1.500 (38.10)	1.130 (28.70)	n/a
RJU275..1	4	15.690 (398.53)	1.500 (38.10)	n/a	1.140 (28.96)
RJU150	3	6.500 (165.10)	2.000 (50.80)	1.560 (39.62)	n/a
RJU150..1	4	7.690 (195.33)	2.000 (50.80)	n/a	1.140 (28.96)
RJU400	3	18.500 (469.90)	2.000 (50.80)	1.560 (39.62)	n/a
RJU400..1	4	19.690 (500.13)	2.000 (50.80)	n/a	1.140 (28.96)

Note

⁽¹⁾ Dimensional tolerances are ± 0.016 (0.406 mm) or ± 1 %, whichever is greater



DERATING

MARKING

- DALE
- Model
- Value
- Tolerance
- Date code



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.