


## Semi-Shielded SMD Power Inductors



### FEATURES

- 6.0 mm x 6.0 mm x 4.5 mm SMD package
- Semi-shielded, wirewound ferrite construction
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### ELECTRICAL SPECIFICATIONS

#### Operating temperature:

-40 °C to +125 °C (temperature rise included)

#### Resistance to solder heat:

260 °C for 10 s (3 times max. through reflow)

### APPLICATIONS


- DC/DC power supplies
- LCD displays
- Noise suppression and filtering
- Lighting drivers
- Battery powered devices

### STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	INDUCTANCE AT 0 A (μH)	IND. TOL. (%)	DCR ± 30 % (mΩ)	HEAT RATING CURRENT DC (A) <sup>(1)</sup>	SATURATION CURRENT DC (A) <sup>(2)</sup>	SRF TYP. (MHz)
IFSC2020DEER1R0N01	1.0	30	14	4.2	8.5	110
IFSC2020DEER1R2N01	1.2	30	16	4.0	8.0	100
IFSC2020DEER1R5N01	1.5	30	18	3.7	7.0	65
IFSC2020DEER1R8N01	1.8	30	18	3.7	7.0	60
IFSC2020DEER2R2N01	2.2	30	21	3.5	6.0	52
IFSC2020DEER3R3N01	3.3	30	24	3.2	5.0	32
IFSC2020DEER4R7M01	4.7	20	31	3.0	4.0	24
IFSC2020DEER5R6M01	5.6	20	36	2.9	3.9	23
IFSC2020DEER6R8M01	6.8	20	38	2.8	3.8	14
IFSC2020DEER100M01	10	20	47	2.5	3.0	12
IFSC2020DEER150M01	15	20	77	1.9	2.3	10
IFSC2020DEER220M01	22	20	115	1.5	1.9	7
IFSC2020DEER330M01	33	20	145	1.4	1.5	6
IFSC2020DEER470M01	47	20	220	1.1	1.3	5
IFSC2020DEER560M01	56	20	310	1.0	1.1	4.5
IFSC2020DEER680M01	68	20	330	0.9	1.0	4
IFSC2020DEER820M01	82	20	460	0.8	0.9	3.9
IFSC2020DEER101M01	100	20	500	0.7	0.8	3
IFSC2020DEER121M01	120	20	620	0.7	0.75	3
IFSC2020DEER151M01	150	20	800	0.65	0.7	2.8
IFSC2020DEER181M01	180	20	930	0.6	0.65	2.6
IFSC2020DEER221M01	220	20	1200	0.5	0.6	2.4
IFSC2020DEER331M01	330	20	1800	0.4	0.5	2.2
IFSC2020DEER471M01	470	20	2000	0.35	0.4	2

#### Notes

- All test data is referenced to 25 °C ambient
  - Test condition: 100 kHz, 1 V
  - Storage condition: -40 °C to +125 °C (on board); less than 40°C and < 60 % RH (in component packaging)
- <sup>(1)</sup> DC current (A) that will cause an approximate ΔT of +40 °C  
<sup>(2)</sup> DC current (A) that will cause L<sub>0</sub> to drop approximately 30 %



DESCRIPTION				
IFSC-2020DE-01	10 $\mu$ H	$\pm 20\%$	ER	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

**GLOBAL PART NUMBER**

I F S C	2 0 2 0 D E	E R	1 0 0	M	0 1
PRODUCT FAMILY	SIZE	PACKAGE CODE	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	SERIES
		ER = tape and reel 1000 pcs/reel	100 = 10 $\mu$ H	M = $\pm 20\%$ N = $\pm 30\%$	



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.