





Through-Hole and Hanging Leads Magnetics Packaging Methods

REEL PACK



TAPE AND REEL in inches [millimeters]							BULK OR TRAY			
MODEL	PACKAGE CODE		REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE		UNITS/ TRAY	UNITS/ BOX
	LEAD (Pb)- BEARING	LEAD (Pb)- FREE					LEAD (Pb)- BEARING	LEAD (Pb)- FREE		
IRF-24	-	ER	12	2.06 [52.39]	0.2 [5.08]	5000	-	-	-	-
IRF-36	-	ER	12	2.06 [52.39]	0.2 [5.08]	5000	-	-	-	-
IRF-46	-	ER	12	2.06 [52.39]	0.2 [5.08]	3000	-	-	-	-
ICMS2321	-	-	-	-	-	-	-	EH	54	324
IHD-1	RR	ER	12	2.06 [52.39]	0.4 [10.16]	800	BH	EB	-	50
IHD-3	AC	ER	12	2.87 [72.90]	0.6 [15.24]	200	BH	EB	-	190
IHD-2	-	-	-	-	-	-	-	EB	-	150
IHD-4	-	-	-	-	-	-	-	EB	-	60
IHA-101	-	-	-	-	-	-	BA	EB	-	210
IHA-102	-	-	-	-	-	-	BA	EB	-	210
IHA-103	-	-	-	-	-	-	BA	EB	-	200
IHA-104	-	-	-	-	-	-	BA	EB	-	160
IHA-105	-	-	-	-	-	-	BA	EB	-	160
IHA-201	-	-	-	-	-	-	BA	EB	-	200
IHA-202	-	-	-	-	-	-	BA	EB	-	180
IHA-203	-	-	-	-	-	-	BA	EB	-	160
IHA-204	-	-	-	-	-	-	BA	EB	-	120
IHA-205	-	-	-	-	-	-	BA	EB	-	75
IHA-301	-	-	-	-	-	-	BA	EB	-	210
IHA-302	-	-	-	-	-	-	BA	EB	-	240
IHA-303	-	-	-	-	-	-	BA	EB	-	160
IHA-304	-	-	-	-	-	-	BA	EB	-	160
IHA-305	-	-	-	-	-	-	BA	EB	-	160
IHA-501	-	-	-	-	-	-	BA	EB	-	210
IHA-502	-	-	-	-	-	-	BA	EB	-	200
IHA-503	-	-	-	-	-	-	BA	EB	-	75
IHA-504	-	-	-	-	-	-	BA	EB	-	75
IHA-505	-	-	-	-	-	-	BA	EB	-	75
IHDC1107	-	-	-	-	-	-	-	EV	40	120
IHTH-0750IZ	-	-	-	-	-	-	-	EB	-	100
IHTH-1125KZ	-	-	-	-	-	-	-	EB	-	50
IHTH-1500MZ	-	-	-	-	-	-	-	EB	-	25
IHTH-1500TZ	-	-	-	-	-	-	-	EB	-	25
IHXL-1500VZ	-	-	-	-	-	-	-	EB	-	100
IHXL-2000VZ	-	-	-	-	-	-	-	EB	-	40
IH-3 5 μH, 27 μH, 50 μH, 100 μH	-	-	-	-	-	-	BQ	EB	-	150
IH-3 10 μH	-	-	-	-	-	-	BQ	EB	-	200
IH-3 150 μH	-	-	-	-	-	-	BQ	EB	-	50



TAPE AND REEL in inches [millimeters]							BULK OR TRAY			
MODEL	PACKAGE CODE		REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE		UNITS/ TRAY	UNITS/ BOX
	LEAD (Pb)- BEARING	LEAD (Pb)- FREE					LEAD (Pb)- BEARING	LEAD (Pb)- FREE		
IH-3 250 μ H	-	-	-	-	-	-	BQ	EB	-	75
IH-4 0 μ H	-	-	-	-	-	-	BQ	EB	-	160
IH-5 5 μ H, 10 μ H	-	-	-	-	-	-	BQ	EB	-	200
IH-5 27 μ H	-	-	-	-	-	-	BQ	EB	-	150
IH-5 50 μ H, 68 μ H, 100 μ H, 150 μ H	-	-	-	-	-	-	BQ	EB	-	50
IH-10 5 μ H, 10 μ H	-	-	-	-	-	-	BQ	EB	-	150
IH-10 27 μ H	-	-	-	-	-	-	BQ	EB	-	50
IH-10 50 μ H, 68 μ H, 100 μ H	-	-	-	-	-	-	BQ	EB	-	75
IH-15 5 μ H	-	-	-	-	-	-	BQ	EB	-	50
IH-15 10 μ H, 27 μ H	-	-	-	-	-	-	BQ	EB	-	75
IH-15 50 μ H	-	-	-	-	-	-	BQ	EB	-	60
IHM-2	-	-	-	-	-	-	PM	EB	-	20
IHB-1	-	-	-	-	-	-	BV	EB	-	48
IHB-2	-	-	-	-	-	-	BV	EB	-	30
IHB-3	-	-	-	-	-	-	BV	EB	-	20
IHB-4	-	-	-	-	-	-	BV	EB	-	16
IHB-5	-	-	-	-	-	-	BV	EB	-	16
IHB-6	-	-	-	-	-	-	BV	EB	-	16
IHV-15-500	-	-	-	-	-	-	BZ	EB	-	10
IHV-20-200	-	-	-	-	-	-	BZ	EB	-	10
IHV-28-60	-	-	-	-	-	-	BZ	EB	-	14
IHV-30-150	-	-	-	-	-	-	BZ	EB	-	5
IHV-40-39	-	-	-	-	-	-	BZ	EB	-	10
IHV-45-92	-	-	-	-	-	-	BZ	EB	-	5
IHV-50-50	-	-	-	-	-	-	BZ	EB	-	5
IHV-60-24	-	-	-	-	-	-	BZ	EB	-	5
TJ3-1U	-	-	-	-	-	-	TG	EB	-	260
TJ3-2U	-	-	-	-	-	-	TG	EB	-	169
TJ3-1U-HT	-	-	-	-	-	-	-	EB	-	260
TJ3-2U-HT	-	-	-	-	-	-	-	EB	-	169
TJ4-1U	-	-	-	-	-	-	TG	EB	-	220
TJ4-2U	-	-	-	-	-	-	TG	EB	-	121
TJ5-1U	-	-	-	-	-	-	TG	EB	-	170
TJ5-2U	-	-	-	-	-	-	TG	EB	-	100
TJ5-1U-HT	-	-	-	-	-	-	-	EB	-	170
TJ5-2U-HT	-	-	-	-	-	-	-	EB	-	100
TJ6-1U	-	-	-	-	-	-	TG	EB	-	70
TJ6-2U	-	-	-	-	-	-	TG	EB	-	49
TJ7-1U	-	-	-	-	-	-	TG	EB	-	66
TJ7-2U	-	-	-	-	-	-	TG	EB	-	30
TJ8-1U	-	-	-	-	-	-	TG	EB	-	28
TJ8-2U	-	-	-	-	-	-	TG	EB	-	16
TJ9-1U	-	-	-	-	-	-	TG	EB	-	18
TJ9-2U	-	-	-	-	-	-	TG	EB	-	9
IWAS-4832FF	-	-	-	-	-	-	-	EB	-	100
IWAS-4832EC	-	-	-	-	-	-	-	EB	-	100



TAPE AND REEL in inches [millimeters]							BULK OR TRAY			
MODEL	PACKAGE CODE		REEL SIZE	CARRIER TAPE WIDTH (W)	COMPONENT PITCH (P)	UNITS/ REEL	PACKAGE CODE		UNITS/ TRAY	UNITS/ BOX
	LEAD (Pb)- BEARING	LEAD (Pb)- FREE					LEAD (Pb)- BEARING	LEAD (Pb)- FREE		
IHDM1008	-	-	-	-	-	-	-	EV	-	120
IHDM1107	-	-	-	-	-	-	-	EV	-	120
IHDF1300	-	-	-	-	-	-	-	EH	-	120
IHPT1207	-	-	-	-	-	-	-	EL / EB	-	72
IHPT1411	-	-	-	-	-	-	-	EL / EB	-	72
IHPT1614	-	-	-	-	-	-	-	EL / EB	-	48
IHPT1710	-	-	-	-	-	-	-	EL / EB	-	72
IHDV1008	-	-	-	-	-	-	-	EV	-	90

MILITARY PART ORDERING EXAMPLES	
TRANSFORMERS AND INDUCTORS	
<p>MIL-T-27E (Basic [TF]) (Established Reliability - None)</p> $\frac{M27}{1} \frac{215}{2} \frac{05}{3} = \text{Dale type TE-3Q0TR } 1.0 \text{ mH } 2\%$	<ol style="list-style-type: none"> 1. Military specification 2. Specification sheet number 3. Specification sheet dash number indicating value and electrical ratings
<p>MIL-C-15305E (Basic [LT]) (Established Reliability MIL-C-39010)</p> $\frac{LT}{1} \frac{4}{2} \frac{K}{3} = \text{Dale type IM-2 } 0.10 \mu\text{H to } 1.00 \mu\text{H } 10\%$	<p>Note Parts will be color banded, value per military standard dash number</p> <ol style="list-style-type: none"> 4. Style 5. Grade and class 6. Family K = coil, radio frequency, fixed