


Wirewound Resistor, Ultra Precision, Epoxy Molded, Axial Lead


FEATURES

- Resistance values up to 6 M Ω
- Resistance tolerances down to $\pm 0.005\%$
- Tighter tolerances and lower resistance values available, please contact factory
- Temperature coefficients down to ± 2 ppm/ $^{\circ}\text{C}$, and up to 6000 ppm/ $^{\circ}\text{C}$
- Matched resistance sets available in tolerances down to $\pm 0.001\%$, and in temperature coefficients down to ± 0.5 ppm/ $^{\circ}\text{C}$, please contact factory
- Custom design capability available, please contact factory
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	POWER RATING W ⁽¹⁾	RESISTANCE RANGE Ω	RESISTANCE RANGE Ω	RESISTANCE RANGE Ω	RESISTANCE RANGE Ω	MAXIMUM WORKING VOLTAGE V ⁽²⁾
		$\pm 0.1\%, \pm 0.25\%, \pm 0.5\%, \pm 1\%$	$\pm 0.05\%, \pm 0.1\%, \pm 0.25\%, \pm 0.5\%, \pm 1\%$	$\pm 0.01\%, \pm 0.05\%, \pm 0.1\%, \pm 0.25\%, \pm 0.5\%, \pm 1\%$	$\pm 0.005\%, \pm 0.01\%, \pm 0.05\%, \pm 0.1\%, \pm 0.25\%, \pm 0.5\%, \pm 1\%$	
MR9352	0.750	1 to 6.0M	5 to 6.0M	50 to 6.0M	1K to 6.0M	600
MR9353	0.500	1 to 3.8M	5 to 3.8M	50 to 3.8M	1K to 3.8M	400
MR9354	0.330	1 to 2.5M	5 to 2.5M	50 to 2.5M	1K to 2.5M	400
MR9355	0.250	1 to 1.2M	5 to 1.2M	50 to 1.2M	1K to 1.2M	300
MR9356	0.200	1 to 1.0M	5 to 1.0M	50 to 1.0M	1K to 1.0M	200
MR9357	1.000	1 to 6.0M	5 to 6.0M	50 to 6.0M	1K to 6.0M	800
MR9358	1.500	1 to 6.0M	5 to 6.0M	50 to 6.0M	1K to 6.0M	900
MR9359	2.000	1 to 6.0M	5 to 6.0M	50 to 6.0M	1K to 6.0M	1000

Notes

- (1) Power rating is based on tolerance, please see derating chart.
 (2) The maximum working voltage is the highest voltage that can be applied to the resistor. Below this value, the maximum voltage that can continuously be applied is given by $(P \times R)^{1/2}$.

GLOBAL PART NUMBER INFORMATION

 Global Part Numbering example: MR9355500K00AAE66 (visit www.vishay.net SAP parts manual for all options)

M	R	9	3	5	5	5	0	0	K	0	0	A	A	E	6	6	
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--

GLOBAL MODEL (6 digits) (see Standard Electrical Specifications Global Model column for options)

VALUE (6 digits) R = decimal K = thousand M = million 15R000 = 15 Ω 1K5000 = 1.5 k Ω 1M0000 = 1 M Ω
--

TOLERANCE (1 digit) S = $\pm 0.005\%$ T = $\pm 0.01\%$ Q = $\pm 0.02\%$ A = $\pm 0.05\%$ B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1.0\%$

TC (1 digit) A = standard, 10 to 30 (W) B = 3900 (Q) C = 4500 (M) D = 6000 (N) E = 3500 (P) Y = 10 ($\geq 1 \Omega$) G = 5 ($\geq 10 \Omega$) J = 2 ($\geq 100 \Omega$)

PACKAGING CODE (3 digits) E66 = lead (Pb)-free bulk pack

SPECIAL (1 digit) (dash number) from 1 to 9 as applicable
--


Historical Part Number example: MR9355W500K0A

MR9355
HISTORICAL MODEL

W = STANDARD
TC

500 k Ω
RESISTANCE VALUE

0.05 %
TOLERANCE

DIMENSIONS in inches [millimeters]


GLOBAL MODEL	DIMENSIONS in inches [millimeters]		
	L ± 0.025 [0.635]	D ± 0.005 [0.127]	LD ± 0.002 [0.051]
MR9352	1.000 [25.40]	0.375 [9.52]	0.032 [0.813]
MR9353	0.750 [19.05]	0.375 [9.52]	0.032 [0.813]
MR9354	0.750 [19.05]	0.250 [6.35]	0.032 [0.813]
MR9355	0.500 [12.70]	0.250 [6.35]	0.032 [0.813]
MR9356	0.375 [9.52]	0.250 [6.35]	0.032 [0.813]
MR9357	1.000 [25.40]	0.500 [12.70]	0.032 [0.813]
MR9358	1.500 [38.10]	0.500 [12.70]	0.032 [0.813]
MR9359	2.000 [50.80]	0.500 [12.70]	0.032 [0.813]

MATERIAL SPECIFICATIONS

Element: nickel-chrome alloy, other materials available depending on TC requirements

Core: molded epoxy


Encapsulant: epoxy

Standard Terminals: 100 % matte tinned copper

Part Marking: MILLS, model, value, tolerance, date code

Note

- Due to resistor size limitations some resistors will have minimal information marked on parts.

DERATING


TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	MR93 RESISTOR CHARACTERISTICS
Temperature Coefficient	ppm/°C	± 10 for > 100 Ω; ± 20 for 10 Ω to 100 Ω; ± 30 for < 10 Ω
Terminal Strength	lb	4.5
Dielectric Withstanding Voltage	V _{AC}	750
Operating Temperature Range	°C	-55 to +145 (see derating chart)

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Dielectric Withstanding Voltage	MIL-STD-202 Method 301, 750 V _{RMS}	± (0.01 %) ΔR
High Frequency Vibration	MIL-STD-202 Method 204, condition D, frequency varied 10 Hz to 2000 Hz, 20 g peak	± (0.01 %) ΔR
High Temperature Exposure	MIL-STD-202 Method 108, 2000 h at 145 °C	± (0.01 %) ΔR
Load Life	MIL-STD-202 Method 108, 2000 h at 125 °C at rated power, 1.5 h "ON", 0.5 h "OFF"	± (0.1 % + 0.01 Ω) ΔR
Low Temperature Storage	-65 °C for 24 h	± (0.01 %) ΔR
Moisture Resistance	MIL-STD 202 Method 106	± (0.01 %) ΔR
Shock, Specified Pulse	MIL-STD-202 Method 213, condition I, 5 shocks in 3 directions	± (0.01 %) ΔR
Thermal Shock	MIL-STD-202 Method 107, condition B	± (0.05 %) ΔR
Short Time Overload	2x rated power for 10 min	± (0.01 %) ΔR
Terminal Strength	MIL-STD-202 Method 211, conditions A and D, 4.5 lb	± (0.01 %) ΔR



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.