

Customized Stainless Steel Braking Resistor



CAPABILITIES

- **Low power:** load bank, overvoltage limiter, crowbar, precharge, dynamic braking
- **Medium power:** braking (tramways, subways, rolling mills), inrush current limiter, static load bank
- **High power:** braking (locomotive, high speed train, haul mining trucks), control of high power motors, power generator load bank

CONTACT INFORMATION

For design assistance, contact: mcbfixedresistors@vishay.com

Design request form:

STANDARD ELECTRICAL SPECIFICATIONS RANGE OVERVIEW

MODEL	RATED POWER W	COOLING
Low power	1K to 20K	Natural
Medium power	10K to 400K	Natural or forced
High power	1M to 5M	Forced

DESCRIPTION

Vishay MCB has established an expertise in the field of high and very high power resistors. We support the traction markets, including railway, haul mining trucks and naval, motor power control, power generators.

These examples are representative of our main markets.

Our range of products is not limited to these models.

Please do not hesitate to contact us for further details about your application.

PERFORMANCE FROM DESIGN TO SERVICE

Our product range utilizes standardized and modular elements, combined into tailored systems, optionally including cooling systems.

This ensures:

- faster design, qualification, production
- ultimate reliability, the vast majority of key components are broadly utilized and proven in the field
- a guaranty of long time availability, service, and spares
- competitiveness through a scale economy

From your specification, Vishay MCB will provide a solution which is both technically and economically optimized.

THERMAL YIELD

The design, achieved through an extensive utilization of computer assisted design of mechanical and thermal models grants high thermal performances.

STABILITY / LOW MAINTENANCE COST

Vishay MCB's metal resistors do not require any specific maintenance.

Periodic inspection and cleaning is what it takes.

RELIABILITY

Stabilized processes including:

- electric welding of resistive elements and connections
- resistive elements stamping without restriction of the electrical path

The way mechanical parts are secured:

- expansion focused and controlled
- fixation on cold areas

High grade materials selection: ensure reliability and ruggedness in the most severe conditions.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.