

Ferrite Power Inductor, Drumcore



FEATURES

- 5.8 mm x 5.2 mm x 4.5 mm size
- Ferrite drumcore construction, unshielded
- Inductance range 1 μ H to 680 μ H
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES


[Product Page](#)

APPLICATIONS


- DC/DC power supplies
- Noise suppression and filtering

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	L ₀ INDUCTANCE (μ H)	INDUCTANCE TOLERANCE (%)	DCR MAX. (m Ω)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾
IDCP2218ER1R0M01	1	20	20	4.00
IDCP2218ER1R5M01	1.5	20	25	3.80
IDCP2218ER2R2M01	2.2	20	27	3.50
IDCP2218ER2R7M01	2.7	20	30	3.20
IDCP2218ER3R3M01	3.3	20	34	3.00
IDCP2218ER4R7M01	4.7	20	40	2.80
IDCP2218ER6R8M01	6.8	20	80	2.50
IDCP2218ER8R2M01	8.2	20	90	2.10
IDCP2218ER100M01	10	20	100	1.50
IDCP2218ER120M01	12	20	120	1.40
IDCP2218ER150M01	15	20	140	1.30
IDCP2218ER180M01	18	20	150	1.23
IDCP2218ER220M01	22	20	180	1.11
IDCP2218ER270M01	27	20	200	0.97
IDCP2218ER330M01	33	20	230	0.88
IDCP2218ER390M01	39	20	320	0.80
IDCP2218ER470M01	47	20	370	0.72
IDCP2218ER560M01	56	20	420	0.68
IDCP2218ER680M01	68	20	460	0.61
IDCP2218ER820M01	82	20	600	0.58
IDCP2218ER101M01	100	20	700	0.52
IDCP2218ER121M01	120	20	930	0.48
IDCP2218ER151M01	150	20	1100	0.40
IDCP2218ER181M01	180	20	1380	0.38
IDCP2218ER221M01	220	20	1570	0.35
IDCP2218ER221K01	220	10	1570	0.35
IDCP2218ER271K01	270	10	1500	0.25
IDCP2218ER331K01	330	10	3000	0.22
IDCP2218ER391K01	390	10	3500	0.20
IDCP2218ER471K01	470	10	4000	0.19
IDCP2218ER561K01	560	10	4000	0.18
IDCP2218ER681K01	680	10	4500	0.15

Notes

- All test data is referenced to 25 °C ambient
 - Operating temperature is -40 °C to +105 °C
 - Test condition: 100 kHz, 0.3 V for 8.2 μ H and below, and 1 kHz, 0.3 V for 10 μ H and above
 - Storage condition: -40 °C to +105 °C (on board); and -10 °C to +40 °C and < 70 % RH (in component packaging)
 - Resistance to solder heat: 255 °C for 10 s (2 times max. through reflow)
- ⁽¹⁾ DC current (A) that will cause an approximate Δ T of 40 °C or cause L₀ to drop by 25 %, whichever is lower

DIMENSIONS in inches [millimeters]

DESCRIPTION
IDCP2218-01

MODEL

2.2 μ H

INDUCTANCE VALUE

 $\pm 20 \%$

INDUCTANCE TOLERANCE

ER

PACKAGE CODE

GLOBAL PART NUMBER

I D C P	2 2 1 8	E R	2 R 2	M	0 1
PRODUCT FAMILY	SIZE	PACKAGE CODE	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	SERIES
		ER = tape and reel	2R2 = 2.2 μ H	M = $\pm 20 \%$ N = $\pm 30 \%$	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.