SGTPL-28



Vishay Custom Magnetics

Space Grade Planar Transformers With Multiple Output Secondaries for 150 W / 28 V Input Forward Converters



LINKS TO ADDITIONAL RESOURCES



APPLICATIONS

- High reliability Space Grade switch mode power supplies
- 28 V primary input voltage forward converters
- \bullet Active clamp or dual switch forward converters up to 150 W

FEATURES

- Input voltage range: 18 V to 36 V
- Multiple secondaries can power up to two 12 V channels or up to four 5 V channels with center tap
- Higher power density levels versus traditional planar designs
- Optimized for 150 W forward converter topologies using 28 V input and 200 kHz operation
- Over-molded windings for environmental protection in ruggedized applications
- MIL-PRF-27 grade 5, product level T, temperature class S
- MIL-STD-981 family 03 power transformer, class S compliant ⁽¹⁾⁽²⁾
- ASTM-E595 outgassing compliant ⁽³⁾
- Tin-lead (Sn63Pb37) coated terminations (does not contain tin composition percentages greater than 97 %)
- Customization available (e.g., pinouts, temperature class, screening, etc.)
- SGTPL design; PATENT(S): www.vishay.com/patents

Notes

- ⁽¹⁾ Screening codes S and B only
- ⁽²⁾ Clarifications to MIL-STD-981 (1):
 - a. MIL-STD-981 figures 3b, c, and d do not apply to this assembly's build construction
 - b. MIL-STD-981 5.5.10 & 5.5.11: parts soldered and inspected to J-STD-001S (space addendum)
 - c. Corona discharge is not applicable
- ⁽³⁾ Applies to all external materials

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	CONDITIONS	LIMITS	UNITS				
Dialoctric withstand voltage (DWAA (1)	Primary to secondary, windings to core	1250	V _{DC}				
Dielectric withstand voltage (DWV)	Primary to primary, secondary to secondary	500	V _{DC}				
Insulation resistance (2)	Windings to windings and core, 10 $G\Omega$ min.	500	V _{DC}				
Power		150	W				
Operating temperature	Continuous	-55 to +130	°C				
Storage temperature	Continuous	-65 to +155	°C				
Frequency		100 to 500	kHz				

Notes

(1) Test conditions adjusted per MIL-STD-981 and MIL-PRF-27 4.7.9.1 during group A and B testing; tested at equivalent DC test voltage

⁽²⁾ Test conditions adjusted per MIL-STD-981 and MIL-PRF-27 4.7.11 during group A and B testing



Vishay Custom Magnetics

STANDARD ELECTRICAL SPECIFICATIONS (part number specific)														
					ICE		MAX.	DCR MAX. (mΩ)						
	RIMARY INPUT DLTAGE	CONDARY JTPUT VOLTAGE	IRNS RATIO RI : SEC) ⁽²⁾	TIMIZED PERATING FREQ 42)	PRIMARY INDUCTAN	(Hr) ⁽³⁾	A) ⁽³⁾	limary 1	limary 2	timary 3	CONDARY 1	CONDARY 2	CONDARY 3	JTPUT POWER (4)(5) (4)(5)
PART NUMBER ⁽¹⁾	ESS	Sog	55	553 502	MIN.	MAX.	ΞΞ	Н	Н	Н	SE	SE	SE	252
SGTPL2516T02812_	18 to 36	12	0.600 : 1	200	38	65	0.5	7	7	n/a	10	20	n/a	150
SGTPL2516T02805_	18 to 36	5	1.500 : 1	200	38	65	0.5	10	10	10	7	7	n/a	150
SGTPL2511T02812_	18 to 36	12	0.600 : 1	200	38	65	0.5	15	15	15	20	20	n/a	100
SGTPL2511T02805_	18 to 36	5	1.500 : 1	200	38	65	0.5	15	15	15	10	10	10	100

Notes

• All test data is referenced to 25 °C ambient unless otherwise specified

⁽¹⁾ See below sections for screening code options

 $^{(2)}$ Turns ratio test condition: \pm 3 %, 1 V_{RMS}, 100 kHz

⁽³⁾ Inductance test condition: 100 mV_{RMS}, 200 kHz

⁽⁴⁾ Typical power ratings for a 25 °C temperature rise

⁽⁵⁾ Derate maximum output power linearly from +105 °C to +130 °C





Vishay Custom Magnetics

SCREENING BREAKDOWN TABLE								
	P = PRODUCTION SCREENED	L = LOW EARTH ORBIT (LEO) SCREENED	B = MIL-STD-981 TABLE VI CLASS B SCREENED	S = MIL-STD-981 TABLE VI AND XII CLASS S SCREENED				
PRODUCTION SCREENING (sample size = 100 %)								
Electrical characteristics (continuity, inductance (L _S), turns ratio (TR), phase, leakage inductance, DWV, insulation resistance, DCR)	\checkmark	\checkmark	\checkmark	\checkmark				
Mechanical inspection	\checkmark	\checkmark	\checkmark	\checkmark				
Visual inspection	\checkmark	\checkmark	\checkmark	\checkmark				
QUALITY CONFORMANCE SCREENING (group A) (sample size = 100 %)								
10 cycle thermal shock (-55 °C to +130 °C)	n/a	\checkmark	n/a	n/a				
96 h burn-in at 130 °C (unpowered)	n/a	\checkmark	n/a	n/a				
25 cycle thermal shock (-55 °C to +130 °C)	n/a	n/a	\checkmark	\checkmark				
96 hour burn-in at 130 °C (powered) (130 °C = ambient temp. + temp. rise)	n/a	n/a	\checkmark	\checkmark				
Induced voltage	n/a	n/a	\checkmark	\checkmark				
Dielectric withstanding voltage (DWV)	n/a	\checkmark	\checkmark	\checkmark				
Insulation resistance (IR)	n/a	\checkmark	\checkmark	\checkmark				
Electrical characteristics (continuity, LS, TR, phase, leakage inductance, DCR)	n/a	\checkmark	\checkmark	\checkmark				
Radiographic inspection	n/a	n/a	n/a	\checkmark				
Mechanical inspection (sampled per table V; MIL-STD-981)	n/a	\checkmark	\checkmark	\checkmark				
Visual inspection (100 %)	n/a	\checkmark	\checkmark	\checkmark				
QUALIFICATION INSPECTION (group B) (sample size = 4 pieces)								
MIL-STD-981 table XII	n/a	n/a	n/a	\checkmark				

TYPICAL BOARD PIN LAYOUT



Revision: 01-Apr-2025

3

Document Number: 34647

For technical questions, contact: <u>magnetics@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



www.vishay.com

SGTPL-28

Vishay Custom Magnetics





Revision: 01-Apr-2025

4 For technical questions, contact: <u>magnetics@vishay.com</u> Document Number: 34647

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2025 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED

Revision: 01-Jan-2025

1