


# Electromagnetic Haptic Feedback Actuator With Carrier for Mounting



## FEATURES

- High displacement (1.5 mm) for excellent touch perception through gloves
- Wide frequency band 50 Hz to 500 Hz
- Available in four sizes for force output up to 120 N
- Size: 73.66 mm x 43.13 mm x 16.73 mm
- High impulse vibrations for clear tactile feedback in noisy environments
- Drives 0.5 kg load to 6 g's of acceleration with 12 V, 5 ms pulse (tested with Vishay's custom spring return fixture)
- Operates on low drive voltages from 8 V<sub>p-p</sub> to 16 V<sub>p-p</sub>
- Includes Immersion license for use of haptics
- Customization options for carrier available
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

## LINKS TO ADDITIONAL RESOURCES



## DESCRIPTION

The IHPC is an electromechanical haptic actuator that exploits solenoid technology to enable extremely responsive, high power touch feedback at low drive voltages. The device takes an amplified ac voltage input and produces a corresponding mechanical driving force for the feedback. Includes an IHPT<sup>®</sup> haptic device mounted to a robust aluminum carrier with springs to achieve oscillatory motion. The assembly includes four mounting holes for easy installation into the end application or test fixture. Ideal for prototyping use.

## APPLICATIONS

- Touch screens
- Appliances, industrial equipment, factory automation and control
- Touch screens for human-machine interfaces

## RELIABILITY SPECIFICATION

- Operating temperature range: -25 °C to 105 °C
- Tested to 1 million cycles
- Dielectric withstand voltage (coil to mount), 5 mA, 60 s = 150 V<sub>DC</sub>

STANDARD ELECTRICAL SPECIFICATIONS								
PART NUMBER	FORCE OUTPUT (N)	SPRING k CONSTANT TYP.	FORCE COEFFICIENT	RESPONSE TIME TYP. (ms)	L <sub>0</sub> INDUCTANCE ± 20 % AT 1 kHz, 0.25 V, 0 A (mH)	I <sub>RMS</sub> TYP. (A <sub>RMS</sub> )	DCR TYP. (Ω)	DCR MAX. (Ω)
IHPC1207AGELR39AA0	25	165 N/mm (940 lbf/in) x 2	0.39	5	1.35	1.1	0.95	1.04
IHPC1710ACEL1R2AA0	45	165 N/mm (940 lbf/in) x 2	1.2	5	4.04	0.8	2	2.2
IHPC1411AFELR73AA0	80	165 N/mm (940 lbf/in) x 2	0.73	5	1.8	1.1	0.95	1.1
IHPC1614ACEL2R7BA0	120	165 N/mm (940 lbf/in) x 2	2.7	5	3.5	1.2	1.2	1.32

### Notes

- All specifications are referenced to 25 °C ambient, and assume a 0.75 mm (0.030") gap
  - Operating temperature range -25 °C to +105 °C
  - Rated operating voltage: 16 V maximum
- (1) Applied force, in newtons, can be estimated by the following equation:  $F = \text{FORCE COEFFICIENT} \times I_{PK}^2$

This product is covered by a license from Immersion or its affiliates solely when incorporated into haptic products in an authorized field of use as set forth in more detail at the following link: [www.vishay.com/doc?34602](http://www.vishay.com/doc?34602). Protected under one or more of the U.S. Patents found at the following address [www.immersion.com/patent-marking.html](http://www.immersion.com/patent-marking.html) and other patents.

**GLOBAL PART NUMBER**

I H P C	1 4 1 1 A F	E L	R 7 3	A A 0
PRODUCT FAMILY	SIZE	PACKAGE CODE	FORCE COEFFICIENT	SERIES
		EL = includes Immersion license	R73 = 0.73	

**DESCRIPTION**

IHPC1411AF	R73	TRAY	e3
MODEL	FORCE COEFFICIENT	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

**MATERIAL**

Core	Laminated steel
Wire	Copper, PU/PA insulated
Solder	Hot dip tin
Carrier	Aluminum
Springs	Steel


**WEIGHT**

IHPC1207AGELR39AA0	81.8 g
IHPC1710ACEL1R2AA0	145 g
IHPC1411AFELR73AA0	138 g
IHPC1614ACEL2R7BA0	218.8 g

**SOLDER COMPOSITION**





Sn	99.3 %
Cu	0.7 %

**DIMENSIONS** in inches [millimeters]





**IHPC1207AG**


**DIMENSIONS** in inches [millimeters]

**IHPC1710AC**







**IHPC1411AF**




**DIMENSIONS** in inches [millimeters]

IHPC1614AC




**TYPICAL APPLICATION**





**TYPICAL RESPONSE CURVES**

**SPRING A**



**SPRING B**






### QUICK START INSTRUCTIONS

- Mount the haptic actuator assembly into the end system using the steps outlined in “Installation into End Application” section
- Generating haptic feedback
  - Apply an AC voltage signal to the two flying leads

### CONSTRUCTION DIAGRAM

#### IHPC1411AFELR73AA0

(complete actuator with carrier)



## INSTALLATION INTO END APPLICATION


To mount haptic actuator assembly into the end system or test fixture, secure device using the four mounting holes available in the carrier:

- a. Connect the **I-bar carrier wing** assembly to the moving portion (e.g., LCD display)
- b. Connect the **U-core carrier wing** assembly to the frame or stationary portion of the haptic system (e.g., frame)
- c. Tighten all socket head screw with an M1.5 Allen wrench

## INSTRUCTIONS FOR SWAPPING OUT SPRING

The stiffness of the spring (or other return mechanisms such as elastomeric rings or leaf springs) can significantly influence the actuator's frequency response. A stiffer spring (higher spring k constant) can increase the resonant frequency of the system. Conversely, a softer spring will lower it.

Follow the below instructions to swap out the springs with the second set of springs that was provided with the purchased product or with other custom springs as desired.



1. The device comes pre-assembled with 165 N/mm springs. To remove the currently installed springs, disassemble the carrier as follows:
  - a. Use vice, clamp, or similar fixture to compress both carrier wings together to loosen the spring tension and allow for removal of **retaining rings**
  - b. Remove **retaining rings**
  - c. Pull apart the **U-core carrier wing, I-bar carrier wing, pins, and O-rings** (the **bushings and IHPT** can remain mounted to the carrier)
2. To install new springs, re-assemble the carrier as follows:
  - a. Select the desired **spring**
  - b. Ensure **bushings** are secure in the holes and are flush with the outside of the carrier
  - c. Insert one **O-ring** each to both **pins**, push **O-ring** all the way to the head of the **pin**
  - d. Insert **pins** into the **U-core carrier wing** assembly



- e. Insert one **spring** onto each **pin**, making sure the **springs** fit around the **bushing**
- f. Assemble the **I-bar carrier wing** to the **U-core carrier wing** assembly
- g. Use vice, clamp, or similar fixture to compress the **carrier wings** to allow access to the retaining grooves on the **pins**
- h. Insert the remaining two **O-rings** onto the protruding ends of the **pins**; push **O-rings** into counter-bore hole so they are seated around pin
- i. Install **retaining rings** to grooves of the **pins** to secure **pins** in place
- j. Release pressure and remove assembly from vice
- k. If necessary, tighten **M3 x 0.5 mm socket head screws** with an M1.5 Allen wrench to secure IHPT to carrier



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.