


Wet Tantalum Capacitors Sintered Anode TANTALEX™ Capacitors for Operation to +125 °C, Elastomer-Sealed



LINKS TO ADDITIONAL RESOURCES



PERFORMANCE CHARACTERISTICS

Operating Temperature: -55 °C to +85 °C
(to +125 °C with voltage derating)

Capacitance Tolerance: at 120 Hz, +25 °C.
± 20 % standard. ± 10 %, ± 5 % available as special.

DC Leakage Current (DCL max.):
at +25 °C, +85 °C, +125 °C: leakage current shall not exceed the values listed in the Standard Ratings tables.

Life Test: capacitors are capable of withstanding a 2000 h life test at a temperature of +85 °C or +125 °C at the applicable DC working voltage.

FEATURES

- Axial through-hole terminations: standard tin / lead (SnPb), 100 % tin (RoHS-compliant) available
- Vishay Sprague model 109D tubular elastomer-sealed, sintered anode TANTALEX capacitors fill the basic requirements for applications where a superior quality, reliable design for industrial, automotive and telecommunications application is desired
- Model 109D capacitors are the commercial equivalents of Tansitor style WC, UWC, Mallory-NACC style TLS, TLH and the military style CL64 and CL65, designed to meet the performance requirements of military specification MIL-DTL-3965
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available



Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

Following the life test:

1. DCL shall not exceed the initial requirements or 1 µA, whichever is greater.
2. The ESR shall meet the initial requirement.
3. Change in capacitance shall not exceed 10 % from the initial measurement. For capacitors with voltage ratings of 15 V_{DC} and below, change in capacitance shall not exceed + 10 %, - 25 % from the initial measurement.

ORDERING INFORMATION						
109D	207	X0	006	C	0	E3
MODEL	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT +85 °C	CASE CODE	STYLE NUMBER	RoHS-COMPLIANT
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow	X0 = ± 20 % X9 = ± 10 % X5 = ± 5 % special order	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	See Ratings and Case Codes table	0 = no outer sleeve Standard 2 = outer plastic film insulation	E3 = 100 % tin termination (RoHS-compliant) Blank = SnPb termination (standard design)

Note

- Packaging: the use of formed plastic trays for packaging these axial lead components is standard. Tape and reel is not available due to the unit weight

DIMENSIONS in inches [millimeters]


CASE CODE	BARE TUBE		WITH PLASTIC-FILM INSULATING SLEEVE		LEAD LENGTH
	D	L	D MAX.	L ⁽¹⁾	
C	0.188 ± 0.016 [4.78 ± 0.41]	0.453 + 0.031 / - 0.016 [11.51 + 0.79 / - 0.41]	0.219 [5.56]	0.608 [15.45]	1.500 ± 0.250 [38.10 ± 6.35]
F	0.281 ± 0.016 [7.14 ± 0.41]	0.641 + 0.031 / - 0.016 [16.28 + 0.79 / - 0.41]	0.312 [7.92]	0.796 [20.22]	2.250 ± 0.250 [57.15 ± 6.35]
T	0.375 ± 0.016 [9.53 ± 0.41]	0.766 + 0.031 / - 0.016 [19.46 + 0.79 / - 0.41]	0.406 [10.31]	0.921 [23.40]	2.250 ± 0.250 [57.15 ± 6.35]
K ⁽²⁾	0.375 ± 0.016 [9.53 ± 0.41]	1.062 + 0.031 / - 0.016 [26.97 + 0.79 / - 0.41]	0.406 [10.31]	1.217 [30.91]	2.250 ± 0.250 [57.15 ± 6.35]

Notes

- ⁽¹⁾ For reference only
- ⁽²⁾ Replaces previous W case

RATINGS AND CASE CODES (Standard)

μF	6 V	8 V	10 V	15 V	20 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V	150 V
1.7													C	C
2.5												C		
3.0												C		C
3.5											C			
3.6													C	
4.0										C				
4.5									C					
4.7												C		
5.0									C					
6.8											C			F
7.0							C							
8.0							C							
8.2										C				
9.0													F	
10						C			C			F		
11												F		F
13											F			
14													F	
15				C			C				F			
18													T	
20			C							F				
22		C				C			F			F		F
25		C							F				T	
27					C	C								
30	C											T		
33				C							F			
39										F				T
40							F				T			
43												T		
47			C						F					
50						F				T				
56		C									T		K	
60									T					



RATINGS AND CASE CODES (Standard)														
μF	6 V	8 V	10 V	15 V	20 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V	150 V
68	C						F	F		T				
70				F										
82									T					
86												K		
100			F			F/T	T							
110											K			
120				F				T						
140	F									K				
150							T							
160									K					
170				T										
180			F			T								
220		F			T	F								
250			T											
270	F			T				K						
290	T	T												
300							K							
330	T													
350						K								
390			T											
430		T												
540				K										
560	T													
750			K											
850		K												
1200	K													

RATINGS AND CASE CODES (Extended)													
μF	6 V	8 V	10 V	15 V	20 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V
2.0												C	
6.8													C
8.2												C	
10												C	
12											C		
15											C		
18										C			
22									C		C		
27										C			F
33								C	C			F	T
39							C					F	T
47						C	C	C			F		T
56					C		C				F	T	K
68				C		C				F		T	
82				C	C				F		F		K
86												T	
100			C	C						F			
110											T		
120			C					F	F			K	
140	C									T			
150			C				F						
160									T				



RATINGS AND CASE CODES (Extended)													
μF	6 V	8 V	10 V	15 V	20 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V
180		C				F	F				T		
200											T		
220					F		F	T		T	K		
250									T				
270				F		F			T	K	K		
330				F	F		T		K				
350						T							
390			F	F			T	T					
470		F	F				T	K					
510				T									
540				T									
560			F			T	K						
680		F				K							
750						K							
820	F			T/K									
1000			T	K									
1200			T/K										
1500	T		K										
1800		K											
2200	K												

STANDARD RATINGS											
CAPACITANCE (μF)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS	
			AT +25 °C	AT -55 °C	(μA) AT		CHANGE (%) AT			RIPPLE	
			120 Hz	120 Hz	+25 °C	+85 °C	-55 °C	+85 °C	+125 °C	CURRENT	
			(Ω)	(Ω)		+125 °C				120 Hz	
										(mA)	
6 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C											
30	C	109D306X0006C0	4.2	100	1.0	2.0	-40	+10.5	+12	140	
68	C	109D686X0006C0	4.0	60	1.0	2.0	-40	+14	+16	160	
140	F	109D147X0006F0	2.0	40	1.0	3.0	-40	+14	+16	330	
270	F	109D277X0006F0	4.0	25	1.0	7.0	-44	+17.5	+20	270	
290	T	109D297X0006T0	2.0	24	2.0	7.0	-70	+20	+20	410	
330	T	109D337X0006T0	2.1	20	2.0	7.9	-44	+14	+16	410	
560	T	109D567X0006T0	3.0	25	2.0	13	-64	+17.5	+20	340	
1200	K	109D128X0006K0	1.6	20	3.0	14	-80	+25	+25	530	
8 V_{DC} AT +85 °C; 5 V_{DC} AT +125 °C											
22	C	109D226X0008C0	6.0	115	1.0	2.0	-40	+10.5	+12	130	
25	C	109D256X0008C0	4.2	100	1.0	2.0	-40	+10.5	+12	140	
56	C	109D566X0008C0	4.0	59	1.0	2.0	-40	+14	+16	160	
220	F	109D227X0008F0	4.0	30	1.0	7.0	-44	+17.5	+20	270	
290	T	109D297X0008T0	2.0	24	2.0	9.5	-70	+20	+20	410	
430	T	109D437X0008T0	3.2	25	2.0	14	-64	+17.5	+20	410	
850	K	109D857X0008K0	1.0	22	4.0	16	-80	+25	+25	670	
10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C											
20	C	109D206X0010C0	5.0	175	1.0	2.0	-32	+10.5	+12	140	
47	C	109D476X0010C0	5.0	100	1.0	2.0	-36	+14	+16	160	
100	F	109D107X0010F0	2.1	60	1.0	4.0	-36	+14	+16	270	
180	F	109D187X0010F0	4.0	40	1.0	7.0	-36	+14	+16	270	
250	T	109D257X0010T0	2.0	30	2.0	10	-40	+14	+16	410	
390	T	109D397X0010T0	3.0	25	2.0	16	-64	+17.5	+20	340	
750	K	109D757X0010K0	1.0	23	4.0	16	-80	+25	+25	670	

Note

(1) Part numbers shown are for units with ± 20 % capacitance tolerance and uninsulated capacitors. For ± 10 % units, change the digit following the letter “X” from “0” to “9”. For units with outer plastic-film insulation, substitute “2” for “0” at the end of the part number. For RoHS-compliant add “E3”



STANDARD RATINGS											
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS RIPPLE CURRENT 120 Hz (mA)	
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	(μ A) AT +25 °C	(μ A) AT +85 °C +125 °C	CHANGE (%) AT				
								-55 °C	+85 °C	+125 °C	
15 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C											
15	C	109D156X0015C0	6.0	155	1.0	2.0	-24	+10.5	+12	130	
33	C	109D336X0015C0	5.0	90	1.0	2.0	-28	+14	+16	160	
70	F	109D706X0015F0	3.6	75	1.0	4.0	-28	+14	+16	270	
120	F	109D127X0015F0	4.0	50	1.0	7.0	-28	+17.5	+20	270	
270	T	109D277X0015T0	3.0	30	2.0	16	-56	+17.5	+20	340	
540	K	109D547X0015K0	1.2	23	6.0	24	-80	+25	+25	610	
20 V_{DC} AT +85 °C; 13 V_{DC} AT +125 °C											
27	C	109D276X0020C0	5.0	100	1.0	2.0	-20	+11	+14	160	
220	T	109D227X0020T0	4.0	3	2.0	16	-48	+13	+15	410	
25 V_{DC} AT +85 °C; 15 V_{DC} AT +125 °C											
10	C	109D106X0025C0	6.0	220	1.0	2.0	-16	+8	+9	130	
22	C	109D226X0025C0	5.0	140	1.0	3.0	-20	+10.5	+12	160	
50	F	109D506X0025F0	4.0	70	1.0	5.0	-28	+13	+15	270	
100	F	109D107X0025F0	4.0	50	1.0	10	-28	+13	+15	270	
100	T	109D107X0025T0	4.0	45	2.0	10	-48	+13	+15	410	
180	T	109D187X0025T0	4.0	32	2.0	18	-48	+13	+15	340	
220	F	109D227X0025F0	2.6	36	3.2	16	-60	+13	+16	300	
350	K	109D357X0025K0	1.3	24	7.0	28	-70	+25	+25	580	
30 V_{DC} AT +85 °C; 20 V_{DC} AT +125 °C											
7.0	C	109D705X0030C0	8.0	275	1.0	2.0	-16	+8	+12	110	
8.0	C	109D805X0030C0	7.5	275	1.0	2.0	-16	+8	+12	130	
15	C	109D156X0030C0	8.0	175	1.0	2.0	-20	+10.5	+12	160	
40	F	109D406X0030F0	4.0	65	1.0	5.0	-24	+10.5	+12	270	
68	F	109D686X0030F0	6.0	60	1.0	8.0	-24	+13	+15	270	
100	T	109D107X0030T0	6.0	40	2.0	12	-28	+10.5	+12	410	
150	T	109D157X0030T0	4.1	35	2.0	18	-48	+13	+15	340	
300	K	109D307X0030K0	1.6	25	8.0	32	-60	+25	+25	550	
35 V_{DC} AT +85 °C; 22 V_{DC} AT +125 °C											
68	F	109D686X0035F0	6.0	60	1.0	8	-24	+12	+15	270	
120	T	109D127X0035T0	4.0	38	2.0	16	-30	+13	+15	410	
270	K	109D277X0035K0	2.2	23	8.0	32	-45	+20	+25	500	
50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C											
4.5	C	109D455X0050C0	9.0	400	1.0	2.0	-16	+5	+6	110	
5.0	C	109D505X0050C0	9.0	400	1.0	2.0	-16	+5	+6	130	
10	C	109D106X0050C0	8.0	250	1.0	2.0	-24	+8	+9	160	
22	F	109D226X0050F0	7.0	95	1.0	4.0	-20	+10.5	+12	230	
25	F	109D256X0050F0	6.0	95	1.0	5.0	-20	+10.5	+12	270	
47	F	109D476X0050F0	6.0	70	1.0	9.0	-28	+13	+15	270	
60	T	109D606X0050T0	3.0	45	2.0	12	-16	+10.5	+12	410	
82	T	109D826X0050T0	4.0	45	2.0	16	-32	+13	+15	340	
160	K	109D167X0050K0	2.2	27	8.0	32	-50	+25	+25	460	

Note

(1) Part numbers shown are for units with $\pm 20\%$ capacitance tolerance and uninsulated capacitors. For $\pm 10\%$ units, change the digit following the letter "X" from "0" to "9". For units with outer plastic-film insulation, substitute "2" for "0" at the end of the part number. For RoHS-compliant add "E3"



STANDARD RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS
			AT +25 °C	AT -55 °C	(A) AT		CHANGE (%) AT			RIPPLE
			120 Hz	120 Hz	+25 °C	+85 °C	-55 °C	+85 °C	+125 °C	CURRENT
			(Ω)	(Ω)		+125 °C				120 Hz
										(mA)
60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C										
4.0	C	109D405X0060C0	10.0	550	1.0	2.0	-16	+5	+6	110
8.2	C	109D825X0060C0	8.0	275	1.0	2.0	-24	+8	+9	140
20	F	109D206X0060F0	5.0	105	1.0	5.0	-16	+10.5	+12	270
39	F	109D396X0060F0	7.0	90	1.0	9.0	-28	+10.5	+12	230
50	T	109D506X0060T0	4.0	50	2.0	12	-16	+10.5	+12	410
68	T	109D686X0060T0	6.0	50	2.0	16	-32	+10.5	+12	340
140	K	109D147X0060K0	2.4	28	8.0	32	-40	+20	+20	430
75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C										
3.5	C	109D355X0075C0	10.0	650	1.0	2.0	-16	+5	+6	110
6.8	C	109D685X0075C0	8.0	300	1.0	2.0	-20	+8	+9	140
13	F	109D136X0075F0	6.0	160	1.0	4.0	-16	+8	+9	190
15	F	109D156X0075F0	6.5	150	1.0	5.0	-16	+8	+9	270
33	F	109D336X0075F0	7.0	90	1.0	10	-24	+10.5	+15	230
40	T	109D406X0075T0	5.0	60	2.0	12	-16	+10.5	+12	410
56	T	109D566X0075T0	6.0	60	2.0	17	-28	+10.5	+15	300
110	K	109D117X0075K0	3.1	29	9.0	36	-35	+20	+20	400
100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C										
2.5	C	109D255X0100C0	26.5	950	1.0	2.0	-16	+7	+8	100
3.0	C	109D305X0100C0	10.0	800	1.0	2.0	-16	+7	+8	110
4.7	C	109D475X0100C0	10.0	500	1.0	2.0	-16	+7	+8	130
10	F	109D106X0100F0	6.0	215	1.0	4.0	-16	+7	+8	190
11	F	109D116X0100F0	6.0	200	1.0	4.0	-16	+7	+8	230
22	F	109D226X0100F0	7.0	100	1.0	9.0	-16	+7	+8	230
30	T	109D306X0100T0	4.0	80	2.0	12	-16	+7	+8	340
43	T	109D436X0100T0	6.0	70	2.0	17	-20	+7	+8	300
86	K	109D866X0100K0	3.1	30	9.0	36	-25	+15	+15	400
125 V_{DC} AT +85 °C; 85 V_{DC} AT +125 °C										
1.7	C	109D175X0125C0	54.6	1250	1.0	2.0	-16	+7	+8	100
3.6	C	109D365X0125C0	15.0	600	1.0	2.0	-16	+7	+8	110
9.0	F	109D905X0125F0	15.0	240	1.0	5.0	-16	+7	+8	210
14	F	109D146X0125F0	12.0	167	1.0	7.0	-16	+7	+8	190
18	T	109D186X0125T0	11.0	129	2.0	9.0	-16	+7	+8	340
25	T	109D256X0125T0	10.0	93	2.0	13	-16	+7	+8	260
56	K	109D566X0125K0	4.1	3.2	10	40	-25	+15	+15	400
150 V_{DC} AT +85 °C; 100 V_{DC} AT +125 °C										
1.7	C	109D175X0150C2	42	1100	1.0	3.0	-14	7	8	110
3.0	C	109D305X0150C2	15	600	1.0	3.0	-14	7	10	140
6.8	F	109D685X0150F2	15	300	2.0	10	-14	10	12	250
11	F	109D116X0150F2	12	250	2.0	10	-14	10	12	250
22	F	109D226X0150F2	4.0	100	5.0	25	-20	12	15	250
39	T	109D396X0150T2	2.2	60	10	40	-16	14	16	400

Note

(1) Part numbers shown are for units with $\pm 20\%$ capacitance tolerance and uninsulated capacitors. For $\pm 10\%$ units, change the digit following the letter "X" from "0" to "9". For units with outer plastic-film insulation, substitute "2" for "0" at the end of the part number. For RoHS-compliant add "E3"



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER ⁽¹⁾	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	(μ A) AT	+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C
6 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C										
140	C	109D147X0006C2	3.0	54	2.0	9.0	-45	+13	+16	160
820	F	109D827X0006F0	2.5	18	3.0	14	-88	+16	+20	300
1500	T	109D158X0006T0	1.5	18	5.0	20	-90	+20	+25	480
2200	K	109D228X0006K0	1.0	13	6.0	24	-90	+25	+30	670
8 V_{DC} AT +85 °C; 5 V_{DC} AT +125 °C										
180	C	109D187X0008C0	3.0	45	2.0	9.0	-60	+13	+16	180
470	F	109D477X0008F0	2.5	25	3.0	14	-75	+16	+20	300
680	F	109D687X0008F0	2.5	22	3.0	14	-90	+16	+20	300
1800	K	109D188X0008K0	1.0	14	7.0	25	-60	+20	+30	670
10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C										
100	C	109D107X0010C0	3.0	60	2.0	9.0	-50	+13	+16	160
120	C	109D127X0010C0	4.0	60	2.0	9.0	-45	+13	+16	160
150	C	109D157X0010C0	3.0	54	2.0	9.0	-55	+13	+16	180
390	F	109D397X0010F0	2.5	30	3.0	16	-70	+16	+20	300
470	F	109D477X0010F0	2.5	30	3.0	16	-65	+16	+20	300
560	F	109D567X0010F0	2.5	27	3.0	16	-77	+16	+20	300
1000	T	109D108X0010T0	1.5	20	5.0	20	-75	+20	+25	480
1200	K	109D128X0010K0	1.0	18	7.0	25	-75	+30	+30	670
1200	T	109D128X0010T0	1.5	18	5.0	20	-88	+20	+25	480
1500	K	109D158X0010K0	1.0	15	7.0	25	-88	+25	+30	670
15 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C										
68	C	109D686X0015C0	4.0	80	2.0	9.0	-40	+13	+16	140
82	C	109D826X0015C0	4.0	80	2.0	9.0	-38	+13	+16	160
100	C	109D107X0015C0	4.0	72	2.0	9.0	-44	+13	+16	160
270	F	109D277X0015F0	2.5	35	3.0	16	-60	+16	+20	300
330	F	109D337X0015F0	2.5	35	3.0	16	-60	+16	+20	300
390	F	109D397X0015F0	2.5	31	3.0	16	-66	+16	+20	300
510	T	109D517X0015T0	1.8	25	6.0	24	-65	+20	+25	340
540	T	109D547X0015T0	1.8	22	6.0	24	-77	+20	+25	440
820	T	109D827X0015T0	1.8	22	6.0	24	-77	+20	+25	440
820	K	109D827X0015K0	1.2	20	8.0	32	-70	+30	+30	610
1000	K	109D108X0015K0	1.2	17	8.0	32	-77	+25	+30	610
20 V_{DC} AT +85 °C; 13 V_{DC} AT +125 °C										
56	C	109D566X0020C0	4.3	90	2.0	9.0	-38	+13	+16	140
82	C	109D826X0020C0	4.3	81	2.0	9.0	-43	+13	+16	160
220	F	109D227X0020F0	2.7	35	3.0	16	-60	+16	+20	300
330	F	109D337X0020F0	2.7	31	3.0	16	-66	+16	+20	300
25 V_{DC} AT +85 °C; 15 V_{DC} AT +125 °C										
47	C	109D476X0025C0	4.3	100	2.0	9.0	-35	+12	+15	140
68	C	109D686X0025C0	4.3	90	2.0	9.0	-40	+12	+15	160
180	F	109D187X0025F0	2.7	37	3.0	16	-55	+13	+16	300
270	F	109D277X0025F0	2.7	33	3.0	16	-62	+13	+16	300
350	T	109D357X0025T0	1.8	27	7.0	28	-60	+20	+25	440
560	T	109D567X0025T0	1.8	24	7.0	28	-72	+20	+25	440
680	K	109D687X0025K0	1.2	19	8.0	32	-72	+25	+30	610
750	K	109D757X0025K2	1.0	18	8.0	29	-60	+25	+25	610

Note

⁽¹⁾ Part numbers shown are for units with $\pm 20\%$ capacitance tolerance and uninsulated capacitors. For $\pm 10\%$ units, change the digit following the letter "X" from "0" to "9". For units with outer plastic-film insulation, substitute "2" for "0" at the end of the part number. For RoHS-compliant add "E3"



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS
			AT +25 °C	AT -55 °C	(μ A) AT	CHANGE (%) AT			RIPPLE	
			120 Hz	120 Hz	+25 °C	+85 °C	-55 °C	+85 °C	+125 °C	CURRENT
			(Ω)	(Ω)		+125 °C				120 Hz
										(mA)
30 V_{DC} AT +85 °C; 20 V_{DC} AT +125 °C										
39	C	109D396X0030C0	5.2	110	2.0	9.0	-28	+10	+12	140
47	C	109D476X0030C0	5.2	100	2.0	9.0	-30	+10	+12	140
56	C	109D566X0030C0	5.2	100	2.0	9.0	-38	+12	+15	140
150	F	109D157X0030F0	2.5	40	3.0	9.0	-40	+12	+15	300
180	F	109D187X0030F0	2.5	40	3.0	16	-45	+13	+16	300
220	F	109D227X0030F0	2.5	36	3.0	16	-60	+13	+16	300
330	T	109D337X0030T0	1.8	28	8.0	16	-45	+20	+25	440
390	T	109D397X0030T0	1.8	28	8.0	32	-50	+20	+25	440
470	T	109D477X0030T0	1.8	25	8.0	32	-65	+20	+25	550
560	K	109D567X0030K0	1.3	20	9.0	32	-65	+25	+30	590
35 V_{DC} AT +85 °C; 22 V_{DC} AT +125 °C										
33	C	109D336X0035C0	5.2	130	2.0	9.0	-30	+10	+12	140
47	C	109D476X0035C0	5.2	115	2.0	9.0	-35	+10	+12	140
120	F	109D127X0035F0	2.5	45	3.0	16	-45	+13	+16	300
220	T	109D227X0035T0	1.8	30	8.0	32	-45	+20	+25	440
390	T	109D337X0035T0	1.8	27	8.0	32	-58	+20	+25	440
470	K	109D477X0035K0	1.3	21	9.0	36	-58	+25	+30	590
50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C										
22	C	109D226X0050C0	5.0	150	2.0	9.0	-24	+10	+12	140
33	C	109D336X0050C0	5.0	135	2.0	9.0	-29	+10	+12	140
82	F	109D826X0050F0	2.5	55	4.0	24	-35	+10	+15	300
120	F	109D127X0050F0	2.5	49	4.0	24	-42	+12	+15	300
160	T	109D167X0050T0	1.8	32	6.0	32	-35	+20	+25	420
250	T	109D257X0050T0	1.8	29	8.0	32	-40	+20	+25	440
270	T	109D277X0050T0	1.8	29	8.0	32	-46	+20	+25	440
330	K	109D337X0050K0	1.5	22	9.0	36	-46	+25	+30	550
60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C										
18	C	109D186X0060C0	5.0	160	3.0	12	-20	+10	+12	140
27	C	109D276X0060C0	5.0	144	3.0	12	-24	+10	+12	140
68	F	109D686X0060F0	3.0	60	3.0	20	-30	+12	+15	270
100	F	109D107X0060F0	2.5	54	4.0	20	-36	+12	+15	300
140	T	109D147X0060T0	2.0	32	8.0	32	-30	+16	+20	420
220	T	109D227X0060T0	1.8	29	8.0	32	-40	+16	+20	440
270	K	109D277X0060K0	1.5	23	9.0	36	-45	+20	+25	550
75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C										
12	C	109D126X0075C0	5.0	175	2.0	12	-12	+8	+10	140
15	C	109D156X0075C0	5.0	160	2.0	12	-14	+10	+12	140
22	C	109D226X0075C0	5.0	157	3.0	12	-19	+10	+12	140
47	F	109D476X0075F0	3.0	75	4.0	24	-18	+10	+12	270
56	F	109D566X0075F0	3.0	70	4.0	24	-20	+12	+15	270
82	F	109D826X0075F0	2.5	63	4.0	24	-30	+12	+15	300
82	T	109D826X0075T2	2.5	45	5.0	20	-25	+16	+20	400
110	T	109D117X0075T0	2.0	33	9.0	36	-25	+16	+20	420
180	T	109D187X0075T0	1.8	30	9.0	36	-35	+16	+20	440
200	T	109D207X0075T0	1.8	29	8.0	32	-40	+20	+25	440
220	K	109D227X0075K0	2.2	24	10	40	-40	+20	+25	450
270	K	109D277X0075K2	1.3	24	10	40	-40	+20	+25	450

Note

(1) Part numbers shown are for units with $\pm 20\%$ capacitance tolerance and uninsulated capacitors. For $\pm 10\%$ units, change the digit following the letter "X" from "0" to "9". For units with outer plastic-film insulation, substitute "2" for "0" at the end of the part number. For RoHS-compliant add "E3"



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL		MAX. CAPACITANCE			MAX. RMS
			AT +25 °C	AT -55 °C	(μ A) AT	CHANGE (%) AT			RIPPLE	
			120 Hz	120 Hz	+25 °C	+85 °C	-55 °C	+85 °C	+125 °C	CURRENT
			(Ω)	(Ω)		+125 °C				120 Hz
										(mA)
100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C										
2.0	C	109D205X0100C0	14.0	870	3.0	12	-20	+12	+12	100
8.2	C	109D825X0100C0	6.0	250	3.0	12	-12	+12	+12	130
10	C	109D106X0100C0	6.0	200	3.0	12	-17	+10	+12	130
33	F	109D336X0100F0	3.5	85	4.0	24	-18	+15	+15	250
39	F	109D396X0100F0	3.5	80	5.0	24	-20	+12	+15	250
56	T	109D566X0100T0	2.2	45	9.0	36	-20	+15	+15	400
68	T	109D686X0100T0	2.2	40	10	40	-30	+14	+16	400
86	T	109D866X0100T0	3.2	30	10	40	-25	+15	+15	370
120	K	109D127X0100K0	2.8	30	12	48	-35	+15	+17	440
125 V_{DC} AT +85 °C; 85 V_{DC} AT +125 °C										
6.8	C	109D685X0125C0	11.7	300	3.0	12	-14	+10	+12	130
27	F	109D276X0125F0	3.5	90	5.0	24	-18	+12	+15	250
39	T	109D396X0125T0	2.2	60	10	40	-16	+14	+16	400
47	T	109D476X0125T0	2.2	50	10	40	-26	+14	+16	400
56	K	109D566X0125K0	4.1	32	10	40	-25	+15	+15	330
82	K	109D826X0125K0	2.8	32	12	48	-30	+15	+17	440

Note

(1) Part numbers shown are for units with \pm 20 % capacitance tolerance and uninsulated capacitors. For \pm 10 % units, change the digit following the letter "X" from "0" to "9". For units with outer plastic-film insulation, substitute "2" for "0" at the end of the part number. For RoHS-compliant add "E3"



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.