


Wet Tantalum Capacitors Tantalum-Case With Glass-to-Tantalum Hermetic Seal for -55 °C to +125 °C Operation, Low ESR



LINKS TO ADDITIONAL RESOURCES



FEATURES

- Models:
 - 136D - axial through-hole terminations
 - 136J - SMD, outward L-leaded terminations
 - 136L - SMD, inward L-leaded terminations
 - 136P - SMD, low profile outward L-leaded terminations
 - 136S - SMD, low profile inward L-leaded terminations
- Military specification MIL-PRF-39006/30 and 39006/31. model 136D capacitors are commercial equivalents of military style CLR90 and CLR91
- Capacitors to meet the MIL-specs must be ordered by M39006 part numbers shown in the relative specification
- Terminations: standard tin / lead (SnPb), 100 % tin (RoHS-compliant) available
- Standard and extended ratings
- Low ESR
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

HALOGEN

FREE
GREEN

(5-2008)

Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

PERFORMANCE CHARACTERISTICS

Operating Temperature: -55 °C to +85 °C
(to +125 °C with voltage derating)

Capacitance Tolerance: at 120 Hz, +25 °C. ± 20 % standard. ± 10 %, ± 5 % available as special.

DC Leakage Current (DCL Max.): at +25 °C and above: leakage current shall not exceed the values listed in the Standard Ratings Tables.

Life Test: capacitors are capable of withstanding a 2000 h life test at a temperature of +85 °C or +125 °C at the applicable rated DC working voltage.


Following life test:

1. DCL, measured at +85 °C rated voltage, shall not be in excess of the original requirement.
2. The equivalent series resistance shall not exceed 150 % of the initial requirement.
3. Change in capacitance shall not exceed 10 % from the initial measurement.

ORDERING INFORMATION						
136D	306	X0	006	C	2	E3
MODEL	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT +85 °C	CASE CODE	STYLE NUMBER	RoHS-COMPLIANT
136D = axial through-hole leaded terminations 136J = SMD, outward L-leaded terminations 136L = SMD, inward L-leaded terminations 136P = low profile SMD, outward L-leaded terminations 136S = low profile SMD, inward L-leaded terminations	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow	X0 = ± 20 % X9 = ± 10 % X5 = ± 5 %	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	See Ratings and Case Codes table	Standard temperature (max. +125 °C) 0 = no insulating sleeve 2 = polyester insulation sleeve 3 = high temperature film insulation	E3 = 100 % tin termination (RoHS-compliant design) Blank = SnPb termination (standard design)

Notes


- Packaging: the use of formed plastic trays for packaging these axial lead components is standard. Tape and reel is not available due to the unit weight
- Contact marketing for SMD capacitors availability
- Capacitors with SMD terminations are available only with high temperature (Kapton) film insulation

DIMENSIONS in inches [millimeters]


TYPE 136D	CLR 90 / 91 EQUIV.	D	L ₁	L ₂ (Max.)	E	WEIGHT (g) (Max.)
CASE CODE						
C	T1	0.188 ± 0.016 [4.78 ± 0.41]	0.453 + 0.031 / - 0.016 [11.51 + 0.79 / - 0.41]	0.734 [18.64]	1.500 ± 0.250 [38.10 ± 6.35]	2.6
F	T2	0.281 ± 0.016 [7.14 ± 0.41]	0.641 + 0.031 / - 0.016 [16.28 + 0.79 / - 0.41]	0.922 [23.42]	2.250 ± 0.250 [57.15 ± 6.35]	6.2
T	T3	0.375 ± 0.016 [9.53 ± 0.41]	0.766 + 0.031 / - 0.016 [19.46 + 0.79 / - 0.41]	1.047 [26.59]	2.250 ± 0.250 [57.15 ± 6.35]	11.6
K	T4	0.375 ± 0.016 [9.53 ± 0.41]	1.062 + 0.031 / - 0.016 [26.97 + 0.79 / - 0.41]	1.343 [34.11]	2.250 ± 0.250 [57.15 ± 6.35]	17.7

Note



- For insulated parts, add 0.015" [0.38] to the diameter. The insulation shall lap over the ends of the capacitor body

SMD PRODUCT DIMENSIONS in inches [millimeters]




TYPE	136J / 136L / 136P / 136S					136J / 136P	136L / 136S	136J / 136L		136P / 136S	
	D (max.)	L (max.)	L ₁	TI (max.)	T _w ± 0.008	A (max.)	B (max.)	H (max.)	H ₂ (max.)	LP H (max.)	LP H ₂ (max.)
C	0.228 [5.8]	0.705 [17.9]	0.469 + 0.031 / - 0.016 [11.91 + 0.79 / - 0.41]	0.157 [4.0]	0.158 [4.0]	0.773 [19.6]	0.513 [13.0]	0.177 [4.5]	0.296 [7.5]		
F	0.316 [8.0]	0.903 [22.9]	0.668 + 0.012 / - 0.12 [16.97 + 0.30 / - 0.30]	0.157 [4.0]	0.217 [5.5]	1.001 [25.4]	0.720 [18.3]	0.212 [5.4]	0.374 [9.5]		
T	0.397 [10.1]	1.051 [26.7]	0.806 + 0.012 / - 0.12 [20.47 + 0.30 / - 0.30]	0.157 [4.0]	0.331 [8.4]	1.143 [29.0]	0.858 [21.8]	0.280 [7.1]	0.492 [12.5]		
K	0.397 [10.1]	1.343 [34.1]	1.062 + 0.031 / - 0.016 [26.97 + 0.79 / - 0.41]	0.157 [4.0]	0.331 [8.4]	1.432 [36.4]	1.140 [29.0]	0.295 [7.5]	0.492 [12.5]	0.225 [5.8]	0.421 [10.7]

Note

- Use appropriate adhesive between capacitor body and the board for improved mechanical strength

PAD DIMENSIONS in inches [millimeters]

STYLE J, P

CASE CODE	A (min.)	B (nom.)	C (nom.)	D (nom.)
C	0.173 [4.40]	0.185 [4.70]	0.465 [11.80]	0.835 [21.20]
F	0.232 [5.90]	0.185 [4.70]	0.650 [16.50]	1.020 [25.90]
T	0.346 [8.80]	0.185 [4.70]	0.783 [19.90]	1.154 [29.30]
K	0.346 [8.80]	0.185 [4.70]	1.059 [26.90]	1.429 [36.30]


STYLE L, S

CASE CODE	A (min.)	B (nom.)	C (nom.)	D (nom.)
C	0.173 [4.40]	0.185 [4.70]	0.205 [5.20]	0.575 [14.60]
F	0.232 [5.90]	0.185 [4.70]	0.390 [9.90]	0.760 [19.30]
T	0.346 [8.80]	0.185 [4.70]	0.527 [13.39]	0.897 [22.79]
K	0.346 [8.80]	0.185 [4.70]	0.800 [20.32]	1.170 [29.72]

RATINGS AND CASE CODES (Standard)

μF	6 V	8 V	10 V	15 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V
1.7												C
2.5											C	
3.5										C		
3.6												C
4.0									C			
4.7											C	
5.0								C				
6.8										C		
8.0						C						
8.2									C			
9.0												F
10					C			C				
11											F	
14												F
15				C		C	C			F		
18												T
20			C						F			
22					C						F	



RATINGS AND CASE CODES (Standard)												
μF	6 V	8 V	10 V	15 V	25 V	30 V	35 V	50 V	60 V	75 V	100 V	125 V
25		C						F			T	T
30	C										T	
33				C						F		
39									F			
40						F				T		
43											T	
47			C					F				
50					F				T			
56		C								T	K	K
60								T				
68	C					F	F		T			
70				F								
82								T				
86											K	
100			F		F	T						
110										K		
120		F		F	T							
140	F								K			
150						T						
160								K				
170				T								
180			F		T							
220		F										
250			T									
270	F			T			K					
290		T										
300						K						
330	T											
350					K							
390			T									
430		T										
540				K								
560	T											
750			K									
850		K										
1200	K											



RATINGS AND CASE CODES (Extended)														
μF	6 V	8 V	10 V	15 V	25 V	30 V	35 V	40 V	50 V	60 V	63 V	75 V	100 V	125 V
6.8														C
10													C	
12												C		
18										C				
22												C		
27										C				F
33									C					
39							C	C					F	
47					C	C								T
56					C	C							T	T
68					C							F	T	K
82				C						F		F		K
100				C					F	F	F			
120			C				F		F				K	
150			C			F								
180		C			F							T		
220	C					F				T		K		
270				F	F				T	K				
300												K		
330							T		K	K				
370							K							
390			F	F		T								
470					T	T								
560	F		F		T	K								
680		F		T	K									
820	F			T										
1000				K										
1200	T		T											
1500	T	T	K											
1800		K												
2200	K													



STANDARD RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX. RIPPLE
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	AT		CHANGE (%) AT			40 kHz I_{RMS} (mA)
					+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C	
6 V_{DC} AT +85 °C; 4 V_{DC} AT +125 °C										
30	C	136(1)306(2)0006C(3)(4)	1.99	100	1	2	-40	+10.5	+12	820
68	C	136(1)686(2)0006C(3)(4)	1.58	60	1	2	-40	+14	+16	960
140	F	136(1)147(2)0006F(3)(4)	0.99	40	1	3	-40	+14	+16	1200
270	F	136(1)277(2)0006F(3)(4)	1.11	25	1	6.5	-44	+17.5	+20	1375
330	T	136(1)337(2)0006T(3)(4)	0.73	20	2	7.9	-44	+14	+16	1800
560	T	136(1)567(2)0006T(3)(4)	0.65	25	2	13	-64	+17.5	+20	1900
1200	K	136(1)128(2)0006K(3)(4)	0.50	20	3	14	-80	+25	+25	2265
8 V_{DC} AT +85 °C; 5 V_{DC} AT +125 °C										
25	C	136(1)256(2)0008C(3)(4)	1.99	100	1	2	-40	+10.5	+12	820
56	C	136(1)566(2)0008C(3)(4)	1.66	59	1	2	-40	+14	+16	900
120	F	136(1)127(2)0008F(3)(4)	1.11	50	1	2	-44	+17.5	+20	1230
220	F	136(1)227(2)0008F(3)(4)	1.12	30	1	7	-44	+17.5	+20	1370
290	T	136(1)297(2)0008T(3)(4)	0.78	25	2	6	-64	+17.5	+20	1770
430	T	136(1)437(2)0008T(3)(4)	0.71	25	2	14	-64	+17.5	+20	1825
850	K	136(1)857(2)0008K(3)(4)	0.47	22	4	16	-80	+25	+25	2330
10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C										
20	C	136(1)206(2)0010C(3)(4)	1.99	175	1	2	-32	+10.5	+12	820
47	C	136(1)476(2)0010C(3)(4)	1.84	100	1	2	-36	+14	+16	855
100	F	136(1)107(2)0010F(3)(4)	0.99	60	1	4	-36	+14	+16	1200
180	F	136(1)187(2)0010F(3)(4)	1.11	40	1	7	-36	+14	+16	1365
250	T	136(1)257(2)0010T(3)(4)	0.80	30	2	10	-40	+14	+16	1720
390	T	136(1)397(2)0010T(3)(4)	0.75	25	2	16	-64	+17.5	+20	1800
750	K	136(1)757(2)0010K(3)(4)	0.44	23	4	16	-80	+25	+25	2360
15 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C										
15	C	136(1)156(2)0015C(3)(4)	1.99	155	1	2	-24	+10.5	+12	780
33	C	136(1)336(2)0015C(3)(4)	1.66	90	1	2	-28	+14	+16	820
70	F	136(1)706(2)0015F(3)(4)	1.11	75	1	4	-28	+14	+16	1150
120	F	136(1)127(2)0015F(3)(4)	1.12	50	1	7	-28	+17.5	+20	1450
170	T	136(1)177(2)0015T(3)(4)	0.78	35	2	10	-32	+14	+16	1480
270	T	136(1)277(2)0015T(3)(4)	0.71	30	2	16	-56	+17.5	+20	1740
540	K	136(1)547(2)0015K(3)(4)	0.47	23	6	24	-80	+25	+25	2330
25 V_{DC} AT +85 °C; 15 V_{DC} AT +125 °C										
10	C	136(1)106(2)0025C(3)(4)	2.66	220	1	2	-16	+8	+9	715
22	C	136(1)226(2)0025C(3)(4)	1.99	140	1	2	-20	+10.5	+12	800
50	F	136(1)506(2)0025F(3)(4)	1.46	70	1	2	-28	+13	+15	1130
100	F	136(1)107(2)0025F(3)(4)	0.99	50	1	10	-28	+13	+15	1435
120	T	136(1)127(2)0025T(3)(4)	1.16	38	2	6	-32	+13	+15	1450
180	T	136(1)187(2)0025T(3)(4)	0.96	32	2	18	-48	+13	+15	1525
350	K	136(1)357(2)0025K(3)(4)	0.67	24	7	28	-70	+25	+25	1970

Notes

- Part number definitions:

(1) Model type:

- 136D - axial through-hole terminations
- 136J - SMD, outward L-leaded terminations
- 136L - SMD, inward L-leaded terminations
- 136P - SMD, low profile outward L-leaded terminations
- 136S - SMD, low profile inward L-leaded terminations

(2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %

(3) Style number:

- Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
- High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve

(4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



STANDARD RATINGS											
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX. RIPPLE	
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	AT		CHANGE (%) AT			40 kHz I_{RMS} (mA)	
					+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C		
30 V_{DC} AT +85 °C; 20 V_{DC} AT +125 °C											
8	C	136(1)805(2)0030C(3)(4)	3.32	275	1	2	-16	+8	+12	640	
15	C	136(1)156(2)0030C(3)(4)	2.21	175	1	2	-20	+10.5	+12	780	
40	F	136(1)406(2)0030F(3)(4)	1.66	65	1	5	-24	+10.5	+12	1120	
68	F	136(1)686(2)0030F(3)(4)	1.27	60	1	8	-24	+13	+15	1285	
100	T	136(1)107(2)0030T(3)(4)	1.13	40	2	12	-28	+10.5	+12	1450	
150	T	136(1)157(2)0030T(3)(4)	1.02	35	2	18	-48	+13	+15	1525	
300	K	136(1)307(2)0030K(3)(4)	0.69	25	8	32	-60	+25	+25	1950	
35 V_{DC} AT +85 °C; 22 V_{DC} AT +125 °C											
15	C	136(1)156(2)0035C(3)(4)	3.10	175	0.75	1.5	-20	+10.5	+12	660	
68	F	136(1)686(2)0035F(3)(4)	1.45	60	1	2	-24	+13	+15	1195	
270	K	136(1)277(2)0035K(3)(4)	0.70	26	3	12	-58	+25	+25	1950	
50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C											
5	C	136(1)505(2)0050C(3)(4)	3.98	400	1	2	-16	+5	+6	580	
10	C	136(1)106(2)0050C(3)(4)	2.66	250	1	2	-24	+8	+9	715	
25	F	136(1)256(2)0050F(3)(4)	2.13	95	1	5	-20	+10.5	+12	1005	
47	F	136(1)476(2)0050F(3)(4)	1.56	70	1	9	-28	+13	+15	1155	
60	T	136(1)606(2)0050T(3)(4)	1.33	45	2	12	-16	+10.5	+12	1335	
82	T	136(1)826(2)0050T(3)(4)	1.22	45	2	16	-32	+13	+15	1400	
160	K	136(1)167(2)0050K(3)(4)	0.71	27	8	32	-50	+25	+25	1900	
60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C											
4	C	136(1)405(2)0060C(3)(4)	4.65	550	1	2	-16	+5	+6	525	
8.2	C	136(1)825(2)0060C(3)(4)	3.24	275	1	2	-24	+8	+9	625	
20	F	136(1)206(2)0060F(3)(4)	2.32	105	1	5	-16	+8	+12	930	
39	F	136(1)396(2)0060F(3)(4)	1.70	90	1	9	-28	+10.5	+12	1110	
50	T	136(1)506(2)0060T(3)(4)	1.33	50	2	12	-16	+10.5	+12	1330	
68	T	136(1)686(2)0060T(3)(4)	1.27	50	2	16	-32	+10.5	+15	1365	
140	K	136(1)147(2)0060K(3)(4)	0.76	28	8	32	-40	+20	+20	1850	
75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C											
3.5	C	136(1)355(2)0075C(3)(4)	4.74	650	1	2	-16	+5	+6	525	
6.8	C	136(1)685(2)0075C(3)(4)	3.42	300	1	2	-20	+8	+9	610	
15	F	136(1)156(2)0075F(3)(4)	2.66	150	1	5	-16	+10.5	+9	890	
33	F	136(1)336(2)0075F(3)(4)	2.01	90	1	10	-24	+10.5	+15	1000	
40	T	136(1)406(2)0075T(3)(4)	1.50	60	2	12	-16	+10.5	+12	1250	
56	T	136(1)566(2)0075T(3)(4)	1.31	60	2	17	-28	+10.5	+15	1335	
110	K	136(1)117(2)0075K(3)(4)	0.73	29	9	36	-35	+20	+20	1850	

Notes

- Part number definitions:

(1) Model type:

- 136D - axial through-hole terminations
- 136J - SMD, outward L-leaded terminations
- 136L - SMD, inward L-leaded terminations
- 136P - SMD, low profile outward L-leaded terminations
- 136S - SMD, low profile inward L-leaded terminations

(2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %

(3) Style number:

- Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
- High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve

(4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



STANDARD RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX. RIPPLE 40 kHz I_{RMS} (mA)
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	AT		CHANGE (%) AT			
					+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C	
100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C										
2.5	C	136(1)255(2)0100C(3)(4)	5.31	950	1	4	-16	+8	+8	505
4.7	C	136(1)475(2)0100C(3)(4)	4.24	500	1	2	-16	+7	+8	565
11	F	136(1)116(2)0100F(3)(4)	3.02	200	1	4	-16	+7	+8	835
22	F	136(1)226(2)0100F(3)(4)	2.26	100	1	9	-16	+7	+8	965
25	T	136(1)256(2)0100T(3)(4)	1.60	93	2	13	-16	+7	+8	1200
30	T	136(1)306(2)0100T(3)(4)	1.55	80	2	12	-16	+8	+8	1240
43	T	136(1)436(2)0100T(3)(4)	1.31	70	2	17	-20	+8	+8	1335
56	K	136(1)566(2)0100K(3)(4)	0.80	32	10	40	-25	+15	+15	1800
86	K	136(1)866(2)0100K(3)(4)	0.77	30	9	36	-25	+15	+15	1800
125 V_{DC} AT +85 °C; 85 V_{DC} AT +125 °C										
1.7	C	136(1)175(2)0125C(3)(4)	7.81	1250	1	2	-16	+7	+8	415
3.6	C	136(1)365(2)0125C(3)(4)	4.98	600	1	2	-16	+7	+8	520
9	F	136(1)905(2)0125F(3)(4)	3.69	240	1	5	-16	+7	+8	755
14	F	136(1)146(2)0125F(3)(4)	2.85	167	1	7	-16	+7	+8	860
18	T	136(1)186(2)0125T(3)(4)	1.85	129	2	9	-16	+7	+8	1130
25	T	136(1)256(2)0125T(3)(4)	1.59	93	2	13	-16	+7	+8	1200
56	K	136(1)566(2)0125K(3)(4)	0.77	32	10	40	-25	+15	+15	1800

Notes

- Part number definitions:

(1) Model type:

- 136D - axial through-hole terminations
- 136J - SMD, outward L-leaded terminations
- 136L - SMD, inward L-leaded terminations
- 136P - SMD, low profile outward L-leaded terminations
- 136S - SMD, low profile inward L-leaded terminations

(2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %

(3) Style number:

- Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
- High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve

(4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX. RIPPLE 40 kHz I_{RMS} (mA)
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	AT		CHANGE (%) AT			
					+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C	
6 V_{DC} AT +85 °C; 4 V_{DC} AT +125 °C										
220	C	136(1)227(2)0006C(3)(4)	1.50	36	2	9	-64	+13	+16	1000
560	F	136(1)567(2)0006F(3)(4)	1.25	21	3	9	-77	+16	+20	1500
820	F	136(1)827(2)0006F(3)(4)	1.25	18	3	14	-88	+16	+20	1500
1200	T	136(1)128(2)0006T(3)(4)	0.75	18	5	18	-88	+20	+25	1900
1500	T	136(1)158(2)0006T(3)(4)	0.75	18	5	20	-90	+20	+25	1900
2200	K	136(1)228(2)0006K(3)(4)	0.50	13	6	24	-90	+25	+30	2300
8 V_{DC} AT +85 °C; 5 V_{DC} AT +125 °C										
180	C	136(1)187(2)0008C(3)(4)	1.50	45	2	9	-60	+13	+16	1000
680	F	136(1)687(2)0008F(3)(4)	1.25	22	3	14	-83	+16	+20	1500
1500	T	136(1)158(2)0008T(3)(4)	0.75	18	5	20	-90	+20	+25	1900
1800	K	136(1)188(2)0008K(3)(4)	0.50	14	7	25	-90	+25	+30	2300
10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C										
120	C	136(1)127(2)0010C(3)(4)	1.60	54	2	6	-40	+14	+16	900
150	C	136(1)157(2)0010C(3)(4)	1.50	54	2	9	-55	+13	+16	900
390	F	136(1)397(2)0010F(3)(4)	1.25	27	3	9	-66	+16	+20	1450
560	F	136(1)567(2)0010F(3)(4)	1.25	27	3	16	-77	+16	+20	1450
1200	T	136(1)128(2)0010T(3)(4)	0.75	18	5	20	-88	+20	+25	1850
1500	K	136(1)158(2)0010K(3)(4)	0.50	15	7	25	-88	+25	+30	2300
15 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C										
82	C	136(1)826(2)0015C(3)(4)	0.95	72	2	6	-35	+12	+16	900
100	C	136(1)107(2)0015C(3)(4)	0.95	72	2	9	-44	+13	+16	900
270	F	136(1)277(2)0015F(3)(4)	1.25	31	3	9	-62	+16	+15	1450
390	F	136(1)397(2)0015F(3)(4)	1.25	31	3	16	-66	+16	+20	1450
680	T	136(1)687(2)0015T(3)(4)	0.90	22	6	18	-74	+20	+25	1800
820	T	136(1)827(2)0015T(3)(4)	0.90	22	6	24	-77	+20	+25	1800
1000	K	136(1)108(2)0015K(3)(4)	0.60	17	8	32	-77	+25	+30	2330
25 V_{DC} AT +85 °C; 15 V_{DC} AT +125 °C										
47	C	136(1)476(2)0025C(3)(4)	2.60	100	2	6	-23	+12	+15	800
56	C	136(1)566(2)0025C(3)(4)	2.15	90	2	6	-25	+12	+15	850
68	C	136(1)686(2)0025C(3)(4)	2.15	90	2	9	-40	+12	+15	850
180	F	136(1)187(2)0025F(3)(4)	1.35	33	3	9	-54	+13	+15	1400
270	F	136(1)277(2)0025F(3)(4)	1.35	33	3	16	-62	+13	+16	1400
470	T	136(1)477(2)0025T(3)(4)	0.90	24	6	18	-65	+18	+25	1750
560	T	136(1)567(2)0025T(3)(4)	0.90	24	7	28	-72	+20	+25	1750
680	K	136(1)687(2)0025K(3)(4)	0.60	19	8	32	-72	+25	+30	2100

Note

- Part number definitions:

(1) Model type:

- 136D - axial through-hole terminations
- 136J - SMD, outward L-leded terminations
- 136L - SMD, inward L-leded terminations
- 136P - SMD, low profile outward L-leded terminations
- 136S - SMD, low profile inward L-leded terminations

(2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %

(3) Style number:

- Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
- High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve

(4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX.
			AT +25 °C	AT -55 °C	AT		CHANGE (%) AT			RIPPLE
			120 Hz	120 Hz	+25 °C	+85 °C	-55 °C	+85 °C	+125 °C	40 kHz
			(Ω)	(Ω)		+125 °C				I _{RMS}
										(mA)
30 V_{DC} AT +85 °C; 20 V_{DC} AT +125 °C										
47	C	136(1)476(2)0030C(3)(4)	2.60	100	2	6	-23	+12	+15	800
56	C	136(1)566(2)0030C(3)(4)	2.60	100	2	9	-38	+12	+15	800
150	F	136(1)157(2)0030F(3)(4)	1.25	36	3	9	-42	+13	+15	1200
220	F	136(1)227(2)0030F(3)(4)	1.25	36	3	16	-60	+13	+16	1200
390	T	136(1)397(2)0030T(3)(4)	0.90	25	6	18	-55	+18	+25	1500
470	T	136(1)477(2)0030T(3)(4)	0.90	25	8	32	-65	+20	+25	1500
560	K	136(1)567(2)0030K(3)(4)	0.65	20	9	36	-65	+25	+30	2000
35 V_{DC} AT +85 °C; 22 V_{DC} AT +125 °C										
39	C	136(1)396(2)0035C(3)(4)	2.05	61	2	6	-22	+12	+14	820
120	F	136(1)127(2)0035F(3)(4)	1.25	31	3	10	-40	+13	+15	1315
330	T	136(1)337(2)0035T(3)(4)	0.90	20	6	18	-50	+16	+25	1640
370	K	136(1)377(2)0035K(3)(4)	0.65	15	9	36	-60	+25	+30	2040
40 V_{DC} AT +85 °C; 25 V_{DC} AT +125 °C										
39	C	136(1)396(2)0040C(3)(4)	2.05	61	2	6	-22	+12	+14	820
50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C										
33	C	136(1)336(2)0050C(3)(4)	2.50	135	2	9	-29	+10	+12	700
100	F	136(1)107(2)0050F(3)(4)	1.40	49	4	12	-36	+13	+15	1200
120	F	136(1)127(2)0050F(3)(4)	1.25	49	4	24	-42	+12	+15	1200
270	T	136(1)277(2)0050T(3)(4)	1.00	30	8	32	-46	+20	+25	1450
330	K	136(1)337(2)0050K(3)(4)	0.75	30	9	36	-46	+25	+30	1900
60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C										
18	C	136(1)186(2)0060C(3)(4)	3.50	160	2	12	-20	+7	+8	700
27	C	136(1)276(2)0060C(3)(4)	2.51	144	3	12	-24	+10	+12	700
82	F	136(1)826(2)0060F(3)(4)	1.45	54	4	16	-30	+15	+15	1100
100	F	136(1)107(2)0060F(3)(4)	1.25	54	4	20	-36	+12	+15	1100
220	T	136(1)227(2)0060T(3)(4)	0.90	29	8	32	-40	+16	+20	1400
270	K	136(1)277(2)0060K(3)(4)	0.70	23	9	36	-45	+20	+25	1850
330	K	136(1)337(2)0060K(3)(4)	0.65	31	10	40	-72	+25	+25	1850
63 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C										
100	F	136(1)107(2)0063F(3)(4)	1.25	54	2	12	-36	+12	+15	1100
75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C										
12	C	136(1)126(2)0075C(3)(4)	2.55	157	3	12	-19	+10	+12	600
22	C	136(1)226(2)0075C(3)(4)	2.57	157	3	12	-19	+10	+12	600
68	F	136(1)686(2)0075F(3)(4)	1.50	63	4	16	-25	+12	+15	1000
82	F	136(1)826(2)0075F(3)(4)	1.23	63	4	24	-30	+12	+15	1000
180	T	136(1)187(2)0075T(3)(4)	0.90	30	9	36	-35	+16	+20	1300
220	K	136(1)227(2)0075K(3)(4)	1.12	24	10	40	-40	+20	+25	1800
300	K	136(1)307(2)0075K(3)(4)	0.90	32	12	48	-60	+22	+22	2000

Note

- Part number definitions:

(1) Model type:

- 136D - axial through-hole terminations
- 136J - SMD, outward L-leaded terminations
- 136L - SMD, inward L-leaded terminations
- 136P - SMD, low profile outward L-leaded terminations
- 136S - SMD, low profile inward L-leaded terminations

(2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %

(3) Style number:

- Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
- High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve

(4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



EXTENDED RATINGS										
CAPACITANCE (μ F)	CASE CODE	PART NUMBER (1)	MAX. ESR	MAX. IMP.	MAX. DCL (μ A)		MAX. CAPACITANCE			MAX. RIPPLE 40 kHz I_{RMS} (mA)
			AT +25 °C 120 Hz (Ω)	AT -55 °C 120 Hz (Ω)	AT		CHANGE (%) AT			
					+25 °C	+85 °C +125 °C	-55 °C	+85 °C	+125 °C	
100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C										
10	C	136(1)106(2)0100C(3)(4)	2.99	200	3	12	-17	+10	+12	800
39	F	136(1)396(2)0100F(3)(4)	1.77	80	5	24	-20	+12	+15	1300
56	T	136(1)566(2)0100T(3)(4)	1.22	50	5	20	-25	+12	+12	1400
68	T	136(1)686(2)0100T(3)(4)	1.11	40	10	40	-30	+14	+16	1600
120	K	136(1)127(2)0100K(3)(4)	1.38	30	12	48	-35	+15	+17	2000
125 V_{DC} AT +85 °C; 85 V_{DC} AT +125 °C										
6.8	C	136(1)685(2)0125C(3)(4)	5.86	300	3	12	-14	+10	+12	700
27	F	136(1)276(2)0125F(3)(4)	1.77	90	5	24	-18	+12	+15	1200
47	T	136(1)476(2)0125T(3)(4)	1.12	50	10	40	-26	+14	+16	1500
56	T	136(1)566(2)0125T(3)(4)	1.11	50	10	40	-26	+14	+16	1500
68	K	136(1)686(2)0125K(3)(4)	1.10	32	11	44	-28	+15	+16	1850
82	K	136(1)826(2)0125K(3)(4)	1.41	32	12	48	-30	+15	+17	1900

Note

- Part number definitions:
 - (1) Model type:
 - 136D - axial through-hole terminations
 - 136J - SMD, outward L-leaded terminations
 - 136L - SMD, inward L-leaded terminations
 - 136P - SMD, low profile outward L-leaded terminations
 - 136S - SMD, low profile inward L-leaded terminations
 - (2) Capacitance tolerance: X0 = 20 %, X9 = 10 %, X5 = 5 %
 - (3) Style number:
 - Standard temperature: 0 = no insulating sleeve, 2 = polyester insulation sleeve, 3 = high temperature film insulation;
 - High temperature: 6 = high temperature film insulation, 8 = no insulating sleeve
 - (4) Termination: blank = standard tin / lead, E3 = RoHS-compliant 100 % tin



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.