


Wet Tantalum Capacitors, Space Level, Established Reliability, DLA Drawing 20001


FEATURES

- Screened for space level applications
- Tantalum case, hermetically sealed, axial leaded
- Screened M39006/33 capacitors
 - Established failure rate
 - "H" or high shock and vibration rated
 - Enhanced 100 % or group A testing
 - Enhanced production lot testing - group B prior to shipment
- Stability
- Thermal shock
- 1000 h life at +85 °C
- Reverse voltage rating at +85 °C is 3 V_{DC} and at +125 °C is 2 V_{DC}

LINKS TO ADDITIONAL RESOURCES


CROSS REFERENCE		
DLA DRAWING	MIL SPECIFICATION	STYLE
DLA 20001	M39006/33	CLR93

Established Reliability "Space Level" Wet Tantalum Capacitors

In accordance with the DLA 20001 drawing, all parts are up-screened from "M" failure rate, "H" characteristic, MIL-PRF-39006/33 capacitors.

Parts are marked with the DLA 20001 drawing number and PIN (dash number).

For information on the exact performance of these capacitors, please refer to the latest issue of the DLA 20001 drawing and M39006/33 specification.

ORDERING INFORMATION	
20001- _____ DLA DRAWING NUMBER	XXXXH _____ PIN OR DASH NUMBER (see Standard Ratings table)

DIMENSIONS in inches [millimeters]				
CASE CODE	BASIC CASE		INSULATED CASE	E ± 0.250 [6.35]
	L ⁽¹⁾ + 0.031 [0.79] / - 0.016 [0.41]	D ± 0.016 [0.41]	D max.	
T1	0.453 [11.51]	0.188 [4.78]	0.219 [5.56]	1.500 [38.10]
T2	0.641 [16.28]	0.281 [7.14]	0.312 [7.92]	2.250 [57.15]
T3	0.766 [19.46]	0.375 [9.52]	0.406 [10.31]	2.250 [57.15]
T4	1.062 [26.97]	0.375 [9.52]	0.406 [10.31]	2.250 [57.15]

Note

(1) Length of basic case sleeving shall be as specified in MIL-PRF-39006



STANDARD RATINGS												
CAPACITANCE (μ F)	CASE CODE	CAP. TOL. (\pm %)	PIN FOR DLA 20001	MAX. DCL (μ A) AT		MAX. ESR AT +25 °C 120 Hz (Ω)	MAX. DF ⁽¹⁾ AT +25 °C 120 Hz (%)	MAX. IMP. AT -55 °C 120 Hz (Ω)	MAX. CAPACITANCE CHANGE (%) AT			MAX. RIPPLE CURRENT ⁽²⁾ AT +85 °C 40 kHz (mA _{RMS})
				+25 °C	+85 °C +125 °C				-55 °C	+85 °C	+125 °C	
50 V_{DC} AT +85 °C; 30 V_{DC} AT +125 °C												
68	T1	20	0021H	1	5	1.5	9.2	35	-25	8	15	1050
68	T1	10	0022H	1	5	1.5	9.2	35	-25	8	15	1050
220	T2	20	0023H	2	10	0.9	17.9	17.5	-50	8	15	1800
220	T2	10	0024H	2	10	0.9	17.9	17.5	-50	8	15	1800
470	T3	20	0027H	3	25	0.75	31.9	10	-50	8	15	2100
470	T3	10	0028H	3	25	0.75	31.9	10	-50	8	15	2100
680	T4	20	0029H	5	40	0.7	43.1	10	-58	10	20	2750
680	T4	10	0030H	5	40	0.7	43.1	10	-58	10	20	2750
60 V_{DC} AT +85 °C; 40 V_{DC} AT +125 °C												
47	T1	20	0031H	1	5	2	8.5	44	-25	8	12	1050
47	T1	10	0032H	1	5	2	8.5	44	-25	8	12	1050
150	T2	20	0033H	2	10	1.1	14.9	20	-40	8	15	1650
150	T2	10	0034H	2	10	1.1	14.9	20	-40	8	15	1650
390	T3	20	0037H	3	25	0.9	31.8	15	-60	8	15	2100
390	T3	10	0038H	3	25	0.9	31.8	15	-60	8	15	2100
560	T4	20	0039H	5	40	0.8	40.5	10	-58	8	15	2750
560	T4	10	0040H	5	40	0.8	40.5	10	-58	8	15	2750
75 V_{DC} AT +85 °C; 50 V_{DC} AT +125 °C												
33	T1	20	0041H	1	5	2.5	7.5	66	-25	5	9	1050
33	T1	10	0042H	1	5	2.5	7.5	66	-25	5	9	1050
110	T2	20	0043H	2	10	1.3	12.9	24	-35	6	10	1650
110	T2	10	0044H	2	10	1.3	12.9	24	-35	6	10	1650
330	T3	20	0047H	3	30	1.0	29.9	12	-45	6	10	2100
330	T3	10	0048H	3	30	1.0	29.9	12	-45	6	10	2100
470	T4	20	0049H	5	50	0.9	38.3	12	-55	8	12	2750
470	T4	10	0050H	5	50	0.9	38.3	12	-55	8	12	2750
100 V_{DC} AT +85 °C; 65 V_{DC} AT +125 °C												
15	T1	20	0051H	1	5	3.5	4.8	125	-18	3	10	1050
15	T1	10	0052H	1	5	3.5	4.8	125	-18	3	10	1050
68	T2	20	0053H	2	10	2.1	12.9	37	-30	4	12	1650
68	T2	10	0054H	2	10	2.1	12.9	37	-30	4	12	1650
150	T3	20	0057H	3	25	1.6	21.7	22	-35	6	12	2100
150	T3	10	0058H	3	25	1.6	21.7	22	-35	6	12	2100
220	T4	20	0059H	5	50	1.2	23.9	15	-40	6	12	2750
220	T4	10	0060H	5	50	1.2	23.9	15	-40	6	12	2750

Notes

- Letter "H" in the dash number indicates high vibration and shock requirements (i.e., 53.79 g's random vibration, 80 g's sinusoidal vibration, and 500 g's shock)
- (1) DF is calculated from ESR and is for reference only
- (2) For ripple current limits at various temperatures, voltages, and frequencies, see "Ripple Current" table



RIPPLE CURRENT MULTIPLIERS VS. FREQUENCY, TEMPERATURE, AND APPLIED PEAK VOLTAGE

FREQUENCY OF APPLIED RIPPLE CURRENT		120 Hz				800 Hz				1 kHz				10 kHz				40 kHz				100 kHz			
AMBIENT STILL AIR		TEMP °C				TEMP °C				TEMP °C				TEMP °C				TEMP °C				TEMP °C			
		≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125
% OF APPLIED VOLTAGE	100 %	0.60	0.39	-	-	0.71	0.43	-	-	0.72	0.46	-	-	0.88	0.55	-	-	1.0	0.63	-	-	1.1	0.69	-	-
	90 %	0.60	0.46	-	-	0.71	0.55	-	-	0.72	0.55	-	-	0.88	0.67	-	-	1.0	0.77	-	-	1.1	0.85	-	-
	80 %	0.60	0.52	0.35	-	0.71	0.62	0.42	-	0.72	0.62	0.42	-	0.88	0.76	0.52	-	1.0	0.87	0.59	-	1.1	0.96	0.65	-
	70 %	0.60	0.58	0.44	-	0.71	0.69	0.52	-	0.72	0.70	0.52	-	0.88	0.85	0.64	-	1.0	0.97	0.73	-	1.1	1.07	0.80	-
	66 2/3 %	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55	0.32	0.88	0.88	0.68	0.40	1.0	1.0	0.77	0.45	1.1	1.1	0.85	0.50

Notes

- At +125 °C the rated voltage of the capacitors decreases to 66 2/3 % of the +85 °C rated voltage
- The peak of the applied AC ripple voltage plus the applied DC voltage must not exceed the DC voltage rating of the capacitor either forward or reverse
- The ripple current listed represents a rating calculated using a maximum internal temperature rise (ΔT) of +50 °C at 40 kHz at +85 °C ambient with a maximum peak rated voltage of 66 2/3 % of the +85 °C peak voltage rating
- The maximum allowable internal temperature rise (ΔT) decreases linearly to a calculated +10 °C rise at +125 °C ambient
- The internal temperature rise is directly proportional to the equivalent series resistance of the capacitor and equivalent series resistance increases with decreasing frequency

GROUP A INSPECTION AND GROUP B INSPECTION PER DLA 20001

GROUP A INSPECTION		
TEST / INSPECTION	REQUIREMENT PARAGRAPH	SAMPLE PROCEDURE
SUBGROUP 1		
Thermal shock (10 cycles)	3.2	100 %
Constant voltage conditioning (168 h)	3.3	
DC leakage at +25 °C	3.1.9	
DC leakage at +85 °C	3.1.9	
Capacitance	3.1.7	
ESR	3.1.11	
Seal, condition C	3.4	
Seal, condition A or D	3.5	
SUBGROUP 2		
Mechanical examination (dimensions only)	3.1.1	See Table IV of DLA20001
SUBGROUP 3		
Solderability	3.6	5 samples, 0 failures
SUBGROUP 4		
Visual inspection	3.8g	13 samples, 0 failures
Materials	3.9	
Marking	3.10	
Workmanship	3.15	

GROUP B INSPECTION		
TEST / INSPECTION	REQUIREMENT PARAGRAPH	SAMPLE PROCEDURE
SUBGROUP 1		
Stability at low and high temperatures	3.7	13 samples, 0 failures
SUBGROUP 2		
Thermal shock (30 cycles)	3.2	10 samples, 0 failures
Life (1000 h at +85 °C)	3.8	
DC leakage at +25 °C	3.1.9	
DC leakage at +85 °C	3.1.9	
Capacitance	3.1.7	
ESR	3.1.11	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.