

Surface Mount Ceramic Chip Antennas for 5.0 GHz



VJ5120W500GXCMT chip antenna

The VJ5120W500T series are small form-factor, high-performance chip-antennas designed to be used in wireless, bluetooth and ISM band 5.0 GHz.

The VJ5120W500T series present an excellent performance (max. gain 2.9 dBi) with a low profile needed in most wireless applications.

DESCRIPTION

The VJ5120W500GXCMT ceramic chip antenna is a small form-factor, high-performance, chip-antenna designed for operation at 5.0 GHz. It allows manufacturers to design high quality products that do not bear the penalty of a large external antenna, and is designed to be assembled onto a PC board using a standard reflow process.

FEATURES

- Ultra small outline (3.1 mm x 1.6 mm x 0.6 mm)
- 50 Ω unbalanced tuning interface
- Omnidirectional
- Assembled onto a PCB in the standard reflow process
- Low profile for thin type terminal
- High stability in temperature / humidity changes
- High mechanical strength
- Wide operating temperature range (- 40 °C to + 85 °C)
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- IEEE 802.11a standard applications
- ISM Band 5.0 GHz wireless applications

ELECTRICAL SPECIFICATIONS

Operating temperature: - 40 °C to + 85 °C

Frequency range (transmission / reception): 4.9 GHz to 5.85 GHz

Note

- Electrical characteristics at + 25 °C unless otherwise specified.

QUICK REFERENCE DATA

SERIES	FREQUENCY (MHz)	MAX. GAIN (dBi)	AVERAGE GAIN (dBi)	BANDWIDTH (- 10 dB) (MHz)	BANDWIDTH (- 3 dB) (MHz)
VJ5120W500GXCMT	5000	+ 2.9	+ 0	1200	2000


CHIP ANTENNA PERFORMANCE

NOMINAL FREQUENCY (MHz)	NOMINAL IMPEDANCE (Ω)	5.0 GHz PEAK GAIN (dBi)	5.0 GHz AVERAGE GAIN (dBi)	5.0 GHz REFLECTED POWER LOSS	5.0 GHz INSERTION POWER LOSS	- 3 dB BANDWIDTH 5.0 GHz	- 3 dB REFLECTED POWER LOSS	- 10 dB BANDWIDTH 5.0 GHz	- 10 dB REFLECTED POWER LOSS
5000	50	+ 0	+ 2.9	< - 15 dB	< 4 %	2000	50 %	1200	10 %
				< 4 %	< 0.14 dB		3 dB		0.46 dB


FOOTPRINT, MECHANICAL, AND PCB DIMENSIONS

The antenna footprint and mechanical dimensions are presented in figure 7. Optimal tuning is adjusted according to PCB layout.


FIGURE	SYMBOL	DIMENSION (mm)
	L	3.10 ± 0.20
	W	1.60 ± 0.20
	T	0.60 ± 0.10
	A	0.25 ± 0.20



Empty Space 6.5 mm x 6.5 mm




Land Pattern (dimensions in mm)



Antenna on Test Board (thickness 0.8 mm)



Antenna S11 on Test Board



Antenna VSWR on Test Board

RADIATION PATTERN



Radiation pattern and gain were dependent on measurement board design. The specification of VJ5120W500GXCMT antenna was measured based on the PCB size and installation position as shown in the below figure test board.



	VERTICAL	HORIZONTAL
<p>Y - Z Plane</p> <p>Average Gain = - 0.75 dBi</p>	<p>Peak Gain = - 0.55 dBi, Average Gain = - 4.9 dBi</p>	<p>Peak Gain = + 0.73 dBi, Average Gain = - 2.86 dBi</p>
<p>X - Z Plane</p> <p>Average Gain = + 1.23 dBi</p>	<p>Peak Gain = + 2.86 dBi, Average Gain = + 0.86 dBi</p>	<p>Peak Gain = - 2.49 dBi, Average Gain = - 9.60 dBi</p>
<p>X - Y Plane</p> <p>Average Gain = - 0.74 dBi</p>	<p>Peak Gain = - 7.02 dBi, Average Gain = - 11.78 dBi</p>	<p>Peak Gain = + 2.3 dBi, Average Gain = - 1.1 dBi</p>

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in figure 2.


PACKAGING


PLASTIC TAPE SPECIFICATIONS (Dimensions in mm)									
A_0	B_0	$\varnothing D$	T	W	E	F	P_0	P_1	P_2
1.95 ± 0.10	3.45 ± 0.10	1.55 ± 0.05	0.75 ± 0.10	8.0 ± 0.30	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10

ORDERING INFORMATION	VISHAY MATERIAL	PACKAGING QUANTITY
VJ5120W500 Chip Antenna	VJ5120W500GXCMT	2000 pieces



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.