













# CAPABILITIES AND CUSTOM OPTIONS

## HIGH VOLTAGE HOCKEY PUCKS

Standard	Special Designs, Coated	Special Designs, Uncoated
<b>Series With Screw Terminal</b>		
 <p><b>715C..KT...</b></p> <ul style="list-style-type: none"> <li>- class 1 ceramic N4700</li> <li>- low dissipation factor</li> <li>- terminal versions: 8-32NC-2B, metric M4 or metric M5</li> <li>- epoxy coated</li> </ul>  <p><b>715C..DK...</b></p> <ul style="list-style-type: none"> <li>- class 2 ceramic Y5U</li> <li>- compact design</li> <li>- higher capacitance values</li> <li>- terminal versions 8-32NC-2B, metric M4 or metric M5</li> <li>- epoxy coated</li> </ul>	 <p><b>715C...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers</li> <li>- different electrical or mechanical parameters</li> <li>- different epoxy material</li> <li>- different ceramic material (e.g. N3300)</li> </ul> 	 <p><b>720C...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers with terminals</li> </ul>  <p><b>722C...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers without terminals</li> </ul>  <p><b>HPD...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers with special terminals</li> </ul>
<b>Series With Lead Wires</b>		
 <p><b>660R...</b></p> <ul style="list-style-type: none"> <li>- RoHS-compliant leads and soldering</li> </ul> <p><b>660C...</b></p> <ul style="list-style-type: none"> <li>- non RoHS-compliant</li> <li>- lower soldering temperatures</li> </ul>	 <p><b>660...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers</li> <li>- different electrical or mechanical parameters</li> <li>- different epoxy material</li> <li>- different ceramic material (e.g. N3300)</li> </ul>	 <p><b>SDRQ...</b></p> <ul style="list-style-type: none"> <li>- customized part numbers with leads</li> </ul>