




The DNA of tech.™

MULTILAYER CERAMIC CHIP CAPACITORS

VJ Safety-Certified Capacitors, C0G (NP0) and X7R

Surface-Mount Multilayer Ceramic Chip Capacitors for Safety-Certified Applications



KEY BENEFITS

- Safety-certified surface-mount (SMD) capacitors
- Approved per IEC 60384-14
- C0G (NP0) and X7R dielectrics in two sizes: 2008 and 2220
- AEC-Q200 qualified available PPAP
- X1 / Y2 and X2 classifications rated for 250 V_{AC}
- Flexible termination “W” for improved bending capability performance
- Wet build process
- Reliable noble metal electrode (NME) system

APPLICATIONS

- Power supplies
- EV charging systems
- AC equipment and appliances
- Lightning strike and voltage surge protection
- EMI and AC line filtering
- Isolators

RESOURCES

- Datasheet: VJ Safety-Certified Capacitors - www.vishay.com/ppg?45255
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912
- For technical questions contact mlcc@vishay.com



RoHS
COMPLIANT

HALOGEN
FREE
Available

GREEN
(5-2008)



The DNA of tech.™

MULTILAYER CERAMIC CHIP CAPACITORS

VJ Safety-Certified Capacitors, C0G (NP0) and X7R

Surface-Mount Multilayer Ceramic Chip Capacitors for Safety-Certified Applications

ELECTRICAL SPECIFICATIONS

Note

- Electrical characteristics at +25 °C unless otherwise specified

Operating Temperature: -55 °C to +125 °C

Capacitance Range X1 / Y2 (1):

C0G (NP0): 10 pF to 1.0 nF

X7R: 100 pF to 4.7 nF

Capacitance Range X2 (1):

C0G (NP0): 10 pF to 390 pF

X7R: 100 pF to 12 nF

Voltage Range: 250 V_{AC}

Temperature Coefficient of Capacitance (TCC):

C0G (NP0): 0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C

X7R: ± 15 % from -55 °C to +125 °C, with 0 V_{DC} applied

Dissipation Factor (DF) (1):

C0G (NP0): 0.1 % maximum

X7R: 2.5 % maximum

Insulating Resistance:

at +25 °C 100 000 MΩ min. or 1000 ΩF whichever is less

at +125 °C 10 000 MΩ min. or 100 ΩF whichever is less

Note

(1) Test conditions per IEC 60384-14:

C0G (NP0): 1.0 V_{RMS} at 1 MHz

X7R: 1.0 V_{RMS} at 1 kHz

Aging Rate:

C0G (NP0): 0 % maximum per decade

X7R: 1 % maximum per decade

Voltage Proof Test:

X1 / Y2: min. 1500 V_{AC}

X2: min. 1075 V_{DC}

Peak Impulse Voltage:

X1 / Y2: 5000 V

X2: 2500 V

Voltage Rating DC:

X1 / Y2: 2000 V_{DC}

X2: 1500 V_{DC}

Climatic Category According to EN 60068-1:

55/125/21

SELECTION CHART				
DIELECTRIC		C0G (NP0) (X1 / Y2)		C0G (NP0) (X2)
STYLE		VJ2008 (1)	VJ2220 (1)	VJ2008 (1)
CASE CODE		2008	2220	2008
VOLTAGE (V _{AC})		250	250	250
VOLTAGE CODE		U	U	U
CAP. CODE	CAP.			
100	10 pF	•		•
120	12 pF	•		•
150	15 pF	•		•
180	18 pF	•		•
220	22 pF	•		•
270	27 pF	•		•
330	33 pF	•		•
390	39 pF	•		•
470	47 pF	•	•	•
560	56 pF	•	•	•
680	68 pF	•	•	•
820	82 pF	•	•	•
101	100 pF	•	•	•
121	120 pF	•	•	•
151	150 pF	•	•	•
181	180 pF	•	•	•
221	220 pF	•	•	•
271	270 pF		•	•
331	330 pF		•	•
391	390 pF		•	•
471	470 pF		•	
561	560 pF		•	
681	680 pF		•	
821	820 pF		•	
102	1.0 nF		•	
122	1.2 nF			
152	1.5 nF			
182	1.8 nF			

Note

(1) See soldering recommendations within this data book, or visit www.vishay.com/doc?45034



The DNA of tech.™

MULTILAYER CERAMIC CHIP CAPACITORS

VJ Safety-Certified Capacitors, C0G (NP0) and X7R

Surface-Mount Multilayer Ceramic Chip Capacitors for Safety-Certified Applications

SELECTION CHART					
DIELECTRIC		X7R (X1 / Y2)		X7R (X2)	
STYLE		VJ2008 ⁽¹⁾	VJ2220 ⁽¹⁾	VJ2008 ⁽¹⁾	VJ2220 ⁽¹⁾
CASE CODE		2008	2220	2008	2220
VOLTAGE (V _{AC})		250	250	250	250
VOLTAGE CODE		U	U	U	U
CAP. CODE	CAP.				
100	10 pF				
220	22 pF				
330	33 pF				
470	47 pF				
560	56 pF				
680	68 pF				
820	82 pF				
101	100 pF	•		•	
121	120 pF	•		•	
151	150 pF	•		•	
181	180 pF	•		•	
221	220 pF	•		•	
271	270 pF	•	•	•	•
331	330 pF	•	•	•	•
391	390 pF	•	•	•	•
471	470 pF	•	•	•	•
561	560 pF	•	•	•	•
681	680 pF	•	•	•	•
821	820 pF	•	•	•	•
102	1.0 nF	•	•	•	•
122	1.2 nF		•	•	•
152	1.5 nF		•	•	•
182	1.8 nF		•	•	•
222	2.2 nF		•	•	•
272	2.7 nF		•	•	•
332	3.3 nF		•	•	•
392	3.9 nF		•	•	•
472	4.7 nF		•	•	•
562	5.6 nF				•
682	6.8 nF				•
822	8.2 nF				•
103	10 nF				•
123	12 nF				•
153	15 nF				•

Note

⁽¹⁾ See soldering recommendations within this data book, or visit www.vishay.com/doc?45034

ORDERING INFORMATION								
VJ2008	Y	102	K	X	U	S	T	### ⁽²⁾
CASE CODE	DIELECTRIC	CAPACITANCE NOMINAL CODE	CAPACITANCE TOLERANCE	TERMINATION	AC VOLTAGE RATING	MARKING	PACKAGING	PROCESS CODE
2008 2220	A = C0G (NP0) Y = X7R	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. Examples: 101 = 100 pF 102 = 1000 pF 103 = 10 000 pF	C0G (NP0): J = ± 5 % K = ± 10 % X7R: K = ± 10 % M = ± 20 %	X = Ni barrier 100 % matte tin plate finish W = Ni barrier with flexible layer, 100 % matte tin plate finish ⁽¹⁾	U = 250 V _{AC}	S = marked (see Part Marking table below)	T = 7" reel / plastic tape	X1 = X1 / Y2 X2 = X2 Vishay automotive grade per customer request, add "A": X1A = X1 / Y2 X2A = X2

Notes

- Detail ratings see "Selection Chart"

⁽¹⁾ "W" flexible termination under qualification

⁽²⁾ Process code must be added to control products and requirements



The DNA of tech.™

MULTILAYER CERAMIC CHIP CAPACITORS

VJ Safety-Certified Capacitors, C0G (NP0) and X7R

Surface-Mount Multilayer Ceramic Chip Capacitors for Safety-Certified Applications

APPROVALS FOR C0G (NP0)				
VDE approval mark (update 2020-02-20):				
X1 / Y2-capacitor:	40036706	10 pF to 1000 pF	250 V _{AC}	
X2-capacitor:	40036706	10 pF to 470 pF	250 V _{AC}	
DIN EN 60384-14 (VDE 0565-1-1):2014-04; EN 60384-14:2013-08; IEC 60384-14 (ed.4)				
CAN / cCSAus approval mark (update 2020-05-05):				
X1 / Y2-capacitor:	70001064	10 pF to 1000 pF	250 V~	
X2-capacitor:	70001064	10 pF to 470 pF	250 V~	
CAN / CSA-E60384-14:14 and ANSI / UL 60384-14-2017				

APPROVALS FOR X7R				
VDE approval mark (update 2020-02-20):				
X1 / Y2-capacitor:	40037440	82 pF to 4700 pF	250 V _{AC}	
X2-capacitor:	40037440	82 pF to 12 000 pF	250 V _{AC}	
DIN EN 60384-14 (VDE 0565-1-1):2014-04; EN 60384-14:2013-08; IEC 60384-14 (ed.4)				
CSA / cCSAus approval mark (update 2020-05-05):				
X1 / Y2-capacitor:	70001064	82 pF to 4700 pF	250 V~	
X2-capacitor:	70001064	82 pF to 12 000 pF	250 V~	
CAN / CSA-E60384-14:14 and ANSI / UL 60384-14-2017				

PART MARKING		
MARKING	1 ST DIGIT MANUFACTURER	2 ND DIGIT DIELECTRIC AND RATING
VC	V = Vishay	C = C0G (NP0), X1 / Y2 - "X" termination option
VT		T = C0G (NP0), X2 - "X" termination option
VD		D = C0G (NP0), X1 / Y2 - "W" termination option
VU		U = C0G (NP0), X2 - "W" termination option
VA		A = X7R, X1 / Y2 - "X" termination option
VM		M = X7R, X2 - "X" termination option
VB		B = X7R, X1 / Y2 - "W" termination option
VN		N = X7R, X2 - "W" termination option



The DNA of tech.™

MULTILAYER CERAMIC CHIP CAPACITORS

VJ Safety-Certified Capacitors, C0G (NP0) and X7R

Surface-Mount Multilayer Ceramic Chip Capacitors for Safety-Certified Applications

DIMENSIONS FOR "X" TERMINATION OPTION in inches (millimeters)						
CASE CODE	PART ORDERING NUMBER	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATION (P)	
					MINIMUM	MAXIMUM
2008	VJ2008	0.200 ± 0.010 (5.08 ± 0.25)	0.080 ± 0.010 (2.03 ± 0.25)	0.086 (2.18)	0.010 (0.25)	0.030 (0.76)
2220	VJ2220	0.220 ± 0.008 (5.59 ± 0.20)	0.200 ± 0.010 (5.08 ± 0.25)	0.086 (2.18)	0.010 (0.25)	0.030 (0.76)

DIMENSIONS FOR "W" TERMINATION OPTION in inches (millimeters)						
CASE CODE	PART ORDERING NUMBER	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATION (P)	
					MINIMUM	MAXIMUM
2008	VJ2008	0.200 - 0.010 / + 0.020 (5.08 - 0.25 / + 0.50)	0.080 ± 0.010 (2.03 ± 0.25)	0.086 (2.18)	0.010 (0.25)	0.030 (0.76)
2220 C0G (NP0)	VJ2220A	0.220 - 0.008 / + 0.018 (5.59 - 0.20 / + 0.45)	0.200 ± 0.010 (5.08 ± 0.25)	0.086 (2.18)	0.010 (0.25)	0.030 (0.76)
2220 X7R	VJ2220Y	0.220 - 0.008 / + 0.018 (5.59 - 0.20 / + 0.45)	0.200 ± 0.010 (5.08 ± 0.25)	0.105 (2.65)	0.010 (0.25)	0.030 (0.76)

Note

- "W" flexible termination under qualification

PACKAGING QUANTITIES ⁽¹⁾		
CASE CODE	TAPE SIZE	7" REEL QUANTITIES
		PACKAGING CODE "T"
2008	12 mm	2000
2220	12 mm	1000

Note

⁽¹⁾ Reference: EIA standard RS481 - "Taping of Surface Mount Components for Automatic Placement"