



The DNA of tech.®

3000 W PAR® and TRANSZORB® TVS in DFN6546A Package

Unidirectional and Bidirectional Devices Featuring a Low 0.88 mm Profile and Wettable Flanks




ADVANTAGE

Save space and provide excellent clamping capability up to 137 V.

KEY PRODUCT FEATURES

- ✓ Peak pulse power of 3000 W (10/1000 µs)
- ✓ Compact footprint and extremely low height (6.5 mm x 4.6 mm x 0.88 mm)
- ✓ AEC-Q101 qualification (T3KNxxA and T3KNxxCA)
- ✓ LL15i Industrial Reliability Qualification (3KDFNxxA and 3KDFNxxCA)
- ✓ High temperature operation up to +185 °C
- ✓ Ideal for automated placement



RESOURCES



Order Samples
T3KNxxA and T3KNxxCA



Order Samples
3KDFNxxA and 3KDFNxxCA



Product Page
T3KNxxA and T3KNxxCA



Product Page
3KDFNxxA and 3KDFNxxCA

Americas



Contact Us

Asia



Contact Us

Europe



Contact Us

MARKETS AND APPLICATIONS



CONNECTIVITY

- Telecom mobile infrastructure



CONSUMER

- Entertainment
- Healthcare



MOBILITY

- Automotive
- Automotive intelligence (smart vehicle) and electrification (e-Powertrain)



ENERGY SECTOR

- Energy generation and exploration



INDUSTRIAL

- Automation and infrastructure
- Drives and tools



COMPUTER

- Computer



AMS

- Avionics, space, military



ADDITIONAL BENEFITS

- The wettable flanks of the DFN6546A package allow for automatic optical inspection (AOI), eliminating the need for an X-ray inspection
- Footprint-compatible with the SMPC (TO-277A) package, the T3KNxxA, T3KNxxCA, 3KDFNxxA, and 3KDFNxxCA series offer twice the power dissipation with a 20 % lower profile. Compared to devices in the SMC (DO-214AB), they offer the same power dissipation while reducing volume by 76 %

DEVICE SPECIFICATION

Series	T3KN12A thru T3KN24A	3KDFN12A thru 3KDFN24A	T3KN12CA thru T3KN100CA	3KDFN12CA thru 3KDFN100CA
Power dissipation (W)	3000			
Breakdown voltage (V)	12 to 24		12 to 100	
Stand-off voltage (V)	10.2 to 20.5		10.2 to 85.5	
Max. clamping voltage (V)	16.7 to 33.2		16.7 to 137	
T _J max. (°C)	185	175	185	175
Polarity	Unidirectional		Bidirectional	
Circuit Configuration	Single			
AEC-Q101	Yes	No	Yes	No