



HIGH VIBRATION ALUMINUM CAPACITORS

FOR HARSH OPERATING CONDITIONS

LEAD (Pb)-FREE
SOLDERING
ACCORDING TO
JEDEC® J-STD-020



AEC-Q200
QUALIFIED
WITH PPAP
AVAILABLE

HIGH VIBRATION

<u>250 RMI-V at 105 °C</u>	<u>250 CRZ-V at 105 °C</u>
<u>246 RTI-V at 125 °C</u>	<u>246 CTI-V at 125 °C</u>
<u>260 RLA-V at 150 °C</u>	<u>260 CLA-V at 150 °C</u>

Up to 50 g




FEATURES

- Up to 8200 µF
- Up to 100 V
- Up to 2000 h / 150 °C

CASE SIZES (mm)

- SMD 16 x 16 up to 18 x 21
- Radial 16 x 20 up to 18 x 40



APPLICATIONS

INDUSTRIAL



AUTOMATION



CONTROL UNITS



MACHINERY




MOTOR DRIVES

AUTOMOTIVE



UNDER THE HOOD



CHASSIS



POWER TRAINS