




RESISTORS FOR SPACE APPLICATIONS

Vishay Sfernice



Overview of Space Qualified Products from Vishay Sfernice



SPACE APPLICATIONS

Components used in aerospace equipment are designed to function reliably when subjected to extremely hot and cold temperatures, intense vibration, and other environmental stresses. Vishay Sfernice has been involved in this market since the early 1980s, beginning with space-level qualifications for its metal film, wirewound, and SIL products. With the growing demand for miniaturization, Vishay Sfernice SMD products have been qualified for space applications since 2002.

In 2009, Vishay Sfernice became the first manufacturer of passive components to hold the ESCC/QML qualification (ESCC Technology Flow Qualified Manufacturer) granted by the European Space Agency (ESA). At Vishay Sfernice, our goal is to offer the widest range of qualified or SCD (customer source control drawing) products and thus to serve as a one-stop-shop for our space customers.

RESOURCES

- For technical questions contact sferthinfilm@vishay.com

Resistors - Qualified for Space Applications

One of the World's Largest Manufacturers of
Discrete Semiconductors and Passive Components





RESISTORS FOR SPACE APPLICATIONS

Vishay Sfernice




Resistors - Qualified for Space Applications

Qualified Products

PHR

Key Features and Benefits


- Space level ESA qualified: ESCC4001/023
- Thin film technology
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: 0603 to 2010 (0402 qualification ongoing)
- Wide ohmic range: 10 Ω to 3 MΩ (depending on size)
- Tight tolerance: down to 0.01 %
- Tight temperature coefficient: down to 5 ppm/°C (- 55 °C; + 155 °C)
- Load life stability: 0.15 % after 2000 h at 70 °C at nominal power (0.02 % typical)



PFRR

Key Features and Benefits

- Established reliability: R failure rate (0.01 %/1000 h)
- Thin film technology
- Operating temperature range - 55 °C; + 155 °C
- ESA qualified: ESCC4001/023
- Various sizes: 0603 to 2010 (0402 qualification ongoing)
- Wide ohmic range: 100 Ω to 3.01 MΩ (depending on size)
- Tight tolerance: down to 0.05 %
- Tight temperature coefficient: down to 10 ppm/°C (- 55 °C; + 155 °C)
- Load life stability: 0.25 % after 8000 h at 70 °C at nominal power (0.05 % typical)
- The industry's only SMD product with an official space qualification and performance as tight as 0.05 % / 10 ppm



PRAHR / CNWHR

Key Features and Benefits


- Space level ESA qualified: ESCC4001/025
- Thin film technology
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: PRAHR100, PARHR135, PRAHR182 (PRAHR070 ongoing)
- Wide ohmic range 100 Ω to 1 MΩ (depending on size)
- Tight tolerances: 0.1 % absolute, 0.05 % ratio (tighter on request)
- Tight temperature coefficient: 10 ppm/°C (- 55 °C; + 155 °C) absolute, 3 ppm/°C ratio
- Same ohmic value (any value) or different ohmic values in same network: CNWHR
- Load life stability: 0.1 % after 1000 h at 70 °C at nominal power, 0.02 % on the ratio



CHPHR

Key Features and Benefits

- Space level ESA qualified: ESCC4001/026
- Thick film technology
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: 0603 to 2512
- Wide ohmic range: 1 Ω to 10 MΩ
- Load life stability: 1 % after 1000 h at 70 °C at nominal power
- Tin/lead or gold terminations





RESISTORS FOR SPACE APPLICATIONS

Vishay Sfernice




Resistors - Qualified for Space Applications

Products with Ongoing Qualification

LHR

Key Features and Benefits


- Space level ESA qualification ongoing
- Thin film technology
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: 0603 to 2010 (2512 under development)
- Ohmic range 0.1 Ω to 9.99 Ω
- Load life stability: 0.5 % after 2000 h at 70 °C at nominal power
- Temperature coefficient: 50 ppm/°C to 300 ppm/°C (depending on ohmic value)



PZHR

Key Features and Benefits

- Space level ESA qualification ongoing
- Strap: 0 Ω
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: 0603 to 2512
- Conform to MIL-PRF-32159




Products Available Under Customer Specification

Die Chips, Current Sensors and Networks

Key Features and Benefits

- Thin film technology
- Nickel chromium, tantalum nitride or chromium silicium depending on performance needed
- Custom networks available
- Operating temperature range - 55 °C; + 155 °C
- Various sizes: 20 mil x 20 mil to 67 mil x 134 mil
- Wide ohmic range 0.05 Ω to 5 M Ω (depending on size)
- Tight tolerance: down to 0.01 %
- Tight temperature coefficient: down to 5 ppm/°C (- 55 °C; + 155 °C)
- Load life stability: 0.05 % after 2000 h at 70 °C typical





RESISTORS FOR SPACE APPLICATIONS

Vishay Sfernice



Resistors - Qualified for Space Applications

WORLDWIDE SALES CONTACTS

THE AMERICAS

UNITED STATES

VISHAY AMERICAS
ONE GREENWICH PLACE
SHELTON, CT 06484
UNITED STATES
PH: +1-402-563-6866
FAX: +1-402-563-6296

ASIA

SINGAPORE

VISHAY INTERTECHNOLOGY ASIA PTE LTD.
37A TAMPINES STREET 92 #07-00
SINGAPORE 528886
PH: +65-6788-6668
FAX: +65-6788-0988

P.R. CHINA

VISHAY CHINA CO., LTD.
15D, SUN TONG INFOPORT PLAZA
55 HUAI HAI WEST ROAD
SHANGHAI 200030
P.R. CHINA
PH: +86-21-5258 5000
FAX: +86-21-5258 7979

JAPAN

VISHAY JAPAN CO., LTD.
SHIBUYA PRESTIGE BLDG. 4F
3-12-22, SHIBUYA
SHIBUYA-KU
TOKYO 150-0002
JAPAN
PH: +81-3-5466-7150
FAX: +81-3-5466-7160

EUROPE

GERMANY

VISHAY ELECTRONIC GMBH
DR.-FELIX-ZANDMAN-PLATZ 1
95100 SELB
GERMANY
PH: +49-9287-71-0
FAX: +49-9287-70435

FRANCE

VISHAY S.A.
199, BD DE LA MADELEINE
06003 NICE, CEDEX 1
FRANCE
PH: +33-4-9337-2727
FAX: +33-4-9337-2726

UNITED KINGDOM

VISHAY LTD.
SUITE 6C, TOWER HOUSE
ST. CATHERINE'S COURT
SUNDERLAND ENTERPRISE PARK
SUNDERLAND SR5 3XJ
UNITED KINGDOM
PH: +44-191-516-8584
FAX: +44-191-549-9556