



Surface-Mount and Axial-Lead Inductors



SURFACE-MOUNT INDUCTORS

Multilayer Ferrite Beads/Inductors: ILB, ILBB, ILSB

Film Inductors: FC

Wirewound Inductors: IMC, ISC

Power Inductors: IHSM, IHLP, IDC, IDCS, IDCP

Transformer: LPE, LPT

AXIAL-LEAD INDUCTORS

TJ, IM, IMS, IHD, IHA

Surface-mount and axial-lead inductors from Vishay are available in a wide range of sizes and electrical specifications making them ideal for use in disk drives, telecommunications, instrumentation, medical equipment, and automotive systems. Vishay manufactures an inductor for every design problem from EMI/RFI suppression and impedance matching to band pass filters.

RESOURCES

- For more information on surface-mount inductors, visit <http://www.vishay.com/inductors>
- For more information on axial-lead inductors, visit <http://www.vishay.com/inductors/axial-leaded/>
- For technical questions contact magnetics@vishay.com

One of the World's Largest Manufacturers of
Discrete Semiconductors and Passive Components














MAGNETICS

Inductors

Inductors - A Solution for Every Design Problem









Product	Characteristics	Case Size	Value Range	Rated Current (mA)
ILB 	Multilayer shield beads, ideal for EMI and RFI suppression (High current beads from 0603 to 1812 are also available)	0402 0603 0805 1206 1210 1806 1812	20 Ω to 600 Ω 10 Ω to 2000 Ω 7 Ω to 2200 Ω 19 Ω to 2000 Ω 31 Ω to 90 Ω 80 Ω to 150 Ω 70 Ω to 120 Ω	200 to 300 50 to 500 80 to 600 100 to 500 400 200 to 400 200
ILSB 	Multilayer, ferrite, shielded inductor	0603 0805 1206	.047 μ H to 10 μ H .047 μ H to 33 μ H .047 μ H to 33 μ H	15 to 50 5 to 300 5 to 300
IMC 	High frequency laser spiral technology, excellent size-to-inductance-range ratio	0402 0603	1 nH to 100 nH 1 nH to 220 nH	90 to 400 70 to 500
IMC 	High frequency wirewound technology, moisture resistant, excellent size-to-inductance-range ratio	0805-01 1008 1210 1812	2.2 nH to 10 000 nH 3.3 nH to 47 000 nH .01 μ H to 220 μ H .01 μ H to 1000 μ H	80 to 800 45 to 1000 50 to 734 30 to 450
ISC 	Molded, shielded, wirewound technology, moisture resistant, excellent size-to-inductance-range ratio	1210 1812	.01 μ H to 100 μ H .1 μ H to 1000 μ H	80 to 810 66 to 552
IHSM 	High current, wirewound, surface mount, flame-retardant encapsulated body	3825 4825 5832 7832	1 μ H to 1000 μ H 1 μ H to 1000 μ H 1 μ H to 4700 μ H 1 μ H to 18 000 μ H	160 to 5110 240 to 8600 140 to 9000 110 to 9000
IHLP 	High current, low profile inductor	1616AB-01 1616AB-11 1616BZ-01 1616BZ-11	.047 μ H to 1.0 μ H .047 μ H to 2.2 μ H .1 μ H to 2.2 μ H .1 μ H to 4.7 μ H	4000 to 13 000 2750 to 15 000 2850 to 11 000 2000 to 12 000
IHLP 	High current, low profile inductor	2525AH-01 2525BD-01 2525CZ-01 2525CZ-11	.1 μ H to 4.7 μ H .1 μ H to 10 μ H .1 μ H to 10 μ H 1.0 μ H to 22 μ H	3000 to 18 000 2500 to 30 000 3000 to 32 500 2900 to 12 500
IHLP 	High current, low profile inductor	4040DZ-01 4040DZ-11	0.19 μ H to 10 μ H 0.19 μ H to 100 μ H	6800 to 40 000 2500 to 40 000
IHLP 	High current, low profile inductor	5050CE-01 5050EZ-01 5050FD-01	.1 μ H to 10 μ H .1 μ H to 10 μ H .1 μ H to 10 μ H	7000 to 43 000 9000 to 55 000 10 000 to 60 000
IDC 	High current, surface mount inductor	2512 5020 7328	1 μ H to 1000 μ H 1 μ H to 1000 μ H 1 μ H to 1000 μ H	70 to 2900 300 to 6800 560 to 8600



MAGNETICS

Inductors

Inductors - A Solution for Every Design Problem

Product	Characteristics	Case Size	Value Range	Rated Current (mA)
IDCS 	High current, shielded, surface mount inductor	2512 5020 7328	1 μ H to 10 000 μ H 1 μ H to 390 μ H 10 μ H to 1000 μ H	20 to 3000 330 to 5000 530 to 3900
IDCP 	High current, surface mount inductor	1813 2218 3020 3114 3722 3916	1 μ H to 68 μ H 10 μ H to 220 μ H 10 μ H to 470 μ H 10 μ H to 330 μ H 10 μ H to 20 μ H 10 μ H to 560 μ H	460 to 3800 350 to 1440 340 to 2300 280 to 1440 240 to 2600 320 to 2380
LPT 	Low profile surface mount, toroidal core, 2 separate windings, 4 terminals, 4545: .450" diameter 3535: .350" diameter	3535 4545	1 μ H to 330 μ H 1 μ H to 330 μ H	270 to 6450 430 to 7540
LPE 	High current, surface mount, gapped and ungapped, ferrite core, 18 package sizes, solvent resistant, above board height: .205" [5.2] to .335" [8.5] transformers and inductors	3525 4841 5047 6562 6855	10 μ H to 3900 μ H 10 μ H to 39 000 μ H 10 μ H to 68 000 μ H 10 μ H to 330 000 μ H 10 μ H to 150 000 μ H	60 to 1010 80 to 2030 70 to 2290 60 to 3090 60 to 3210
TJ 	High current, vertical mount reduces PC board size, toroid design decreases EMI, 7 sizes, current ratings up to 20 Amps		1.2 μ H to 5600 μ H	500 to 20 000
IM 	Standard and military models, axial leads, flameproof, molded epoxy coating	Standard	.10 μ H to 10 000 μ H	28 to 3600
IMS 	Standard and military models. Axial leads, shielded, molded epoxy encapsulation, flameproof, moisture proof	Standard	.10 μ H to 100 000 μ H	11 to 2900
IHD 	High current, axial leads, polyolefin sleeve, current ratings up to 5 Amps	IHD-1 IHD-3	1 μ H to 18 000 μ H 3.9 μ H to 100 000 μ H	80 to 5300 70 to 4000
IHA 	High current, axial leads, polyolefin sleeve, flame-retardant, current ratings up to 9 Amps		50 μ H to 1000 μ H	1400 to 9300



WORLDWIDE SALES CONTACTS

THE AMERICAS

UNITED STATES

VISHAY AMERICAS
ONE GREENWICH PLACE
SHELTON, CT 06484
UNITED STATES
PH: +1-402-563-6866
FAX: +1-402-563-6296

ASIA

SINGAPORE

VISHAY INTERTECHNOLOGY ASIA PTE LTD.
37A TAMPINES STREET 92 #07-00
SINGAPORE 528886
PH: +65-6788-6668
FAX: +65-6788-0988

P.R. CHINA

VISHAY CHINA CO., LTD.
15D, SUN TONG INFOPORT PLAZA
55 HUAI HAI WEST ROAD
SHANGHAI 200030
P.R. CHINA
PH: +86-21-5258 5000
FAX: +86-21-5258 7979

JAPAN

VISHAY JAPAN CO., LTD.
SHIBUYA PRESTIGE BLDG. 4F
3-12-22, SHIBUYA
SHIBUYA-KU
TOKYO 150-0002
JAPAN
PH: +81-3-5466-7150
FAX: +81-3-5466-7160

EUROPE

GERMANY

VISHAY ELECTRONIC GMBH
DR.-FELIX-ZANDMAN-PLATZ 1
95100 SELB
GERMANY
PH: +49-9287-71-0
FAX: +49-9287-70435

FRANCE

VISHAY S.A.
199, BD DE LA MADELEINE
06003 NICE, CEDEX 1
FRANCE
PH: +33-4-9337-2727
FAX: +33-4-9337-2726

UNITED KINGDOM

VISHAY LTD.
SUITE 6C, TOWER HOUSE
ST. CATHERINE'S COURT
SUNDERLAND ENTERPRISE PARK
SUNDERLAND SR5 3XJ
UNITED KINGDOM
PH: +44-191-516-8584
FAX: +44-191-549-9556