



Industrial Potentiometer



FEATURES

- High power rating 2 W at 70 °C
- Full sealing
- Low contact resistance variation (1 % typical)
- Robust nickel plated brass shaft
- Use of faston 2.86 connections
- Cermet element
- Center detent option (haptic technology)
- Test according to CECC 41000 or IEC 60393-1
- Electrical performance in accordance with MIL-PRF-94 standards
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT


LINKS TO ADDITIONAL RESOURCES



QUICK REFERENCE DATA	
Multiple module	No
Switch module	n/a
Detent module	Yes
Special electrical laws	A: linear, L: logarithmic, F: reverse logarithmic
Sealing level	IP 67
Lifespan	25K cycle

DIMENSIONS in millimeters (inches) ± 0.5 mm (± 0.02")

PRV4F



Length L	1/2"	7/8"	2"
Shaft code	GBS	GJS	GRS



ELECTRICAL SPECIFICATIONS		
Resistive element		Cermet
Electrical travel		$270^\circ \pm 10^\circ$
Resistance range	Linear taper	20 Ω to 10 M Ω
	Logarithmic taper	100 Ω to 2.5 M Ω
Standard series		1 - 2 - 2.5 - 5
Tolerance	Standard	$\pm 20\%$
	On request	$\pm 10\%$
Taper		<p>The graph shows Total Resistance (%) on the y-axis (0 to 100) versus Clockwise Shaft Rotation (%) on the x-axis (0 to 100). Three curves are plotted: 'F' (orange) rises steeply from (0,0) to (50,100); 'A' (blue) is a straight line from (0,0) to (100,100); 'L' (green) rises slowly from (0,0) to (100,100).</p>
Circuit diagram		<p>The diagram shows a potentiometer with terminals (1), (2), and (3). Terminal (1) is at the top left, (2) is at the bottom center, and (3) is at the top right. A wiper is connected to terminal (2). An arrow labeled 'cw' indicates clockwise rotation.</p>
Power rating	Linear Logarithmic	<p>The graph shows Power (W) on the y-axis (0 to 2) versus Ambient Temperature (°C) on the x-axis (0 to 140). Two curves are plotted: 'Linear taper "A"' (blue) is constant at 2 W from 0 to 70°C, then drops to 0 at 125°C; 'Logarithmic taper "L and F"' (orange) is constant at 1 W from 0 to 70°C, then drops to 0 at 125°C.</p> <p>2 W at 70 °C 1 W at 70 °C</p>
Temperature coefficient (typical)		300 ppm/°C
Limiting element voltage (linear law)		500 V
Contact resistance variation (typical)		1 % R _n or 3 Ω
End resistance		4 Ω
Dielectric strength (RMS)		1500 V
Insulation resistance (500 V _{DC})		10 ⁴ M Ω
Independent linearity (typical)		5 %



STANDARD RESISTANCE ELEMENT DATA

STANDARD RESISTANCE VALUES	LINEAR TAPER			LOGARITHMIC TAPER		
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH ELEMENT WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH ELEMENT WIPER
Ω	W	V	mA	W	V	mA
20	2	6.32	316			
25	2	7.07	283			
50	2	10.0	200			
100	2	14.1	141	1	10.0	100
200	2	20.0	100.0	1	14.1	70.7
250	2	22.4	89.4	1	15.8	53.2
500	2	31.6	53.2	1	22.4	44.7
1K	2	44.7	44.7	1	31.5	31.6
2K	2	53.2	31.6	1	44.7	22.4
2.5K	2	70.7	28.3	1	50.0	20.0
5K	2	100	20.00	1	70.7	14.1
10K	2	141	14.14	1	100	10.0
20K	2	200	10.00	1	141	7.07
25K	2	224	6.04	1	158	6.32
50K	2	315	6.32	1	224	4.47
100K	2	447	4.47	1	315	3.16
200K	2	500	2.50	1	447	2.24
250K	1	500	2.00	1	499	2.00
500K	1	500	1.00	0.50	500	1.00
1M	0.25	500	0.50	0.25	500	0.50
2M	0.13	500	0.25	0.13	500	0.25
2.5M	0.10	500	0.20	0.10	500	0.20
5M	0.05	500				
10M	0.03	500				


MECHANICAL SPECIFICATIONS


Mechanical travel	300° ± 5°
Operating torque / typical value	2 Ncm (2.83 oz.-inch)
End stop torque	70 Ncm max. (6 lb-inch max.)
Tightening torque of mounting nut	200 Ncm max. (17.3 lb-inch max.)
Unit weight	23 g to 32 g max. (0.82 oz. to 1.14 oz.)

ENVIRONMENTAL SPECIFICATIONS

Temperature range	-55 °C to +125 °C
Climatic category	55/125/10
Sealing	Fully sealed - container IP 67



OPTIONS	
Special feature command shaft	Length is measured from the mounting surface to the free end of the shaft. The screwdriver slot is aligned with the wiper within $\pm 10^\circ$. Special shafts are available, in accordance to drawings supplied by customers. We recommend that customers should not machine tool shafts, in order to avoid damage. Bending or torsion of terminals should also be avoided.
PRV4 LPRP - with locating peg	

CENTER DETENT (haptic technology)	
<ul style="list-style-type: none"> Positive tactile feedback with stable position in mid mechanical travel Output ratio 50 % \pm 10 % Rotational life: 10 000 actuations 	
ORDERING INFORMATION (first order only)	
CV1M	

MARKING
<ul style="list-style-type: none"> Vishay trademark Full ordering information (see Ordering Information table) Manufacturing date Marking of terminals 1, 2, 3

PERFORMANCE				
TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS		
		$\Delta R_T/R_T$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)	OTHER
Electrical endurance	1000 h at rated power 90°/30° - ambient temp. 70 °C	± 3 %	± 5 %	Contact res. variation: < 5 %
Moisture resistance	MIL-STD-202 method 105 10 cycles of 24 h constituted with damp heat - cold - vibrations	± 2 %	± 3 %	Dielectric strength: 100 V _{RMS} Insulation resistance: > 10 ⁴ MΩ
Damp heat, steady state	10 days 40 °C, 93 % HR	± 2 %	± 3 %	Dielectric strength: 100 V _{RMS} Insulation resistance: > 10 ⁴ MΩ
Change of temperature	5 cycles -55 °C at +125 °C	± 1 %	-	$\Delta V_{1-2}/V_{1-3} < \pm 2$ %
Mechanical endurance	25 000 cycles	± 5 %	-	-
Shock	MIL-STD-202 method 213/1 100 g's at 6 ms 3 successive shocks in 3 directions	± 1 %	-	$\Delta V_{1-2}/V_{1-3} < \pm 1$ %
Vibration	MIL-STD-202 method 204/D 20 g's at 12 h	± 1 %	-	$\Delta V_{1-2}/V_{1-3} < \pm 1$ %

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

**ORDERING INFORMATION** (part number)

P	R	V	4	F	L	G	J	S	1	0	2	M	L				
MODEL	BUSHING	OPTION	SHAFT	SHAFT END	OHMIC VALUE	TOLERANCE	TAPER	SPECIAL									
PRV4	F = Ø 3/8"	L = LPRP 0 = no option	GB GJ GR AP = custom shaft	S = slotted On request: R = round F = flattened D = knurled or C = custom	Linear from 20 Ω to 10 MΩ Logarithmic from 100 Ω to 2.5. MΩ 102 = 1 kΩ	M = 20 % On request: K = 10 %	A = linear L = clockwise logarithmic F = inverse clockwise logarithmic	CV1M = detent option or special code given by Vishay									

PART NUMBER DESCRIPTION (for information only)

PRV4	F	L	GJ	S	1K	20 %	L		BO50			e3
MODEL	BUSHING	OPTION	SHAFT	SHAFT END	VALUE	TOLERANCE	TAPER	DETENT OPTION	PACKAGING	AP N°	SPECIAL	LEAD (Pb)-FREE

ACCESSORIES

Additional Accessories (to order separately)	www.vishay.com/doc?51051
Control knobs	www.vishay.com/doc?51101

RELATED DOCUMENTS**APPLICATION NOTES**

Potentiometers and Trimmers	www.vishay.com/doc?51001
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029
Capabilities and Custom Options	www.vishay.com/doc?48485



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.