

Long Life / Heavy Duty Potentiometer



FEATURES

- High power rating 2 W at 70 °C
- Sealed up to IP 67
- Low contact resistance variation (2 % typical)
- Robust nickel plated brass shaft
- Use of faston 2.86 connections
- Cermet element
- Center detent option
- Test according to IEC 60393-1
- Long life $\geq 200K$ cycle
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

LINKS TO ADDITIONAL RESOURCES



| QUICK REFERENCE DATA | |
|-------------------------|------------|
| Multiple module | No |
| Switch module | n/a |
| Detent module | Yes |
| Special electrical laws | A: linear |
| Sealing level | IP 67 |
| Lifespan | 200K cycle |

DIMENSIONS in millimeters (inches) ± 0.5 mm (± 0.02 ")



| | | | |
|------------|------|------|-----|
| Length "L" | 1/2" | 7/8" | 2" |
| Shaft code | GBS | GJS | GRS |




| ELECTRICAL SPECIFICATIONS | | |
|--------------------------------------------------------------------|--------------|----------------------------------------------------------|
| Resistive element | | Cermet |
| Electrical travel | | 270° ± 10° |
| Resistance range | Linear taper | 500 Ω to 5 MΩ |
| Standard series | | |
| Standard series | | Please refer to table "Standard Resistance Element Data" |
| Tolerance | Standard | ± 20 % |
| | On request | ± 10 % |
| Taper standard law: A (linear) (other custom laws upon request) | | |
| Circuit diagram | | |
| Power rating | Linear | 2 W at 70 °C |
| Temperature coefficient (typical) | | 300 ppm/°C |
| Limiting element voltage (linear law) | | 500 V |
| Contact resistance variation (typical) | | 2 % R _n |
| End resistance | | 1 Ω |
| Dielectric strength (RMS) | | 1500 V |
| Insulation resistance (500 V _{DC}) | | 10 ⁴ MΩ |
| Independent linearity (typical) | | 5 % |

| STANDARD RESISTANCE ELEMENT DATA | | | |
|-----------------------------------------|---------------------|----------------------|---------------------------------|
| STANDARD RESISTANCE VALUES | LINEAR TAPER | | |
| | MAX. POWER AT 70 °C | MAX. WORKING VOLTAGE | MAX. CUR. THROUGH ELEMENT WIPER |
| Ω | W | V | mA |
| 500 | 2 | 31.6 | 53.2 |
| 1K | 2 | 44.7 | 44.7 |
| 2K | 2 | 53.2 | 31.6 |
| 5K | 2 | 100 | 20.00 |
| 10K | 2 | 141 | 14.14 |
| 20K | 2 | 200 | 10.00 |
| 50K | 2 | 315 | 6.32 |
| 100K | 2 | 447 | 4.47 |
| 200K | 1 | 500 | 2.50 |
| 500K | 0.50 | 500 | 1.00 |
| 1M | 0.25 | 500 | 0.50 |
| 2M | 0.13 | 500 | 0.25 |
| 5M | 0.05 | 500 | 0.10 |

| MECHANICAL SPECIFICATIONS | |
|-----------------------------------|------------------------------------------|
| Mechanical travel | 300° ± 5° |
| Operating torque / typical value | 2 Ncm (2.83 oz.-inch) |
| End stop torque | 70 Ncm max. (6.5 lb-inch max.) |
| Tightening torque of mounting nut | 200 Ncm max. (17.3 lb-inch max.) |
| Unit weight | 23 g to 32 g max. (0.82 oz. to 1.14 oz.) |

| ENVIRONMENTAL SPECIFICATIONS | |
|-------------------------------------|--------------------------------|
| Temperature range | -55 °C to +125 °C |
| Climatic category | 55/125/10 |
| Sealing | Fully sealed - container IP 67 |

| OPTIONS | |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Special feature command shaft | Length is measured from the mounting surface to the free end of the shaft. The screwdriver slot is aligned with the wiper within ± 10°. Special shafts are available, in accordance to drawings supplied by customers. We recommend that customers should not machine tool shafts, in order to avoid damage. Bending or torsion of terminals should also be avoided. |
| RV4L LPRP - with locating peg |  |

| MARKING |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> • Vishay trademark • Full ordering information (see Ordering Information table) • Manufacturing date • Marking of terminals 1, 2, 3 |



| PERFORMANCE | | | |
|-------------------------|---------------------------------------------------------------------------------------------------|---------------------------|---------------------------------------------|
| TESTS | CONDITIONS | TYPICAL VALUES AND DRIFTS | |
| | | $\Delta R_T/R_T$ (%) | OTHER |
| Electrical endurance | 1000 h at rated power 90°/30° - ambient temp. 70 °C | ± 3 % | - |
| Climatic sequence | Phase A dry heat 125 °C Phase B damp heat Phase C cold -55 °C Phase D damp heat 5 cycles | ± 0.5 % | - |
| Damp heat, steady state | 56 days 40 °C, 93 % HR | ± 0.5 % | Insulation resistance: > 10 ⁵ MΩ |
| Change of temperature | 5 cycles -55 °C at +125 °C | ± 0.5 % | |
| Mechanical endurance | 200 000 cycles at rated power turn angle ± 60° T° = 20 °C | ± 20 % | Independent linearity ± 10 % |
| Shock | 50 g's at 11 ms 3 successive shocks in 3 directions | ± 1 % | |
| Vibration | 10 Hz to 55 Hz 0.75 mm or 10 g's at 6 h | ± 1 % | |

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

| ORDERING INFORMATION (part number) | | | | | | | | | | | | | | | | | |
|------------------------------------|------------|---------------------------------|-----------------------------------------|--------------------------------------------------------------------------------------------|---------------------------------------------|-----------------------------------------|----------------------------------------------|------------------------------------------------------|---|---|---|---|---|--|--|--|--|
| R | V | 4 | L | F | L | G | J | S | 5 | 0 | 2 | M | A | | | | |
| MODEL | BUSHING | OPTION | SHAFT | SHAFT END | OHMIC VALUE | TOLERANCE | TAPER | SPECIAL | | | | | | | | | |
| RV4L | F = Ø 3/8" | L = LPRP 0 = no locating peg | GB GJ GR AP = custom shaft (1) | S = slotted On request: R = round F = flatted D = knurled or C = custom | Linear from 500 Ω to 5 MΩ 502 = 5 kΩ | M = 20 % On request: K = 10 % | A = linear On request: custom laws | CV1M = detent option or special code given by Vishay | | | | | | | | | |

Note

- (1) See Dimensions table

| PART NUMBER DESCRIPTION (for information only) | | | | | | | | | | | | | |
|------------------------------------------------|---------|--------|-------|-----------|-------|-----------|-------|---------------|-----------|-------|---------|----------------|----|
| RV4L | F | L | GJ | S | 5K | 20 % | A | | BO50 | | | | e3 |
| MODEL | BUSHING | OPTION | SHAFT | SHAFT END | VALUE | TOLERANCE | TAPER | DETENT OPTION | PACKAGING | AP N° | SPECIAL | LEAD (Pb)-FREE | |

| ACCESSORIES | |
|----------------------------------------------|------------------------------------------------------------------------|
| Additional Accessories (to order separately) | www.vishay.com/doc?51051 |
| Control knobs | www.vishay.com/doc?51101 |

| RELATED DOCUMENTS | |
|-------------------------------------------------------------------|------------------------------------------------------------------------|
| APPLICATION NOTES | |
| Potentiometers and Trimmers | www.vishay.com/doc?51001 |
| Guidelines for Vishay Sfernice Resistive and Inductive Components | www.vishay.com/doc?52029 |
| Capabilities and Custom Options | www.vishay.com/doc?48485 |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.