

1 1/16" (27 mm) Single Turn Wirewound Precision Potentiometer



FEATURES

- Gangable up to 6 sections
- Extra taps on request
- Bushing or servo mount types available
- Ohmic value range: 5 Ω up to 100 k Ω
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

QUICK REFERENCE DATA

Sensor type	ROTATIONAL, single turn wirewound
Output type	Output by turrets
Market appliance	Professional
Dimensions	1 1/16" (27 mm)

ELECTRICAL SPECIFICATIONS

PARAMETER	STANDARD	SPECIAL
Total resistance	5 Ω to 20 k Ω	to 30 k Ω
Tolerance: 20 Ω and above	$\pm 3\%$	$\pm 1\%$
Below 20 Ω	$\pm 5\%$	$\pm 3\%$
Linearity (independent):	STANDARD	BEST PRACTICAL
5 Ω to 200 Ω	$\pm 1.0\%$	$\pm 0.50\%$
200 Ω to 2 k Ω	$\pm 0.5\%$	$\pm 0.35\%$
2 k Ω to 10 k Ω	$\pm 0.5\%$	$\pm 0.25\%$
10 k Ω and above	$\pm 0.5\%$	$\pm 0.20\%$
Noise	100 Ω ENR	
Electrical angle	350° $\pm 2^\circ$	
Power rating	1.50 W at 70 °C ambient, derated to zero at 125 °C	
Section 1:	75 % of the rating of section 1 (1.125 W at 70 °C)	
Additional sections:		
Insulation resistance	1000 M Ω minimum, 500 V _{DC}	
Dielectric strength	1000 V _{RMS} 60 Hz	
Absolute minimum resistance	Linearity x total resistance or 0.5 Ω , whichever is greater	
End voltage	Linearity x total applied voltage for total resistance above 20 Ω , 2.0 % of total applied voltage for 20 Ω and below	
Phasing (CCW end points)	Additional sections phased to section 1 within $\pm 1^\circ$	
Taps (extra)	9 available as special standard tolerance $\pm 1^\circ$	

ORDERING INFORMATION



1	2	2	S	1	2	0	3	2	0	3	X	X	X	X
MODEL		STYLE		GANGS		OHMIC VALUE GANGS N° 1		OHMIC VALUE GANGS N° 2		SPECIAL REQUEST				
122		B: bushing S: servo		1 2 3 4 5 6		470 = 47 Ω 222 = 2.200 Ω 103 = 10 k Ω For ohmic value range see electrical specification		470 = 47 Ω 222 = 2.200 Ω 103 = 10 k Ω For ohmic value range see electrical specification		xxxx				

**PART NUMBER DESCRIPTION** (for information only)

122-	1	1	102	103	xxxx
MODEL	STYLE	GANGS	OHMIC VALUE GANGS N° 1	OHMIC VALUE GANGS N° 2	SPECIAL


B: 1

S: 2

DIMENSIONS in inches (millimeters)**BUSHING MOUNT: 122B/122-1...****SERVO MOUNT: 122S/122-2...**

ADD 0.500 ± 0.002 (12.70) FOR EACH ADDITIONAL SECTION

TOLERANCES: UNLESS OTHERWISE NOTED.
DECIMALS ± 0.005 ANGLES ± 2°

**MATERIAL SPECIFICATIONS**

Housing and lids	Aluminum, anodized
Shaft	Stainless steel, non-magnetic non-passivated
Terminals	Brass, plated for solderability
Bushing mount hardware Lockwasher internal tooth: Panel nut:	Steel, nickel plated Brass, nickel plated

ENVIRONMENTAL SPECIFICATIONS

Vibration	15 g thru 2000 CPS
Shock	50 g
Salt spray	96 h
Rotational life	1 million shaft revolutions
Load life	900 h
Temperature range	-55 °C to +125 °C

Note


- Nothing stated herein shall be construed as a guarantee of quality or durability

**MARKING**

Unit identification	Units shall be marked with Vishay Spectrol name and model number resistance and resistance tolerance, linearity, terminal identification and data code. Example of a marking for a standard part: 122-11502
---------------------	--

POWER RATING CHART

(Ratings for cup No. 1. Additional cups 75 % of values shown)

**RESISTANCE ELEMENT DATA**

RESISTANCE VALUES (Ω)	RESOLUTION (%)	OHMS PER TURN	MAXIMUM CURRENT AT 70 °C AMBIENT (mA)	MAXIMUM VOLTAGE ACROSS COIL (V)	WIRE TEMP. COEF. (ppm/°C)
5	0.364	0.018	548	2.74	800
10	0.311	0.031	387	3.87	800
20	0.250	0.050	274	5.48	180
50	0.232	0.116	173	8.65	180
100	0.232	0.231	122	12.2	20
200	0.194	0.389	86.6	17.3	20
500	0.168	0.841	54.8	27.4	20
1K	0.156	1.557	38.7	38.7	20
2K	0.109	2.178	27.4	54.8	20
5K	0.088	4.382	17.3	86.5	20
10K	0.076	7.644	12.2	122	20
20K	0.071	14.235	8.66	173	20
50K	0.062	30.921	5.48	274	20
100K	0.052	51.983	3.87	387	20

MECHANICAL SPECIFICATIONS

PARAMETER		
Rotation	360° continuous	
Bearing type	Servo mount: ball bearing Bushing mount: sleeve bearing	
Torque (maximums)	STARTING	RUNNING
Servo, 1 section	0.25 oz. - in (18.0 g - cm)	0.15 oz. - in (10.8 g - cm)
Bushing, 1 section	0.30 oz. - in (21.6 g - cm)	0.25 oz. - in (18.0 g - cm)
Each additional section	0.20 oz. - in (14.4 g - cm)	0.15 oz. - in (10.8 g - cm)
Mechanical runouts (maximums):	SERVO	BUSHING
Shaft runout (TIR/in)	0.002" (0.05 cm)	0.002" (0.05 cm)
Pilot dia. runout (TIR)	0.002" (0.05 cm)	0.002" (0.05 cm)
Lateral runout (TIR)	0.002" (0.05 cm)	0.005" (0.13 cm)
Shaft end play	0.005" (0.13 cm)	0.005" (0.13 cm)
Shaft radial play	0.002" (0.05 cm)	0.003" (0.08 cm)
Weight (maximums):		
Single section	0.8 oz. (22.7 g)	
Each additional section	0.4 oz. (11.3 g)	
Ganging	6 sections maximum, terminal alignment, added sections within $\pm 10^\circ$ of section 1 terminals	
Moment of inertia	0.12 g - cm ² per section maximum	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.