




25 mil Pitch Thin Film Surface Mount Resistor/Capacitor Network



Actual Size

IEEE 1284 parallel port termination network

FEATURES

- Rugged, molded case construction
JEDEC MO-137AD
- Reduces total assembly costs
- Saves board space
- Compatible with automatic surface mounting equipment
- Uniform performance characteristics
- Resistors and capacitors on a single chip
- UL 94 V-0 flame resistant
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition




RoHS
COMPLIANT
HALOGEN
FREE

TYPICAL PERFORMANCE

	TCR	TOLERANCE
RESISTOR	200	10
	TCC	TOLERANCE
CAPACITOR	200	20

SCHEMATIC



STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Tantalum nitride	-
Pin/Lead Number	20	-
Resistance Range	10 Ω to 10 k Ω	-
TCR: Absolute	± 200 ppm/ $^{\circ}$ C	-
TCR: Tracking	-	-
Tolerance: Absolute	± 10 % (R_1 and R_2), ± 20 % (C)	At 1 MHz and V_{RMS} over $+10^{\circ}$ C to $+70^{\circ}$ C
Power Rating: Resistor	100 mW	-
Power Rating: Package	1 W	-
Stability: Ratio	-	-
Operating Temperature Range	-	-
Storage Temperature Range	-	-
Capacitance Range	27 pF to 220 pF	Based on number of resistors
ESD Protection	> 2 kV	MIL-STD-883, method 3015
Breakdown Voltage	25 V	-

DIMENSIONS in inches and millimeters

DIMENSION	MODEL VSSRC1284	
	INCHES	
	MINIMUM	MAXIMUM
A	0.344 max.	8.74 max.
B (ref.)	0.025	0.64
C (ref.)	0.010	0.25
D	0.006	0.15
E (typ.)	0.025	0.64
F	0.154 ± 0.003	3.85 ± 0.08
G	0.015 x 45°	0.38 x 45°
H	0.236 ± 0.008	5.9 ± 0.20
J (ref.)	0.010	0.25
W	0.064 ± 0.005	1.64 ± 0.13

Note

- Mold flash not included in body dimensions


IMPRINTING
VSSRC1284-X

Date code

-X = Molded version number from table below

MECHANICAL SPECIFICATIONS

Resistive Element	Tantalum nitride
Substrate Material	Silicon
Body	Molded epoxy
Terminals	Copper alloy
Plating	100 % matte Sn
Lead Coplanarity	0.0005"
Marking Resistance to Solvents	Permanency testing per MIL-STD-202, method 215

DERATING CURVE

STANDARD VALUES

AVAILABLE MODELS	R ₁ ± 10 % (Ω)	R ₂ ± 10 % (Ω)	C ± 20 % (pF)
VSSRC1284-1	2.2K	33	220
VSSRC1284-2	4.7K	33	180
VSSRC1284-3	1K	33	180
VSSRC1284-4	4.7K	10	180
VSSRC1284-5	4.7K	27	33
VSSRC1284-6	4.7K	270	33
VSSRC1284-7	10K	10	27



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: VSSRC1284-1TF

V S S R C 1 2 8 4 - 1 T F

GLOBAL MODEL
VSSRC1284

VALUE
-1
-2
-3
-4
-5
-6
-7

PACKAGING
UF = TUBED
TAPE AND REEL
TF = Full reels

Historical Part Number example: VSSRC1284-1T/R (for reference purposes only)

VSSRC1284
MODEL

-1
VALUE

T/R
PACKAGING



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.