


Molded, SC-70 Thin Film Resistor, Surface Mount Network



Vishay Dale Thin Film MP Series Dividers provide ± 2 ppm/ $^{\circ}\text{C}$ tracking and a ratio tolerance as tight as $\pm 0.05\%$, ultra small size, 3 or 4 lead package and exceptional stability for all surface mount applications. The standard SC-70 package format with common standard resistance values provide easy selection for most applications requiring matched pair resistor elements. If you require a non-standard ratio, consult the applications engineering group as we may be able to meet your requirements.

SCHEMATIC



FEATURES

- Small physical size EIAJ SC70 format
- Tight resistance ratio tolerances $\pm 0.05\%$
- Low TCR tracking ± 2 ppm
- Excellent long term ratio stability ($\Delta R \pm 0.015\%$ at 70°C for 2000 h)
- Center-tapped or isolated matched pair resistors
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

TYPICAL PERFORMANCE

	ABSOLUTE	TRACKING
TCR	25	2
	ABSOLUTE	RATIO
TOL.	0.1	0.05

STANDARD RESISTANCE VALUES


TYPE	STANDARD VALUES	
	R_1 (Ω)	R_2 (Ω)
MP3	500	500
	1K	1K
	10K	10K
MP4	1K	1K
	10K	10K
	50K	50K

STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin/Lead Number	3, 4	-
Resistance Range	100 Ω to 50 k Ω per resistor	-
TCR: Absolute	± 25 ppm/ $^{\circ}\text{C}$	-55°C to $+125^{\circ}\text{C}$
TCR: Tracking	± 2 ppm/ $^{\circ}\text{C}$ (typical)	-55°C to $+125^{\circ}\text{C}$
Tolerance: Absolute	$\pm 0.10\%$ to $\pm 1.0\%$	$+25^{\circ}\text{C}$
Tolerance: Ratio	$\pm 0.05\%$ (standard), $\pm 1.0\%$	-
Power Rating: Resistor	0.075 W	Maximum at $+70^{\circ}\text{C}$
Power Rating: Package	0.150 W	Maximum at $+70^{\circ}\text{C}$
Stability: Absolute	$\Delta R \pm 0.05\%$	2000 h at $+70^{\circ}\text{C}$
Stability: Ratio	$\Delta R \pm 0.015\%$	2000 h at $+70^{\circ}\text{C}$
Voltage Coefficient	0.1 ppm/V	-
Working Voltage	100 V max. not to exceed $\sqrt{P \times R}$	-
Operating Temperature Range	-55°C to $+125^{\circ}\text{C}$	-
Storage Temperature Range	-55°C to $+150^{\circ}\text{C}$	-
Noise	< -30 dB	-
Thermal EMF	0.1 $\mu\text{V}/^{\circ}\text{C}$	-
Shelf Life Stability: Absolute	$\Delta R \pm 0.01\%$	1 year at $+25^{\circ}\text{C}$
Shelf Life Stability: Ratio	$\Delta R \pm 0.002\%$	1 year at $+25^{\circ}\text{C}$

DIMENSIONS AND IMPRINTING in millimeters			
	DIMENSION	MIN.	MAX.
	A	0.800	1.100
	A1	0.000	0.100
	A2	0.800	1.000
	B	0.100	0.018
	b1	0.575	0.700
	b2	0.150	0.300
	b3	0.250	0.400
	D	1.800	2.200
	E	1.800	2.400
	E1	1.150	1.350
	e	1.300 BSC	-
	e1	1.150 BSC	-
	e2	0.650 BSC	-
	L	0.100	0.030
	L1	0.260	0.460

MECHANICAL SPECIFICATIONS	
Resistive Element	Passivated nichrome
Substrate Material	Silicon
Body	Molded epoxy
Terminals	Copper alloy
Lead (Pb)-free Option	100 % matte tin
Tin Lead Option	Sn85
Tin Lead and Lead (Pb)-free Finish	Plated



GLOBAL PART NUMBER INFORMATION														
New Global Part Numbering: MP32001AWS														
M	P	T	4	1	0	0	1	5	0	0	1	B	T	1
M	P	3					2	0	0	1		A	W	S
GLOBAL MODEL (2 or 3 digits)	LEADS	RESISTANCE (4 or 8 digits)					TOLERANCE AND RATIO TOLERANCE		PACKAGING					
MP (Tin lead)	3 4	First 3 digits are significant figures and the last digit specifies the number of zeros to follow. When like values are required use total resistance. When dual values are required list both values. Example: (List R1 first in part number with dual values) 1002 = 10K (5K/5K) 10011002 = 1K/10K divider					Abs. Tol. Ratio A = 0.1 % 0.05 % B = 0.1 % 0.1 % C = 0.25 % 0.1 % D = 0.5 % 0.1 % F = 1.0 % 0.5 %		BS = BULK 100 min., 1 mult. WS = WAFFLE 100 min., 1 mult. TAPE AND REEL T1 = 1000 min., 1000 mult. (1) Note (1) Preferred packaging code					
Historical Part Number Example: MP32002BW (for reference purposes only)														
MP	3	2002			B		W							
SERIES	LEADS	RESISTANCE			TOLERANCE AND RATIO TOLERANCE		PACKAGING							



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.