


Surface Mount Thin Film Single Layer Resistor Array



Product may not be to scale

FEATURES

- Standard chip sizes 0.100", 0.150", 0.210" wide
- Custom chip sizes up to 0.500" x 0.500"
- Custom chip sizes up to 0.500" x 0.500"
- Case: 0510 to 2010
- Mixed values to 500 k Ω
- Multiple reference resistor groups
- Ratio tolerance to $\pm 0.05\%$
- Ratio TCR's to ± 1 ppm/ $^{\circ}\text{C}$
- Nichrome resistor material standard. Tantalum nitride available, consult factory
- Custom pad spacing 0.025" or greater

SLR (single layer resistor carrier) networks are offered to provide the user with a leadless device that maximizes board density while maintaining tight ratio tolerances and TCR tracking. Pads are provided top and bottom connected by edge castellations for ease of visual solder joint inspection. Resistors can be covered with Vishay Electro-Films (EFI) proprietary thermal set plastic for physical protection or left uncoated to facilitate user trimming.

SLR's are provided with 0.050" standard contact spacing; however, 0.025" contact spacing is also available. The standard contact metallization is gold flash over nickel plate. Solder coated contacts can be provided if preferred. Custom configurations, values, and tolerance combinations are available with fast turnaround.

TEMPERATURE COEFFICIENT OF RESISTANCE, VALUES, AND TOLERANCES

PARAMETER	VALUE	UNIT
Total Resistance Range	10 to 500K	Ω
Standard Tolerance	± 0.1 to ± 1	%
TCR	± 50 ; available to ± 10	ppm/ $^{\circ}\text{C}$



STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	VALUE	UNIT
Absolute Resistance Tolerance	± 0.1 to ± 1	%
Resistance Ratio Tolerance	± 0.05 to ± 0.1	%
Ratio TCR	± 5 available to ± 1	ppm/ $^{\circ}\text{C}$
Absolute Resistor Stability (Mean)	300 per 1000 h at 125 $^{\circ}\text{C}$ typ.	ppm
Ratio Resistor Stability (Mean)	18 per 1000 h at 125 $^{\circ}\text{C}$ typ.	ppm
Temperature Range	0 to + 70, - 40 to + 85, - 55 to + 125	$^{\circ}\text{C}$
DC Power Rating at 70 $^{\circ}\text{C}$	0.1	W
DC Power Rating at 125 $^{\circ}\text{C}$	0.05	W

The SLR construction allows for a wide selection of special sizes and shapes with rapid turnaround and low NRE costs. The holes for the edge castellations are laser drilled into a multiple-up, large area substrates in-house prior to metallization. This permits new configurations with only laser software and a mask set.

Custom parts can be provided with combinations of features listed:

1. Any combination of resistor values between 100 Ω and 100 k Ω in the standard sizes.
2. Custom resistor network patterns (no crossovers).
3. A wide variety of rectangular sizes and shapes with contact pads on two to four sides.
4. Pad center-to-center spacings from 0.025" (0.635 mm) and larger.
5. Uncoated to permit customer trimming.


OUTLINE DRAWING


Single Layer 16 Pin Chip Carrier
Chip measures 0.300" x 0.300".
Castellations are on 0.050" (1.27 mm) centers.
(Special Order)

DIMENSIONS in inches [millimeters]						
CENTERS	A	B	C	D	E	F
0.025 [0.64]	(1)	0.100 [2.54]	0.015 [0.38]	0.025 [0.64]	0.015 [0.38]	0.020 [0.51]
0.050 [1.28]	(2)	0.100 [2.54]	0.030 [0.76]	0.050 [1.28]	0.015 [0.38]	0.020 [0.51]
0.050 [1.28]	(2)	0.150 [3.84]	0.030 [0.76]	0.050 [1.28]	0.025 [0.64]	0.020 [0.51]
0.050 [1.28]	(2)	0.210 [5.37]	0.030 [0.76]	0.050 [1.28]	0.025 [0.64]	0.020 [0.51]

Notes

- (1) 0.025" [0.64 mm] per resistor, 2 to 18 pads
(2) 0.050" [1.28 mm] per resistor, 2 to 18 pads



Standard Pitch: Castellations are
on 0.050" (1.27 mm) centers
(0.025" pitch special order)

ORDERING INFORMATION

Global Part Number: SLRC410001FFCGGS

Global Part Number Description: SLRC 4 RES 10K 1 % RT 1 % 50 ppm 2 ppm Au WS

S	L	R	C	4	1	0	0	0	1	F	F	C	G	G	W	S
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

MODEL	WIDTH (mil)	NUMBER RESISTORS	RESISTANCE	RES. MULTIPLIER CODE	TOL. CODE (%)	RATIO TOL. (%)	TCR (ppm/°C)	TC TRACK (ppm/°C)	TERMINATION	PACKAGING CODE
SLR Resistor Carrier NiCr on Alumina	C = 100 N = 150 M = 210	2 = 2 3 = 3 4 = 4 7 = 7 8 = 8	First 4 digits are significant figures of resistance	B = 0.01 A = 0.1 0 = 1.0 1 = 10.0 2 = 100.0	B = 0.1 C = 0.25 D = 0.5 F = 1.0 G = 2.0 J = 5.0 K = 10.0	W = 0.01 V = 0.02 A = 0.05 B = 0.1 C = 0.25 D = 0.5 F = 1.0 G = 2.0	B = ± 10 E = ± 25 C = ± 50 K = ± 100 M = ± 250	F = ± 1 G = ± 2 H = ± 3 J = ± 5 K = ± 10	G = Au S = SnPb T = Lead (Pb)-free (e1)	WS = Waffle pack 100 min., 1 mult



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.