




25 mil or 50 mil Pitch, T-Filter Thin Film Surface Mount Resistor/Capacitor Network



Small outline, surface mount, EMI/RFI reduction, T-filter networks
 Vishay Thin Film's schematic AD is designed as an 8 channel filter for use with personal computer and peripheral 110 ports such as SCSI ports. The use of single die technology for filtering minimizes space and allows for more freedom in routing. With a rugged molded case to protect the circuit from the environment and an integrated thin film network this product is your choice when reduced size, improved accuracy and surface mount capability are your goals.
 Available packages SOIC, SSOP and TSSOP.

SCHEMATIC AD



FEATURES

- Resistors and capacitors on a single chip
- Saves board space
- Reduces total assembly costs
- Uniform performance characteristics
- Compatible with automatic surface mounting equipment
- UL 94 V-0 flame resistant
- Rugged, molded case construction
- Compliant to RoHS Directive 2002/95/EC



TYPICAL PERFORMANCE

| | TCR | TOLERANCE |
|-----------|-----|-----------|
| RESISTOR | 200 | 10 |
| | TCC | TOLERANCE |
| CAPACITOR | 200 | 20 |

STANDARD VALUES

| MODELS | | | R (Ω) | C (pF) |
|--------|-------|-------|-------|--------|
| VSORC | VSSRC | VTSRC | | |
| | X | | 33 | 47 |

| STANDARD ELECTRICAL SPECIFICATIONS | | |
|------------------------------------|--|---|
| TEST | SPECIFICATIONS | CONDITIONS |
| Material | Tantalum nitride on silicon | - |
| Pin/Lead Number | 20 | - |
| Resistance Range | 10 Ω to 750 Ω | - |
| TCR: Absolute | ± 200 ppm/°C | 0 °C to + 70 °C |
| TCR: Tracking | ± 10 ppm/°C | - |
| Tolerance: Absolute | ± 10 % standard (R), ± 20 % standard (C) | At 1 MHz and V _{RMS} over + 10 °C to + 70 °C |
| Power Rating: Resistor | 100 mW | - |
| Power Rating: Package | (T)SSOP: 1 W, SOIC: 1.2 W | See derating curve |
| Stability: Ratio | ± 2 % | 1000 h |
| Operating Temperature Range | 0 °C to + 70 °C | - |
| Storage Temperature Range | - 55 °C to + 125 °C | - |
| Capacitance Range | TSSOP: 10 pF to 150 pF, SOIC/SSOP: 10 pF to 250 pF | - |
| ESD Protection | > 2 kV | MIL-STD-883, method 3015 |
| Breakdown Voltage | 35 V to 50 V | - |

DIMENSIONS in inches and millimeters



| DIMENSION | JEDEC M0-153AC, VTSRC20-AD | | JEDEC M0-137AD, VSSRC20-AD | | JEDEC MS-013AC, VSORC20-AD | |
|-----------|----------------------------|-------------|----------------------------|-------------|----------------------------|-------------|
| | INCHES | MILLIMETERS | INCHES | MILLIMETERS | INCHES | MILLIMETERS |
| A | 0.256 ± 0.003 | 6.5 ± 0.08 | 0.344 max. | 8.74 max. | 0.500 ± 0.010 | 12.7 ± 0.25 |
| B (ref.) | 0.025 | 0.65 | 0.025 | 0.64 | 0.050 | 1.27 |
| C (ref.) | 0.0087 | 0.22 | 0.010 | 0.25 | 0.016 | 0.41 |
| D | 0.004 | 0.10 | 0.006 | 0.15 | 0.008 | 0.20 |
| E (typ.) | 0.024 | 0.61 | 0.025 | 0.64 | 0.030 | 0.76 |
| F | 0.173 ± 0.003 | 4.39 ± 0.08 | 0.154 ± 0.003 | 3.9 | 0.293 ± 0.003 | 7.44 |
| G | 0.015 x 45° | 0.38 | 0.015 x 45° | 0.38 | 0.025 x 45° | 0.64 |
| H | 0.252 ± 0.005 | 6.4 ± 0.13 | 0.236 ± 0.008 | 6.0 ± 0.20 | 0.406 ± 0.005 | 10.31 |
| J (ref.) | 0.005 | 0.13 | 0.010 | 0.25 | 0.010 | 0.25 |
| W | 0.043 ± 0.005 | 1.09 ± 0.13 | 0.064 ± 0.005 | 1.6 | 0.100 ± 0.005 | 2.59 |

IMPRINTING

| | | | | | |
|----------------------------|-----------|-------------------|--|----------|---|
| VSORC, VSSRC, VTSRC | 20 | AD | XXX | / | XXX |
| MODEL | PIN COUNT | SCHEMATIC | RESISTANCE Code: e.g. 100 = 10 Ω | / | CAPACITANCE Code: e.g. 101 = 100 pF |
| | | XXXX Date code | | | Optional marking |

MECHANICAL SPECIFICATIONS

| | |
|---------------------------------------|--|
| Resistive Element | Tantalum nitride |
| Substrate Material | Silicon |
| Body | Molded epoxy |
| Terminals | Copper alloy |
| Plating | 100 % matte Sn |
| Lead Coplanarity | 0.0005" |
| Marking Resistance to Solvents | Permanency testing per MIL-STD-202, method 215 |

DERATING CURVE

PACKING INFORMATION

| MODEL | LEADS | TAPE AND REEL | TUBES |
|-------------------------------|-------|---------------|-------|
| JEDEC M0-153AC, VTSRC (TSSOP) | 20 | 2500 | 74 |
| JEDEC M0-137AD, VSSRC (SSOP) | 20 | 2500 | 55 |
| JEDEC MS-013AC, VSORC (SOIC) | 20 | 1000 | 38 |



| GLOBAL PART NUMBER INFORMATION | | | | | | | | | | | | | | | | |
|--|---|--------------------|---|--------------------------------|---|------------|--|-----------|---|-----------|---|--|---|---|---|---|
| New Global Part Numbering: VTSRC20AD330470TF | | | | | | | | | | | | | | | | |
| V | T | S | R | C | 2 | 0 | A | D | 3 | 3 | 0 | 4 | 7 | 0 | T | F |
| GLOBAL MODEL | | | | NUMBER OF LEADS/ SCHEMATICS | | | RESISTANCE AND TOLERANCE/ CAPACITANCE AND TOLERANCE | | | | | PACKAGING | | | | |
| VSSRC VTSRC VSORC | | | | 20AD | | | xxxxyy First 2 digits are significant figures. Last digit specifies number of zeros to follow. K = 10 % resistance tol. fixed M = 20 % capacitor tol. fixed | | | | | UF = TUBED TAPE AND REEL TF = Full reels | | | | |
| Historical Part Number example: VTSRC20AD330K470MT/R (for reference purposes only) | | | | | | | | | | | | | | | | |
| VTSRC | | 20 | | AD | | 330K | | 470M | | T/R | | | | | | |
| MODEL | | NUMBER OF LEADS | | SCHEMATIC | | RESISTANCE | | TOLERANCE | | PACKAGING | | | | | | |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.