



25 mil Pitch, IEEE 1284 Termination Thin Film Surface Mount Resistor, Capacitor, Diode



Product is pictured larger than actual size to show detail

Vishay has upgraded the standard IEEE 1284 Thin Film technology Network, incorporating diodes for protecting the inputs/outputs from electro-static discharge (ESD).

The sophisticated circuit is housed in a standard QSOP, 28-pin package.

Uses include ECP/EPP parallel port terminations for PC peripherals, notebooks, desktops, workstations and servers. This is a guaranteed stock part.


FEATURES

- One sophisticated, integrated Thin Film technology solution
- Up-graded IEEE 1284 parallel port termination, pull-up with the addition of diodes for filtering on the parallel port
- Standard QSOP package (28 pins) - JEDEC MO-137AF
- 17 terminating lines
- Reduces total cost
- Increase board utilization
- Better performance over discretes
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

SCHEMATIC



STANDARD ELECTRICAL SPECIFICATIONS		
TEST	SPECIFICATIONS	CONDITIONS
Material	Polysilicon / thin film on silicon	-
Pin/Lead Number	28	-
Resistance Range	-	-
TCR: Absolute	-	-
TCR: Tracking	-	-
Tolerance: Absolute	$\pm 10\%$ (R), $\pm 20\%$ (C)	-
Power Rating: Resistor	100 mW	-
Power Rating: Package	1 W	-
Stability: Ratio	-	-
Operating Temperature Range	0 °C to +70 °C	-
Storage Temperature Range	-65 °C to +150 °C	-
Capacitance Range	-	-
ESD Protection	See table	-
Breakdown Voltage	-	-
Signal clamp voltage	(+) clamp > 6 V; (-) clamp < -6 V	-
Maximum leakage current at V _{CC}	1 μ A	Maximum at 25 °C



ESD PROTECTION		
	MAXIMUM	MINIMUM
Peak Discharge Voltage at any I/O, Human Body Model, Method 3015 ⁽¹⁾	+8 kV	-4 kV
In System Protection HBM ⁽²⁾	+15 kV	-8 kV
In System Protection, IEC 1000-4-2, Level 2 ⁽²⁾⁽³⁾	+8 kV	-4 kV
Channel Clamp Voltage at 8 kV ESD Pulses, HBM ⁽¹⁾⁽²⁾	+30 V	-30 V

Notes

- ⁽¹⁾ Human body model per MIL-STD-883, method 3015 C_{Discharge} = 100 pF, R_{Discharge} = 1.5 kΩ pin 20 at 5 V and pin 22 at ground.
- ⁽²⁾ Pin 22 grounded, pin 20 to V_{CC} all other pins are open. ESD contact discharge between ground and pins 1, 2, 8, 10, 12, 15, 16, 17, 18, 19, 21, 23 through 28, one at a time.
- ⁽³⁾ Standard IEC 1000-4-2 with C_{Discharge} = 150 pF, R_{Discharge} = 330 Ω pin 20 at 5 V and pin 22 at ground.

DIMENSIONS in inches and millimeters			
	DIMENSION	INCHES	MILLIMETERS
	A	0.068	1.727
	A1	0.008	0.203
	B	0.012	0.305
	C	0.010	0.254
	D	0.394	10.008
	E	0.157	3.988
	e	0.025	0.635
	H	0.244	6.198
	h	0.016	0.406
	L	0.038	0.889
	a°		8

Note

- Mold flash not included in body dimensions.
JEDEC MO-137 package

MECHANICAL SPECIFICATIONS	
R/C Element	Polysilicon/thin film
Substrate Material	Silicon
Body	Molded epoxy
Terminals	Copper alloy
Plating	100 % matte Sn
Lead Coplanarity	0.005"
Marking Resistance to Solvents	MIL-STD-202, method 15
Flammability	UL 94 V-0

STANDARD VALUES			
AVAILABLE MODELS	R ₁ (Ω)	R ₂ (Ω)	C (pF)
VSSX1284A	4.7K	33	180
VSSX1284B	2.2K	33	220

GLOBAL PART NUMBER INFORMATION												
Global Part Numbering: VSSX1284ATF												
<table border="1" style="margin: auto;"> <tr> <td>V</td><td>S</td><td>S</td><td>X</td><td>1</td><td>2</td><td>8</td><td>4</td><td>A</td><td>T</td><td>F</td> </tr> </table>	V	S	S	X	1	2	8	4	A	T	F	
V	S	S	X	1	2	8	4	A	T	F		
<table border="1" style="margin: auto;"> <tr> <td>GLOBAL MODEL</td> </tr> <tr> <td>VSSX1284A or VSSX1284B</td> </tr> </table>	GLOBAL MODEL	VSSX1284A or VSSX1284B	<table border="1" style="margin: auto;"> <tr> <td>PACKAGING</td> </tr> <tr> <td>UF = TUBED</td> </tr> <tr> <td>TAPE AND REEL</td> </tr> <tr> <td>TF = Full reels</td> </tr> </table>	PACKAGING	UF = TUBED	TAPE AND REEL	TF = Full reels					
GLOBAL MODEL												
VSSX1284A or VSSX1284B												
PACKAGING												
UF = TUBED												
TAPE AND REEL												
TF = Full reels												



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.