


Case Outline for TDFN10-22



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A ⁽⁴⁾	0.65	0.75	0.85	0.026	0.030	0.034
A1	0.00	-	0.05	0.000	-	0.002
A2	0.20 ref.			0.008 ref.		
b ⁽¹⁾	0.15	0.25	0.35	0.006	0.010	0.014
D	1.90	2.00	2.10	0.075	0.079	0.083
D1	0.15	0.25	0.35	0.006	0.010	0.014
D2	0.20	0.30	0.40	0.008	0.012	0.016
e	0.500 BSC.			0.020 BSC.		
e1	0.475 BSC.			0.019 BSC.		
e2	1.450 BSC.			0.057 BSC.		
e3	0.450 BSC.			0.018 BSC.		
e4	1.350 BSC.			0.053 BSC.		
E	1.90	2.00	2.10	0.075	0.079	0.083
L	0.30	0.40	0.50	0.012	0.016	0.020

ECN: E24-0430-Rev. A, 26-Aug-2024

DWG: 6120

Notes

- Use millimeters as the primary measurement
 - Dimensioning and tolerances conform to ASME Y14.5M.-1994
 - Package warpage max. 0.08 mm
- (1) Dimension b applies to plated terminal and is measured between 0.20 mm and 0.25 mm from terminal tip
- (2) The pin #1 identifier must be existed on the top surface of the package by using identification mark or other feature of package body
- (3) Exact shape and size of this feature is optional
- (4) Applied only for terminals