



High Speed Quad SPST CMOS Analog Switch

DESCRIPTION

The DG201HS is an improved monolithic device containing four independent analog switches. It is designed to provide high speed, low error switching of analog signals. Combining low on-resistance (25 Ω) with high speed (t_{on}: 38 ns), the DG201HS is ideally suited for high speed data acquisition requirements.

To achieve high voltage ratings and superior switching performance, the DG201HS is built on a proprietary high-voltage silicon-gate process. An epitaxial layer prevents latchup.

Each switch conducts equally well in both directions when on, and blocks input voltages to the supply values, when off.

BENEFITS

- Faster throughput
- Higher accuracy
- Reduced pedestal error
- Upgrades existing designs
- Simple interfacing
- Replaces HI201HS, ADG201HS
- Space savings (TSSOP)

FEATURES

- Fast switching-t_{on}: 38 ns
- Low on-resistance: 25 Ω
- Low leakage: 100 pA
- Low charge injection
- TTL/CMOS logic compatible
- Single supply compatibility
- High current rating: -30 mA
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note


* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details



APPLICATIONS

- Data acquisition
- Hi-Rel systems
- Sample and hold circuits
- Communication systems
- Automatic test equipment
- Integrator reset circuits
- Choppers
- Gain switching
- Avionics

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE	
LOGIC	SWITCH
0	On
1	Off

Note

- Logic "0" ≤ 0.8 V; logic "1" ≥ 2.4 V

ORDERING INFORMATION		
TEMP. RANGE	PACKAGE	PART NUMBER
-40 °C to +85 °C	16-pin narrow SOIC	DG201HSDY-E3 DG201HSDY-T1-E3
	16-pin TSSOP	DG201HSDQ-E3 DG201HSDQ-T1-E3
	16-pin plastic DIP	DG201HSDJ-E3

ABSOLUTE MAXIMUM RATINGS			
PARAMETER		LIMIT	UNIT
Voltages referenced, V+ to V-		44	V
GND		25	
Digital inputs ^a , V _S , V _D		(V-) - 4 to (V+) + 4 or 30 mA, whichever occurs first	
Current (any terminal)		30	mA
Peak current S or D (pulsed at 1 ms, 10 % duty cycle max.)		100	
Storage temperature	(A suffix)	-65 to +150	°C
	(D suffix)	-65 to +125	
Power dissipation (package) ^b	16-pin plastic DIP ^c	470	mW
	16-pin narrow body SOIC and TSSOP ^e	600	

Notes

- Signals on S_X, D_X, or IN_X exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings
- All leads welded or soldered to PC board
- Derate 6 mW/°C above 75 °C
- Derate 12 mW/°C above 75 °C
- Derate 7.6 mW/°C above 75 °C


SCHEMATIC DIAGRAM (typical channel)


Fig. 1



SPECIFICATIONS ^a										
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS SPECIFIED V ₊ = 15 V, V ₋ = -15 V V _{IN} = 3 V, 0.8 V ^f	TEMP. ^b	TYP. ^c	A SUFFIX -55 °C to +125 °C		D SUFFIX -40 °C to +85 °C		UNIT	
					MIN. ^d	MAX. ^d	MIN. ^d	MAX. ^d		
Analog Switch										
Analog signal range ^e	V _{ANALOG}		Full	-	V-	V+	V-	V+	V	
Drain-source on-resistance	R _{DS(on)}	V _D = ± 10 V, I _S = 1 mA	Room	25	-	50	-	50	Ω	
R _{DS(on)} match	ΔR _{DS(on)}		Full	-	-	75	-	75		
Source off leakage current	I _{S(off)}	V ₊ = 16.5 V, V ₋ = -16.5 V, V _D = ± 15.5 V, V _S = ± 15.5 V	Room	0.1	-1	1	-1	1	nA	
Drain off leakage current	I _{D(off)}		Full	-	-60	60	-20	20		
Drain on leakage current	I _{D(on)}		Room	0.1	-1	1	-1	1		
			Full	-	-60	60	-20	20		
Digital Control										
Input voltage high	V _{INH}		Full	-	2.4	-	2.4	-	V	
Input voltage low	V _{INL}		Full	-	-	0.8	-	0.8		
Input current	I _{INH} or I _{INL}	V _{IN} under test = 0.8 V, 3 V	Full	-	-1	1	-1	1	μA	
Input capacitance	C _{IN}		Full	5	-	-	-	-	pF	
Dynamic Characteristics										
Turn-on time	t _{on}	R _L = 1 kΩ, C _L = 35 pF, V _S = ± 10 V, V _{INH} = 3 V, see Fig. 2	Room	48	-	60	-	60	ns	
			Full	-	-	75	-	75		
Turn-off time	t _{off1}		Room	30	-	50	-	50		
			Full	-	-	70	-	70		
	t _{off2}		Room	150	-	-	-	-		
Output setting time to 0.1 %	t _S		Room	180	-	-	-	-		
Charge injection	Q	C _L = 1 nF, V _S = 0 V, V _{GEN} = 0 V, R _{gen} = 0 Ω	Room	-5	-	-	-	-	pC	
Source-off capacitance	C _{S(off)}	V _S = V _D = 0 V, f = 1 MHz	Room	8	-	-	-	-	pF	
Drain-off capacitance	C _{D(off)}		Room	8	-	-	-	-		
Channel on capacitance	C _{D(on)}		Room	30	-	-	-	-		
Drain to source capacitance	C _{DS(off)}		Room	0.5	-	-	-	-		
Off isolation	OIRR	C _L = 10 pF, R _L = 1 kΩ, f = 100 kHz	Room	85	-	-	-	-	dB	
Channel-to-channel crosstalk	X _{TALK}	Any other channel switches, C _L = 10 pF, R _L = 1 kΩ, f = 100 kHz	Room	100	-	-	-	-		
Power Supply										
Positive supply current	I ₊	V ₊ = 15 V, V ₋ = -15 V, V _{IN} = 0 V or 5 V	Room	4.5	-	-	-	-	mA	
			Full	-	-	10	-	10		
Negative supply current	I ₋		Room	3.5	-	-	-	-		
			Full	-	-6	-	-6	-		
Power consumption ^c	P _C		Room	-	-	240	-	240		mW
			Full	-	-	240	-	240		


Notes

- a. Refer to "Process Option Flowchart"
- b. Room = 25 °C, full = as determined by the operating temperature suffix
- c. Typical values are for "Design Aid Only", not guaranteed nor subject to production testing
- d. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
- e. Guaranteed by design, not subject to production test
- f. V_{IN} = input voltage to perform proper function


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




$R_{DS(on)}$ vs. V_D and Power Supply Voltages




$R_{DS(on)}$ vs. V_D and Temperature




$R_{DS(on)}$ vs. V_D and Single Power Supply Voltages



Leakage Currents vs. Temperature




Input Switching Threshold vs. Supply Voltage




Switching Time vs. Power Supply Voltage




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Switching Times vs. Temperature




Switching Times vs. Temperature



Switching Times vs. Temperature




Charge Injection vs. Source Voltage



Off Isolation vs. Frequency

TEST CIRCUITS



C_L (includes fixture and stray capacitance)

$$V_O = V_S \frac{R_L}{R_L + r_{DS(on)}}$$

Fig. 2 - Switching Time








Fig. 3 - Charge Injection



$$\text{Off Isolation} = 20 \log \left| \frac{V_S}{V_O} \right|$$

Fig. 4 - Off Isolation




$$X_{\text{TALK}} \text{ Isolation} = 20 \log \left| \frac{V_S}{V_O} \right|$$

C = RF bypass

Fig. 5 - Crosstalk

APPLICATIONS

A high-speed, low-glitch analog switch such as Vishay Siliconix's DG201HS improves the accuracy and shortens the acquisition and settling times of a sample-and-hold circuit.





PRODUCT SUMMARY			
Part number	DG201HS	DG201HS	DG201HS
Status code	2	2	2
Configuration	SPST x 4, NC	SPST x 4, NC	SPST x 4, NC
Single supply min. (V)	5	5	5
Single supply max. (V)	36	36	36
Dual supply min. (V)	5	5	5
Dual supply max. (V)	22	22	22
On-resistance (Ω)	25	25	25
Charge injection (pC)	-5	-5	-5
Source on capacitance (pF)	-	-	-
Source off capacitance (pF)	8	8	8
Leakage switch on typ. (nA)	0.1	0.1	0.1
Leakage switch off max. (nA)	1	1	1
-3 dB bandwidth (MHz)	-	-	-
Package	TSSOP-16	SO-16 (narrow) AS	Plastic DIP-16
Functional circuit / applications	Multi purpose, instrumentation, medical and healthcare	Multi purpose, instrumentation, medical and healthcare	Multi purpose, instrumentation, medical and healthcare
Interface	Parallel	Parallel	Parallel
Single supply operation	Yes	Yes	Yes
Dual supply operation	Yes	Yes	Yes
Turn on time max. (ns)	50	50	50
Crosstalk and off isolation	-85	-85	-85

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?61555.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.