




Case Outline for PowerPAK® 8x8 BWL



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.90	1.00	1.10	0.035	0.039	0.043
A1	0.00	-	0.05	0.000	-	0.002
A2	0.20 ref.			0.008 ref.		
A3	0.10 min.			0.004 min.		
b	0.90	1.00	1.10	0.035	0.039	0.043
D	7.90	8.00	8.10	0.311	0.315	0.319
D1	4.98	5.08	5.18	0.196	0.200	0.204
D2-1	0.25	0.35	0.45	0.010	0.014	0.018
e	2.00 BSC.			0.079 BSC.		
e1	6.00 BSC.			0.236 BSC.		
e2	2.78 BSC.			0.109 BSC.		
e3	1.20 BSC.			0.047 BSC.		
E	7.90	8.00	8.10	0.311	0.315	0.319
E1	6.80	6.90	7.00	0.268	0.272	0.276
L	0.65	0.75	0.85	0.026	0.030	0.033
L1	0.55 ref.			0.022 ref.		
L2	0.035 ref.			0.001 ref.		
L3	0.60 ref.			0.024 ref.		
K	0.50 ref.			0.020 ref.		
K1	1.22 ref.			0.048 ref.		
K2	1.58 ref.			0.062 ref.		
ECN: T23-0471-Rev. A, 11-Dec-2023						
DWG: 6112						

Note

- Use millimeters as the primary measurement