




Case Outline for Low Voltage PowerPAK® 10 x 12



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	2.30	2.30	2.40	0.087	0.091	0.094
b	0.70	0.80	0.90	0.028	0.031	0.035
b1	9.40			0.366	0.0370	0.074
b2	0.46 ref.			0.018 ref.		
c	0.40	0.48	0.60	0.016	0.019	0.024
D	10.28	10.38	10.48	0.405	0.409	0.413
D2	2.45 ref.			0.096 ref.		
e	1.20 BSC.			0.047 BSC.		
E	9.80	9.90	10.00	0.386	0.390	0.394
E1	7.40 ref.			0.291 ref.		
E5	8.20	8.40	8.60	0.323	0.331	0.339
H	11.58	11.68	11.78	0.452	0.460	0.468
H2	6.41	6.61	6.81	0.252	0.260	0.268
L	1.70	1.90	2.10	0.067	0.075	0.083
L1	0.50	0.70	0.90	0.020	0.028	0.035
L2	0.40	0.60	0.80	0.016	0.024	0.031
L3	0.70 ref.			0.028 ref.		
θ	11 ° ref.			11 ° ref.		
aaa	0.10			0.004		
ccc	0.20			0.008		
ddd	0.25			0.010		
eee	0.20			0.008		
ECN: E24-0179-Rev. B, 01-Apr-2024						
DWG: 6114						

Note

- Use millimeters as the primary measurement