




## Case Outline for PowerPAIR® 3 x 3FS BWL



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A <sup>(4)</sup>	0.65	0.75	0.85	0.026	0.030	0.033
A1	0.00	-	0.05	0.000	-	0.002
A2	0.20 ref.			0.008 ref.		
b <sup>(3)</sup>	0.27	0.32	0.37	0.011	0.013	0.015
b1	0.27 ref.			0.011 ref.		
D	3.20	3.30	3.40	0.126	0.130	0.134
e	0.65 BSC			0.026 BSC		
e1	1.95 BSC			0.077 BSC		
E	3.20	3.30	3.40	0.126	0.130	0.134
L	0.44	0.54	0.64	0.017	0.021	0.025
L1	0.15	0.25	0.35	0.006	0.010	0.014
D2-1	1.38	1.48	1.58	0.054	0.058	0.062
D2-2	1.09	1.19	1.29	0.043	0.047	0.051
E2-1	1.33	1.43	1.53	0.052	0.056	0.060
E2-2	0.10	0.20	0.30	0.004	0.008	0.012
K	0.35 ref.			0.014 ref.		
K1	0.44 ref.			0.017 ref.		

ECN: T24-0047-Rev. C, 05-Feb-2024  
 DWG: 6095

**Notes**

- (1) The pin #1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body
- (2) Exact shape and size of this feature is optional
- (3) Dimension b applies to plated terminal and is measured between 0.20 mm and 0.25 mm from terminal tip
- (4) Applied only for terminals
- Use millimeters as the primary measurement
- Dimensioning and tolerances conform to ASME Y14.5M-1994
- Package warpage max. 0.08 mm