




Case Outline for High Voltage PowerPAK® 10 x 12



DIM.	MILLIMETERS		
	MIN.	NOM.	MAX.
A	2.10	-	2.50
b	0.60	-	1.00
b1	9.60	-	10.00
b2	0.26	-	0.66
c	0.30	-	0.70
D	10.23	-	10.63
D2	3.00	3.30	3.60
E	9.70	9.90	10.10
E1	7.90	8.10	8.30
e	1.20 BSC		
H	11.48	11.68	11.88
H1	6.75	6.95	7.15
N	-	8	-
J	2.95	3.15	3.35
K1	3.98	4.18	4.38
L	1.40	1.60	1.80
L1	0.50	0.70	0.90
L2	0.40	0.60	0.80
L4	0.95	1.15	1.35
θ	4 °	7 °	10 °

ECN: E21-0604-Rev. B, 25-Oct-2021
 DWG: 6091

Notes

- Dimensioning and tolerances conform to ASME Y14.5M-1994
- All dimensions are in millimeters. Angles are in degree
- Coplanarity applies to the exposed head slug as well as the terminal
- Radius on terminal is optional