


uDFN4L - 1.1 mm x 1.1 mm Case Outline



DIMENSION	MILLIMETERS ⁽¹⁾			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.50	0.55	0.60	0.020	0.022	0.024
A1	0	-	0.05	0	-	0.002
A3	0.15 REF			0.006 REF		
b	0.18	0.25	0.30	0.007	0.010	0.012
D	1.10 BSC			0.043 BSC		
e	0.65 BSC			0.026 BSC		
E	1.10 BSC			0.043 BSC		
L	0.30	0.40	0.50	0.012	0.016	0.020
θ	0°	-	12°	0°	-	12°
N ⁽³⁾	4			4		
Ne ⁽³⁾	2			2		

Notes

- (1) Use millimeters as the primary measurement.
- (2) Dimensioning and tolerances conform to ASME Y14.5M. - 1994.
- (3) N is the number of terminals. Ne is the number of terminals in E site.
- (4) Dimensions b applies to plated terminal and is measured between 0.15 mm and 0.30 mm from terminal tip.
- (5) The pin 1 identifier must be existed on the top surface of the package by using identification mark or other feature of package body.
- (6) Package warpage max. 0.05 mm.

ECN: S13-1370-Rev. A, 24-Jun-13
DWG: 6015