


MICRO FOOT® 0.8 x 0.8 CARRIER TAPE



Version	A ₀	B ₀	K ₀
-1	0.88 ± 0.03	0.88 ± 0.03	0.44 ± 0.03

Notes

- 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
- Camber not to exceed 1 mm in 100 mm, camber also not to exceed 1 cm in 1 m actually.
- Material: 0.25 mm ± 0.02 mm thickness.
- Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- Pocket center and pocket hole center must be same position.
- Vishay part number must be labeled at all reels of cover and carrier tape.
- Surface resistivity: 1x10⁴ to 1x10¹¹ Ω.
- No any particle with more than 0.2 mm is allowed.

QUANTITY PER REEL	
T2	3000

ECN: C23-0767-Rev. H, 03-Jul-2023
 DWG: 93-5268-X