



# Automotive N-Channel 40 V (D-S) 175 °C MOSFET





RoHS COMPLIANT HALOGEN FREE

PRODUCT SUMMARY	
V <sub>DS</sub> (V)	40
R <sub>DS(on)</sub> (Ω) at V <sub>GS</sub> = 10 V	0.0018
I <sub>D</sub> (A)	200
Configuration	Single
Package	TO-263-7L

## FEATURES

- TrenchFET® power MOSFET
- Package with low thermal resistance
- 100 % R<sub>g</sub> and UIS tested
- AEC-Q101 qualified <sup>d</sup>
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



## ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25 °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V <sub>DS</sub>	40	V
Gate-Source Voltage	V <sub>GS</sub>	± 20	
Continuous Drain Current	I <sub>D</sub>	T <sub>C</sub> = 25 °C <sup>a</sup>	200
		T <sub>C</sub> = 125 °C	192
Continuous Source Current (Diode Conduction) <sup>a</sup>	I <sub>S</sub>	200	A
Pulsed Drain Current <sup>b</sup>	I <sub>DM</sub>	600	
Single Pulse Avalanche Current	I <sub>AS</sub>	85	
Single Pulse Avalanche Energy	E <sub>AS</sub>	361	mJ
Maximum Power Dissipation <sup>b</sup>	P <sub>D</sub>	T <sub>C</sub> = 25 °C	375
		T <sub>C</sub> = 125 °C	125
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C

## THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Junction-to-Ambient	R <sub>thJA</sub>	40	°C/W
Junction-to-Case (Drain)	R <sub>thJC</sub>	0.4	

### Notes

- Package limited.
- Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2 %.
- When mounted on 1" square PCB (FR4 material).
- Parametric verification ongoing.



SPECIFICATIONS ( $T_C = 25\text{ }^\circ\text{C}$ , unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
<b>Static</b>							
Drain-Source Breakdown Voltage	$V_{DS}$	$V_{GS} = 0\text{ V}$ , $I_D = 250\text{ }\mu\text{A}$		40	-	-	V
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$ , $I_D = 250\text{ }\mu\text{A}$		2.5	3.0	3.5	
Gate-Source Leakage	$I_{GSS}$	$V_{DS} = 0\text{ V}$ , $V_{GS} = \pm 20\text{ V}$		-	-	$\pm 100$	nA
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{GS} = 0\text{ V}$	$V_{DS} = 40\text{ V}$	-	-	1	$\mu\text{A}$
		$V_{GS} = 0\text{ V}$	$V_{DS} = 40\text{ V}$ , $T_J = 125\text{ }^\circ\text{C}$	-	-	50	
		$V_{GS} = 0\text{ V}$	$V_{DS} = 40\text{ V}$ , $T_J = 175\text{ }^\circ\text{C}$	-	-	250	
On-State Drain Current <sup>a</sup>	$I_{D(on)}$	$V_{GS} = 10\text{ V}$	$V_{DS} \geq 5\text{ V}$	200	-	-	A
Drain-Source On-State Resistance <sup>a</sup>	$R_{DS(on)}$	$V_{GS} = 10\text{ V}$	$I_D = 30\text{ A}$	-	0.0015	0.0018	$\Omega$
		$V_{GS} = 10\text{ V}$	$I_D = 30\text{ A}$ , $T_J = 125\text{ }^\circ\text{C}$	-	-	0.0028	
		$V_{GS} = 10\text{ V}$	$I_D = 30\text{ A}$ , $T_J = 175\text{ }^\circ\text{C}$	-	-	0.0034	
Forward Transconductance <sup>b</sup>	$g_{fs}$	$V_{DS} = 15\text{ V}$ , $I_D = 30\text{ A}$		-	198	-	S
<b>Dynamic <sup>b</sup></b>							
Input Capacitance	$C_{iss}$	$V_{GS} = 0\text{ V}$	$V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$	-	13 880	17 350	$\mu\text{F}$
Output Capacitance	$C_{oss}$			-	1414	1770	
Reverse Transfer Capacitance	$C_{rss}$			-	840	1050	
Total Gate Charge <sup>c</sup>	$Q_g$	$V_{GS} = 10\text{ V}$	$V_{DS} = 20\text{ V}$ , $I_D = 120\text{ A}$	-	206	310	nC
Gate-Source Charge <sup>c</sup>	$Q_{gs}$			-	50	-	
Gate-Drain Charge <sup>c</sup>	$Q_{gd}$			-	44	-	
Gate Resistance	$R_g$	f = 1 MHz		0.25	0.8	1.8	$\Omega$
Turn-On Delay Time <sup>c</sup>	$t_{d(on)}$	$V_{DD} = 20\text{ V}$ , $R_L = 0.17\text{ }\Omega$ $I_D \cong 120\text{ A}$ , $V_{GEN} = 10\text{ V}$ , $R_g = 1\text{ }\Omega$		-	26	39	ns
Rise Time <sup>c</sup>	$t_r$			-	21	32	
Turn-Off Delay Time <sup>c</sup>	$t_{d(off)}$			-	68	102	
Fall Time <sup>c</sup>	$t_f$			-	12	18	
<b>Source-Drain Diode Ratings and Characteristics <sup>b</sup></b>							
Pulsed Current <sup>a</sup>	$I_{SM}$			-	-	600	A
Forward Voltage	$V_{SD}$	$I_F = 80\text{ A}$ , $V_{GS} = 0\text{ V}$		-	0.86	1.5	V


**Notes**

- Pulse test; pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$ .
- Guaranteed by design, not subject to production testing.
- Independent of operating temperature.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




Transfer Characteristics



Transconductance









On-Resistance vs. Drain Current



Capacitance




TYPICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C, unless otherwise noted)






**THERMAL RATINGS** ( $T_A = 25\text{ }^\circ\text{C}$ , unless otherwise noted)




**Safe Operating Area**



**Normalized Thermal Transient Impedance, Junction-to-Ambient**



**THERMAL RATINGS** ( $T_A = 25\text{ }^\circ\text{C}$ , unless otherwise noted)



**Normalized Thermal Transient Impedance, Junction-to-Case**

**Note**

- The characteristics shown in the two graphs
  - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)
  - Normalized Transient Thermal Impedance Junction-to-Case (25 °C)
 are given for general guidelines only to enable the user to get a “ball park” indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions.

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?67184](http://www.vishay.com/ppg?67184).




REVISION HISTORY <sup>a</sup>		
REVISION	DATE	DESCRIPTION OF CHANGE
B	04-Aug-15	• Revised R <sub>g</sub> minimum limit

**Note**

a. As of April 2014

## D<sup>2</sup>PAK (TO-263-7L) Case Outline



DETAIL A (ROTATED 90°) SECTION A-A


### Notes

1. Plane B includes maximum features of heat sink tab and plastic.
2. No more than 25 % of L1 can fall above seating plane by max. 8 mils.
3. Pin to pin coplanarity max. 4 mils.
4. Lead thickness 25 mils.
5. For SUM part numbers lead thickness is 24 mils to 29 mils.
6. For reference only.
7. Use inches as the primary measurement.
8. This feature is only for SUM.

DIM.	INCHES		MILLIMETERS	
	MIN.	MAX.	MIN.	MAX.
A	0.160	0.190	4.064	4.826
b	0.020	0.039	0.508	0.990
b1	0.020	0.035	0.508	0.889
b2	0.045	0.055	1.143	1.397
c* SUB	0.012	0.018	0.305	0.457
c* SUM	0.022	0.028	0.559	0.711
c1	0.018	0.025	0.457	0.635
c2	0.045	0.055	1.143	1.397
D	0.340	0.380	8.636	9.652
D1	0.220	0.240	5.588	6.096
D2	0.038	0.042	0.965	1.067
D3	0.045	0.055	1.143	1.397
E	0.380	0.410	9.652	10.414
E1	0.245	-	6.223	-
E2	0.072	0.078	1.829	1.981
e	0.050 BSC		1.27 BSC	
K	0.045	0.055	1.143	1.397
L	0.575	0.625	14.605	15.875
L1	0.090	0.110	2.286	2.794
L2	0.040	0.055	1.016	1.397
L3	0.050	0.070	1.270	1.778
L4	0.010 BSC		0.254 BSC	
M	-	0.002	-	0.050
ECN: T13-0709-Rev. B, 30-Sep-13				
DWG: 6006				



## Recommended Land Pattern D<sup>2</sup>PAK (TO-263-7L)





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.