

# Thick Film Chip Resistors, High Resistance Value



## FEATURES

- High resistance values up to 3 G $\Omega$
- Automatic placement capability
- Termination style: 3-sided wraparound termination or single termination flip chip available
- Tape and reel packaging available
- Internationally standardized sizes, custom sizes available
- Suitable for solderable, epoxy bondable, or wire bondable applications
- Termination material: solder-coated nickel barrier or solder coated non-magnetic terminations standard; gold terminations available
- Multiple styles, termination materials and configurations, allow wide design flexibility
- Epoxy bondable or wire bondable non-magnetic terminations available
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


 Available  
**RoHS\***  
 Available

**HALOGEN**  
**FREE**

### Note

\* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

## STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CASE SIZE	POWER RATING <sup>(1)</sup> $P_{70^{\circ}\text{C}}$ W	MAX. WORKING VOLTAGE <sup>(2)</sup> V	RESISTANCE RANGE <sup>(3)</sup> $\Omega$	TOLERANCE $\pm$ %	TEMPERATURE COEFFICIENT $\pm$ ppm/ $^{\circ}\text{C}$
RCHR0805	0805	Contact factory	175	500K to 1G	5, 10, 25	500
RCHR1005	1005	Contact factory	200	500K to 2G	5, 10, 25	500
RCHR1206	1206	Contact factory	300	1M to 3G	5, 10, 25	500

### Notes

- For non-standard sizes, lower values or higher power rating requirement, contact factory.
- (1) Not specified as voltage is always limiting. Due to the high resistance values, the power dissipation is always small.
- (2) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.
- (3) Resistance values calibrated at 10 V<sub>DC</sub>. Calibration at other voltages available upon request.

## TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	RCHR0805	RCHR1005	RCHR1206
Rated dissipation at 70 $^{\circ}\text{C}$	W	Contact factory	Contact factory	Contact factory
Limiting element voltage	V $\equiv$	175	200	300
Insulation resistance	$\Omega$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$
Category temperature range	$^{\circ}\text{C}$	-55 to +155	-55 to +155	-55 to +155
Weight/1000 (typical)	g	6.4	8.3	12.3

## VOLTAGE COEFFICIENT OF RESISTANCE

MODEL	VALUE ( $\Omega$ )	VCR (ppm/V)	FURTHER INSTRUCTIONS
RCHR0805	500K to 1G	5	
RCHR1005	500K to 1G	10	Values over 1G, consult factory
RCHR1206	1M to 1G	15	Values over 1G, consult factory

## GLOBAL PART NUMBER INFORMATION

Global Part Numbering: RCHR1206AF750MJP EW (preferred part number format)

GLOBAL MODEL	SIZE	TERM STYLE	TERM MATERIAL	RESISTANCE VALUE	TOLERANCE	TCR	SOLDER TERMINATION	PACKAGING
RCHR	0805 1005 1206	A = 3-sided B = Top only	F = Nickel barrier G = Non-magnetic C = Gold	K = k $\Omega$ M = M $\Omega$ G = G $\Omega$  110K = 110 k $\Omega$ 49M9 = 49.9 M $\Omega$ 3G00 = 3 G $\Omega$	J = $\pm$ 5 % K = $\pm$ 10 % V = $\pm$ 25 %	P = 500 ppm	E = Sn100 F = Sn95/Ag5, HSD N = No solder S = Sn62/Pb36/Ag2, HSD T = Sn90/Pb10	B = Bulk F = T/R (full reel) 1 = T/R (1000 pcs) 5 = T/R (500 pcs) T = T/R (250 pcs min.) W = Waffle tray

### Note

- For additional information on packaging, refer to the Surface Mount Resistor Packaging document ([www.vishay.com/doc?31543](http://www.vishay.com/doc?31543)).

DIMENSIONS in inches (millimeters)					
Termination style A (3-sided wraparound)	Termination style B (top conductor only)	MODEL	LENGTH <sup>(1)</sup> (L)	WIDTH <sup>(1)</sup> (W)	THICKNESS <sup>(1)</sup> (T)
		RCHR0805	0.075 ± 0.006 (1.90 ± 0.15)	0.050 ± 0.006 (1.27 ± 0.15)	0.025 ± 0.002 (0.64 ± 0.05)
		RCHR1005	0.100 ± 0.006 (2.54 ± 0.15)	0.050 ± 0.006 (1.27 ± 0.15)	0.025 ± 0.002 (0.64 ± 0.05)
		RCHR1206	0.125 ± 0.006 (3.18 ± 0.15)	0.063 ± 0.006 (1.60 ± 0.15)	0.025 ± 0.002 (0.64 ± 0.05)


**Note**

<sup>(1)</sup> All dimensions are before solder coating.

TYPE	TERMINATION MATERIAL	TERMINATION STYLE	TERMINATION STYLE/ MATERIAL CODE	SOLDER TERMINATION CODE
Solderable	Nickel barrier	3-sided (wraparound)	AF	E or T (standard); F or S (optional) <sup>(2)</sup>
Solderable	Non-magnetic	3-sided (wraparound)	AG	E or T (standard); F or S (optional) <sup>(2)</sup>
Wire bondable/ Epoxy bondable	Gold	Top only (flip chip)	BC	N

**Note**

<sup>(2)</sup> Standard solder plating for the nickel barrier and non-magnetic parts is solder terminations E or T. Hot solder dipped terminations F or S are also available.



MATERIAL SPECIFICATIONS	
Resistive element	Ruthenium oxide
Encapsulation	Epoxy
Substrate	96 % alumina
Termination	Solder-coated nickel barrier or solder coated non-magnetic terminations standard. Gold terminations available.
Solder finish	Pure tin or tin/lead solder alloys standard. Tin/silver or tin/lead/silver solder alloys available.

PERFORMANCE			
TEST	CONDITIONS OF TEST	TEST LIMITS	TEST RESULTS (TYPICAL TEST LOTS)
Life	MIL-STD-202, method 108 1000 h rated power at + 70 °C	± 2 %	≤ ± 0.50 %
Short time overload	MIL-PRF-55342, paragraph 4.8.6	± 0.5 %	≤ ± 0.02 %
High temperature exposure	MIL-PRF-55342, paragraph 4.8.7	± 1 %	≤ ± 0.50 %
Low temperature operation	MIL-PRF-55342, paragraph 4.8.5	± 0.5 %	≤ ± 0.02 %
Resistance to bonding exposure	MIL-PRF-55342, paragraph 4.8.8.2	± 0.5 %	≤ ± 0.05 %
Moisture resistance	MIL-STD-202, method 106	± 1 %	≤ ± 0.06 %
Solder mounting integrity	MIL-PRF-55342, paragraph 4.8.13.1	No evidence of mechanical damage	
Solderability	MIL-STD-202, method 208	95 % coverage	



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.