


Thick Film Planar Dividers, Through-Hole, High Voltage



FEATURES

- 30 000 V capability
- Very low voltage coefficient to less than 1 ppm/V
- Outstanding stability under adverse conditions
- Stable cermet resistive elements bonded to a high-purity alumina substrate
- Tough epoxy-based coating and high voltage stability
- Custom designs built from customer supplied schematics available
- Custom dividers available with leadwire terminals or with leadless conductive pads
- Maximum resistance ratio of 1000:1 (for ratio's over 1000:1, contact factory)
- Minimum resistance ratio of 40:1
- TCR tracking to ± 25 ppm/ $^{\circ}$ C
- Resistors available, see Vishay Techno's TR datasheet (www.vishay.com/doc?68000)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

HALOGEN FREE

APPLICATIONS

Applications include power supplies, transformers and any application requiring operation within an environment where high voltages are used.

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS								
GLOBAL MODEL / SIZE	POWER RATING $P_{25^{\circ}\text{C}}$ W	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V	RESISTANCE RANGE R_1 ⁽²⁾⁽³⁾ Ω	ABSOLUTE TOLERANCE \pm %	ABSOLUTE TEMPERATURE COEFFICIENT \pm ppm/ $^{\circ}$ C	RATIO TOLERANCE \pm %	TCR TRACKING ⁽⁴⁾ \pm ppm/ $^{\circ}$ C	RATIO MAX. ⁽⁵⁾
TDA03	0.25	0.8K	300 to 3M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				3.01M to 25M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX03		2.5K	25M to 250M	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				260M to 2G	5, 10, 20	200	1, 2, 5	25, 50, 100
			2.1G to 10G	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1
TDA05	0.5	4K	500 to 25M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				25.1M to 200M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX05		5K	30M to 1G	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				1.1G to 20G	5, 10, 20	200	1, 2, 5	25, 50, 100
			21G to 100G	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1
TDA10	1	6.5K	1K to 16M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				16.1M to 120M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX10		10K	20M to 1G	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				1.1G to 15G	5, 10, 20	200	1, 2, 5	25, 50, 100
			16G to 1T	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1
TDA15	1.5	12.5K	1.5K to 45M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				45.1M to 340M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX15		15K	60M to 1G	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				1.1G to 35G	5, 10, 20	200	1, 2, 5	25, 50, 100
			36G to 1.5T	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1
TDA20	2	17.5K	2K to 64M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				64.1M to 480M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX20		20K	80M to 1G	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				1.1G to 50G	5, 10, 20	200	1, 2, 5	25, 50, 100
			51G to 2T	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1
TDA30	3	25K	3K to 82M	0.5, 1, 2, 5, 10, 20	100	0.5, 1, 2, 5	25, 50, 100	1000:1
				82.1M to 620M	0.5, 1, 2, 5, 10, 20	200	0.5, 1, 2, 5	25, 50, 100
TDX30		30K	80M to 1G	1, 2, 5, 10, 20	200	1, 2, 5	25, 50, 100	1000:1
				1.1G to 60G	5, 10, 20	200	1, 2, 5	25, 50, 100
			61G to 3T	5, 10, 20	500	1, 2, 5	25, 50, 100	1000:1

Notes

- Custom sizes available
 - Voltage coefficient: typically less than 1 ppm/V (tested per MIL-STD-202)
- (1) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less
 (2) All resistance values are calibrated at 100 V_{DC}. Calibration at other voltages available upon request
 (3) Minimum R_2 value is 50 Ω
 (4) TCR Tracking measured from 0 $^{\circ}$ C to +70 $^{\circ}$ C
 (5) For ratios over 1000:1, contact factory

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: TDA20E100M3300FFEB																	
T	D	A	2	0	E	1	0	0	M	3	3	0	0	F	F	E	B
GLOBAL MODEL	VOLTAGE RATING	SIZE	TCR TRACKING	RESISTANCE VALUE R_1	RATIO R_1/R_2	RATIO TOLERANCE	TOLERANCE	TERMINAL FINISH	PACKAGING								
TD	A = medium voltage X = high voltage	03 05 10 15 20 30	E = 25 ppm H = 50 ppm K = 100 ppm	R = Ω K = k Ω M = M Ω G = G Ω T = T Ω 400R = 400 Ω 10M0 = 10 M Ω 10G7 = 10.7 G Ω	3 digit significant figure, followed by a multiplier 0400 = 40:1 2210 = 221:1 1001 = 1000:1	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	E = Sn100 R = Sn60/Pb40	B = bag								

Notes

- For additional information on packaging, refer to the Through Hole Resistor Packaging document (www.vishay.com/doc?31544)
- The TCR listed in this datasheet is for resistance values up to 1 G Ω . For resistance values > 1 G Ω , please contact factory

MECHANICAL SPECIFICATIONS

Resistive Element: thick film
Substrate: 96 % pure alumina
Encapsulation: epoxy base, conformal coating
Terminals: solder plated copper leads
Terminal Strength: 4.5 pounds pull-test
Power: derated from ambient temperature +25 $^{\circ}\text{C}$

ENVIRONMENTAL SPECIFICATIONS

Temperature Range: -55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$
 (for higher temperature range, consult factory)
Load Life: less than 0.15 %, 1000 h


DIMENSIONS in inches (millimeters)					
Schematic					
Figure 1		Figure 2			
MODEL	A (LENGTH)	B (HEIGHT)	C (OVERALL LEAD SPACING)	D (LEAD DIA.)	E (R_2 LEAD SPACING)
TDA03, TDX03 ⁽¹⁾	0.300 \pm 0.030 (7.62 \pm 0.76)	0.210 \pm 0.021 (5.33 \pm 0.53)	0.200 \pm 0.020 (5.08 \pm 0.51)	0.025 \pm 0.002 (0.64 \pm 0.05)	0.100 \pm 0.010 (2.54 \pm 0.25)
TDA05, TDX05 ⁽¹⁾	0.500 \pm 0.050 (12.70 \pm 1.27)	0.300 \pm 0.030 (7.62 \pm 0.76)	0.400 \pm 0.040 (10.16 \pm 1.02)	0.025 \pm 0.002 (0.64 \pm 0.05)	0.100 \pm 0.010 (2.54 \pm 0.25)
TDA10, TDX10	1.00 \pm 0.100 (25.40 \pm 2.54)	0.350 \pm 0.035 (8.89 \pm 0.89)	0.900 \pm 0.090 (22.86 \pm 2.29)	0.032 \pm 0.002 (0.81 \pm 0.05)	0.200 \pm 0.020 (5.08 \pm 0.51)
TDA15, TDX15	1.50 \pm 0.150 (38.10 \pm 3.81)	0.350 \pm 0.035 (8.89 \pm 0.89)	1.40 \pm 0.140 (35.56 \pm 3.56)	0.032 \pm 0.002 (0.81 \pm 0.05)	0.200 \pm 0.020 (5.08 \pm 0.51)
TDA20, TDX20	2.00 \pm 0.200 (50.80 \pm 5.08)	0.350 \pm 0.035 (8.89 \pm 0.89)	1.90 \pm 0.190 (48.26 \pm 4.83)	0.032 \pm 0.002 (0.81 \pm 0.05)	0.200 \pm 0.020 (5.08 \pm 0.51)
TDA30, TDX30	3.00 \pm 0.300 (76.20 \pm 7.62)	0.400 \pm 0.040 (10.16 \pm 1.02)	2.90 \pm 0.290 (73.66 \pm 7.37)	0.032 \pm 0.002 (0.81 \pm 0.05)	0.200 \pm 0.020 (5.08 \pm 0.51)

Note

- ⁽¹⁾ Refer to Fig. 1 for TDA03, TDX03, TDA05 and TDX05 lead lengths



DERATING





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.