



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR SC-70-6L					
STRESS	SAMPLE SIZE	DEVICE HR./CYC	CONDITION	TOTAL FAILS	FAIL PERCENTAGE
HAST	50	5000	130 °C, 85 % RH	0	0
Pressure Pot	100	9500	121°, 15 PSIG	0	0
Solder DUNK	190	180	260 °C, 10 s	0	0
Temp. Cycle	200	20 000	-55 °C to 150 °C	0	0