




## Dual N-Channel 30 V (D-S) MOSFETs

PRODUCT SUMMARY				
	V <sub>DS</sub> (V)	R <sub>DS(on)</sub> (Ω)	I <sub>D</sub> (A) <sup>a</sup>	Q <sub>g</sub> (Typ.)
Channel-1	30	0.0240 at V <sub>GS</sub> = 10 V	11	3.5 nC
		0.0320 at V <sub>GS</sub> = 4.5 V	11	
Channel-2	30	0.0110 at V <sub>GS</sub> = 10 V	28	6.8 nC
		0.0165 at V <sub>GS</sub> = 4.5 V	28	



**Ordering Information:**  
 SiZ300DT-T1-GE3 (Lead (Pb)-free and Halogen-free)

### FEATURES


- PowerPAIR Optimizes High-Side and Low-Side MOSFETs for Synchronous Buck Converters
- TrenchFET<sup>®</sup> Power Mosfets
- 100 % R<sub>g</sub> and UIS Tested
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
 COMPLIANT  
 HALOGEN  
**FREE**

### APPLICATIONS

- Computing System Power
- POL
- Synchronous Buck Converter



ABSOLUTE MAXIMUM RATINGS (T <sub>A</sub> = 25 °C, unless otherwise noted)					
Parameter	Symbol	Channel-1	Channel-2	Unit	
Drain-Source Voltage	V <sub>DS</sub>	30		V	
Gate-Source Voltage	V <sub>GS</sub>	± 20			
Continuous Drain Current (T <sub>J</sub> = 150 °C)	I <sub>D</sub>	T <sub>C</sub> = 25 °C	11 <sup>a</sup>	28 <sup>a</sup>	A
		T <sub>C</sub> = 70 °C	11 <sup>a</sup>	28 <sup>a</sup>	
		T <sub>A</sub> = 25 °C	9.8 <sup>b, c</sup>	14.9 <sup>b, c</sup>	
		T <sub>A</sub> = 70 °C	7.8 <sup>b, c</sup>	11.9 <sup>b, c</sup>	
Pulsed Drain Current (t = 300 μs)	I <sub>DM</sub>	30	40		
Continuous Source Drain Diode Current	I <sub>S</sub>	T <sub>A</sub> = 25 °C	11 <sup>a</sup>	26	
		T <sub>A</sub> = 25 °C	3.2 <sup>b, c</sup>	3.8 <sup>b, c</sup>	
Avalanche Current	I <sub>AS</sub>	12	15		
Single Pulse Avalanche Energy	E <sub>AS</sub>	7	11	mJ	
Maximum Power Dissipation	P <sub>D</sub>	T <sub>C</sub> = 25 °C	16.7	31	W
		T <sub>C</sub> = 70 °C	10.7	20	
		T <sub>A</sub> = 25 °C	3.7 <sup>b, c</sup>	4.2 <sup>b, c</sup>	
		T <sub>A</sub> = 70 °C	2.4 <sup>b, c</sup>	2.7 <sup>b, c</sup>	
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	- 55 to 150		°C	
Soldering Recommendations (Peak Temperature) <sup>d, e</sup>		260			

Notes:

a. Package limited.

b. Surface mounted on 1" x 1" FR4 board.

c. t = 10 s.

d. See solder profile ([www.vishay.com/doc?73257](http://www.vishay.com/doc?73257)). The PowerPAIR is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.

e. Rework conditions: manual soldering with a soldering iron is not recommended for leadless components.

THERMAL RESISTANCE RATINGS							
Parameter		Symbol	Channel-1		Channel-2		Unit
			Typ.	Max.	Typ.	Max.	
Maximum Junction-to-Ambient <sup>a, b</sup>	$t \leq 10$ s	$R_{thJA}$	27	34	24	30	°C/W
Maximum Junction-to-Case (Drain)	Steady State	$R_{thJC}$	6	7.5	3.2	4	

Notes:

a. Surface mounted on 1" x 1" FR4 board.

b. Maximum under steady state conditions is 69 °C/W for channel-1 and 64 °C/W for channel-2.

SPECIFICATIONS ( $T_J = 25$ °C, unless otherwise noted)							
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit	
<b>Static</b>							
Drain-Source Breakdown Voltage	$V_{DS}$	$V_{GS} = 0, I_D = 250 \mu A$	Ch-1	30			V
		$V_{GS} = 0 V, I_D = 250 \mu A$	Ch-2	30			
$V_{DS}$ Temperature Coefficient	$\Delta V_{DS}/T_J$	$I_D = 250 \mu A$	Ch-1		24		mV/°C
		$I_D = 250 \mu A$	Ch-2		30		
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$	$I_D = 250 \mu A$	Ch-1		- 4.1		
		$I_D = 250 \mu A$	Ch-2		- 5		
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250 \mu A$	Ch-1	1		2.4	V
		$V_{DS} = V_{GS}, I_D = 250 \mu A$	Ch-2	1		2.2	
Gate Source Leakage	$I_{GSS}$	$V_{DS} = 0 V, V_{GS} = \pm 20 V$	Ch-1			$\pm 100$	nA
			Ch-2			$\pm 100$	
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = 30 V, V_{GS} = 0 V$	Ch-1			1	$\mu A$
		$V_{DS} = 30 V, V_{GS} = 0 V$	Ch-2			1	
		$V_{DS} = 30 V, V_{GS} = 0 V, T_J = 55$ °C	Ch-1			5	
		$V_{DS} = 30 V, V_{GS} = 0 V, T_J = 55$ °C	Ch-2			5	
On-State Drain Current <sup>b</sup>	$I_{D(on)}$	$V_{DS} \geq 5 V, V_{GS} = 10 V$	Ch-1	10			A
		$V_{DS} \geq 5 V, V_{GS} = 10 V$	Ch-2	10			
Drain-Source On-State Resistance <sup>b</sup>	$R_{DS(on)}$	$V_{GS} = 10 V, I_D = 9.8 A$	Ch-1		0.0200	0.0240	$\Omega$
		$V_{GS} = 10 V, I_D = 15 A$	Ch-2		0.0090	0.0110	
		$V_{GS} = 4.5 V, I_D = 8.5 A$	Ch-1		0.0265	0.0320	
		$V_{GS} = 4.5 V, I_D = 12 A$	Ch-2		0.0135	0.0165	
Forward Transconductance <sup>b</sup>	$g_{fs}$	$V_{DS} = 15 V, I_D = 9.8 A$	Ch-1		30		S
		$V_{DS} = 15 V, I_D = 15 A$	Ch-2		30		
<b>Dynamic<sup>a</sup></b>							
Input Capacitance	$C_{iss}$	Channel-1 $V_{DS} = 15 V, V_{GS} = 0 V, f = 1$ MHz	Ch-1		400		pF
Output Capacitance	$C_{oss}$		Ch-2		730		
Reverse Transfer Capacitance	$C_{rss}$	Channel-2 $V_{DS} = 15 V, V_{GS} = 0 V, f = 1$ MHz	Ch-1		125		
			Ch-2		155		
Total Gate Charge	$Q_g$	$V_{DS} = 15 V, V_{GS} = 10 V, I_D = 9.8 A$	Ch-1		7.4	12	nC
		$V_{DS} = 15 V, V_{GS} = 10 V, I_D = 15 A$	Ch-2		14.2	22	
		Channel-1 $V_{DS} = 15 V, V_{GS} = 4.5 V, I_D = 9.8 A$	Ch-1		3.5	5.3	
			Ch-2		6.8	11	
Gate-Source Charge	$Q_{gs}$	Channel-2 $V_{DS} = 15 V, V_{GS} = 4.5 V, I_D = 15 A$	Ch-1		1.5		
Gate-Drain Charge	$Q_{gd}$		Ch-2		2.2		
Gate Resistance	$R_g$	$f = 1$ MHz	Ch-1	0.5	2.6	5.2	$\Omega$
			Ch-2	0.5	2.6	5.2	

Notes:

a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width  $\leq 300 \mu s$ , duty cycle  $\leq 2$  %.



<b>SPECIFICATIONS</b> ( $T_J = 25\text{ }^\circ\text{C}$ , unless otherwise noted)								
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit		
<b>Dynamic<sup>a</sup></b>								
Turn-On Delay Time	$t_{d(on)}$	Channel-1 $V_{DD} = 15\text{ V}, R_L = 1.9\ \Omega$ $I_D \cong 8\text{ A}, V_{GEN} = 4.5\text{ V}, R_g = 1\ \Omega$	Ch-1		25	50	ns	
			Ch-2		25	50		
Rise Time	$t_r$		Ch-1		45	90		
			Ch-2		80	160		
Turn-Off Delay Time	$t_{d(off)}$	Channel-2 $V_{DD} = 15\text{ V}, R_L = 1.5\ \Omega$ $I_D \cong 10\text{ A}, V_{GEN} = 4.5\text{ V}, R_g = 1\ \Omega$	Ch-1		10	20		
			Ch-2		20	40		
Fall Time	$t_f$		Ch-1		10	20		
			Ch-2		40	80		
Turn-On Delay Time	$t_{d(on)}$	Channel-1 $V_{DD} = 15\text{ V}, R_L = 1.9\ \Omega$ $I_D \cong 8\text{ A}, V_{GEN} = 10\text{ V}, R_g = 1\ \Omega$	Ch-1		5	10		
			Ch-2		5	10		
Rise Time	$t_r$		Ch-1		10	20		
			Ch-2		20	40		
Turn-Off Delay Time	$t_{d(off)}$	Channel-2 $V_{DD} = 15\text{ V}, R_L = 1.5\ \Omega$ $I_D \cong 10\text{ A}, V_{GEN} = 10\text{ V}, R_g = 1\ \Omega$	Ch-1		10	20		
			Ch-2		15	30		
Fall Time	$t_f$		Ch-1		7	15		
			Ch-2		10	20		
<b>Drain-Source Body Diode Characteristics</b>								
Continuous Source-Drain Diode Current	$I_S$	$T_C = 25\text{ }^\circ\text{C}$	Ch-1			11	A	
			Ch-2					26
Pulse Diode Forward Current <sup>a</sup>	$I_{SM}$		Ch-1			30		
			Ch-2					40
Body Diode Voltage	$V_{SD}$	$I_S = 8\text{ A}, V_{GS} = 0\text{ V}$	Ch-1		0.84	1.2	V	
		$I_S = 10\text{ A}, V_{GS} = 0\text{ V}$	Ch-2		0.82	1.2		
Body Diode Reverse Recovery Time	$t_{rr}$	Channel-1 $I_F = 8\text{ A}, di/dt = 100\text{ A}/\mu\text{s}, T_J = 25\text{ }^\circ\text{C}$	Ch-1		17	35	ns	
			Ch-2		20	40		
Body Diode Reverse Recovery Charge	$Q_{rr}$			Ch-1		9	20	nC
				Ch-2		14	30	
Reverse Recovery Fall Time	$t_a$	Channel-2 $I_F = 10\text{ A}, di/dt = 100\text{ A}/\mu\text{s}, T_J = 25\text{ }^\circ\text{C}$	Ch-1		9.5		ns	
			Ch-2		12.5			
Reverse Recovery Rise Time	$t_b$			Ch-1		7.5		
				Ch-2		7.5		

## Notes:

- a. Guaranteed by design, not subject to production testing.  
 b. Pulse test; pulse width  $\leq 300\ \mu\text{s}$ , duty cycle  $\leq 2\%$ .


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

# SiZ300DT


Vishay Siliconix




## CHANNEL-1 TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature




**CHANNEL-1 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




Threshold Voltage



On-Resistance vs. Gate-to-Source Voltage




Single Pulse Power




Safe Operating Area, Junction-to-Ambient



## CHANNEL-1 TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating\*




Power, Junction-to-Case


\* The power dissipation  $P_D$  is based on  $T_{J(max)} = 150$  °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.



**CHANNEL-1 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)




**Normalized Thermal Transient Impedance, Junction-to-Ambient**




**Normalized Thermal Transient Impedance, Junction-to-Case**


**CHANNEL-2 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)




**Output Characteristics**




**Transfer Characteristics**




**On-Resistance vs. Drain Current**



**Capacitance**



**Gate Charge**




**On-Resistance vs. Junction Temperature**







**CHANNEL-2 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)




**Source-Drain Diode Forward Voltage**




**On-Resistance vs. Gate-to-Source Voltage**



**Threshold Voltage**




**Single Pulse Power**




**Safe Operating Area, Junction-to-Ambient**



**CHANNEL-2 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)



**Current Derating\***




**Power, Junction-to-Case**


\* The power dissipation  $P_D$  is based on  $T_{J(max)} = 150$  °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.



**CHANNEL-2 TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)



**Normalized Thermal Transient Impedance, Junction-to-Ambient**




**Normalized Thermal Transient Impedance, Junction-to-Case**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?267715](http://www.vishay.com/ppg?267715).




### PowerPAIR® 3 x 3 Case Outline



Note  
\* Indicates pin #1 orientation (optional)

DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.70	0.75	0.80	0.028	0.030	0.031
A1	0.00		0.05	0.000		0.002
b	0.35	0.40	0.45	0.014	0.016	0.018
b1	0.20	0.25	0.38	0.008	0.010	0.015
C	0.18	0.20	0.23	0.007	0.008	0.009
D	2.90	3.00	3.10	0.114	0.118	0.122
D2	2.35	2.40	2.45	0.093	0.094	0.096
E	2.90	3.00	3.10	0.114	0.118	0.122
E1	0.94	0.99	1.04	0.037	0.039	0.041
E2	0.47	0.52	0.57	0.019	0.020	0.022
e	0.65 BSC			0.026 BSC		
K	0.25 typ.			0.010 typ.		
K1	0.35 typ.			0.014 typ.		
K2	0.30 typ.			0.012 typ.		
L	0.27	0.32	0.37	0.011	0.013	0.015
ECN: T12-0347-Rev. C, 18-Jun-12						
DWG: 5998						

## RECOMMENDED MINIMUM PAD FOR PowerPAIR® 3 x 3



Recommended PAD for PowerPAIR 3 x 3

Dimensions in millimeters (inches)

Keep-Out 3.5 mm x 3.5 mm for non terminating traces



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.