


## Thick Film Chip Resistors, High Voltage



### FEATURES

- Voltages up to 3000 V
- Automatic placement capability
- Termination style:  
3-sided wraparound termination
- Tape and reel packaging available
- Suitable for solderable applications
- Internationally standardized sizes, custom sizes available
- Termination material: solder-coated nickel barrier
- Non-magnetic termination available
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



Available  
**RoHS\***  
Available  
**HALOGEN FREE**

### LINKS TO ADDITIONAL RESOURCES



### Note

\* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

### STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^{\circ}\text{C}}$ W	MAX. WORKING VOLTAGE <sup>(2)</sup> V	RESISTANCE RANGE <sup>(1)</sup> $\Omega$	TOLERANCE $\pm$ %	TEMPERATURE COEFFICIENT <sup>(3)</sup> $\pm$ ppm/ $^{\circ}\text{C}$
CRMV1206	1206	0.30	1000	150 to 15M	0.5, 1, 2, 5, 10, 20	100
CRMV1210	1210	0.35	1250	300 to 20M	0.5, 1, 2, 5, 10, 20	100
CRMV2010	2010	0.50	2000	500 to 40M	0.5, 1, 2, 5, 10, 20	100
CRMV2510	2510	0.80	2500	1K to 60M	0.5, 1, 2, 5, 10, 20	100
CRMV2512	2512	1.0	3000	1K to 75M	0.5, 1, 2, 5, 10, 20	100

### Notes

- For non-standard sizes, lower values or higher power rating requirement, contact factory
- <sup>(1)</sup> Resistance values calibrated at 10 V<sub>DC</sub>. Calibration at other voltages available upon request
- <sup>(2)</sup> Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less
- <sup>(3)</sup> Reference only: Not for all values specified. Consult factory for your size and value

### TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CRMV1206	CRMV1210	CRMV2010	CRMV2510	CRMV2512
Rated dissipation at 70 °C	W	0.30	0.35	0.50	0.80	1.0
Limiting element voltage	V $\equiv$	1000	1250	2000	2500	3000
Insulation resistance	$\Omega$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$
Category temperature range	$^{\circ}\text{C}$	-55 to +155	-55 to +155	-55 to +155	-55 to +155	-55 to +155
Weight/1000 (typical)	g	12.2	19.6	32.2	39.8	49.7

### VOLTAGE COEFFICIENT OF RESISTANCE

MODEL	VALUE ( $\Omega$ )	VCR (ppm/V)	FURTHER INSTRUCTIONS
CRMV1206	150 to 15M	Consult factory	Consult factory
CRMV1210	300 to 20M	Consult factory	Consult factory
CRMV2010	500 to 40M	Consult factory	Consult factory
CRMV2510	1K to 60M	Consult factory	Consult factory
CRMV2512	1K to 75M	Consult factory	Consult factory


GLOBAL PART NUMBER INFORMATION																	
Global Part Numbering: CRMV1210AF1K00FLET (preferred part number format)																	
C	R	M	V	1	2	1	0	A	F	1	K	0	0	F	L	E	T
GLOBAL MODEL	SIZE	TERMINAL STYLE	TERMINAL MATERIAL	RESISTANCE VALUE	TOLERANCE	TCR	SOLDER TERMINATION	PACKAGING									
CRMV	1206 1210 2010 2510 2512	A = 3-sided	F = nickel barrier G = non-magnetic	R = $\Omega$ K = k $\Omega$ M = M $\Omega$ 110R = 110 $\Omega$ 49K9 = 49.9 k $\Omega$ 10M0 = 10 M $\Omega$	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	K = 100 ppm L = 150 ppm	E = Sn100 N = no solder T = Sn90 / Pb10	B = bulk (250 pcs max.) F = T / R (full reel) 1 = T / R (1000 pcs) 5 = T / R (500 pcs) T = T / R (250 pcs min.) W = waffle tray									

**Note**

- For additional information on packaging, refer to the Surface Mount Resistor Packaging document ([www.vishay.com/doc?31543](http://www.vishay.com/doc?31543))

DIMENSIONS in inches (millimeters)				
<b>TERMINATION STYLE A (3-SIDED WRAPAROUND)</b> 	MODEL	LENGTH (L)	WIDTH (W)	THICKNESS (T)
	CRMV1206	0.125 $\pm$ 0.006 (3.18 $\pm$ 0.15)	0.063 $\pm$ 0.006 (1.60 $\pm$ 0.15)	0.025 $\pm$ 0.004 (0.64 $\pm$ 0.10)
	CRMV1210	0.125 $\pm$ 0.006 (3.18 $\pm$ 0.15)	0.100 $\pm$ 0.006 (2.54 $\pm$ 0.15)	0.025 $\pm$ 0.004 (0.64 $\pm$ 0.10)
	CRMV2010	0.200 $\pm$ 0.006 (5.08 $\pm$ 0.15)	0.100 $\pm$ 0.006 (2.54 $\pm$ 0.15)	0.025 $\pm$ 0.004 (0.64 $\pm$ 0.10)
	CRMV2510	0.250 $\pm$ 0.006 (6.35 $\pm$ 0.15)	0.100 $\pm$ 0.006 (2.54 $\pm$ 0.15)	0.025 $\pm$ 0.004 (0.64 $\pm$ 0.10)
	CRMV2512	0.250 $\pm$ 0.006 (6.35 $\pm$ 0.15)	0.126 $\pm$ 0.006 (3.20 $\pm$ 0.15)	0.025 $\pm$ 0.004 (0.64 $\pm$ 0.10)

TYPE	TERMINATION MATERIAL	TERMINATION STYLE	TERMINATION STYLE / MATERIAL CODE	SOLDER TERMINATION CODE
Solderable	Nickel barrier	3-sided (wraparound)	AF	E or T
	Non-magnetic		AG	



MATERIAL SPECIFICATIONS	
Resistive element	Ruthenium oxide
Encapsulation	Epoxy
Substrate	96 % alumina
Termination	Solder-coated nickel barrier or solder coated non-magnetic terminations
Solder finish	Pure tin or tin / lead solder alloys standard



PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)
Life	MIL-STD-202, method 108 1000 h rated power at +70 °C	$\leq \pm 0.50 \%$
Short time overload	MIL-PRF-55342, paragraph 4.8.6	$\leq \pm 0.02 \%$
Thermal shock	MIL-STD-202, method 107 -55 °C to +150 °C	$\leq \pm 0.50 \%$
Low temperature operation	MIL-PRF-55342, paragraph 4.8.5	$\leq \pm 0.02 \%$
Resistance to bonding exposure	MIL-STD-202, methods 210	$\leq \pm 0.05 \%$
Moisture resistance	MIL-PRF-55342, paragraph 4.8.9	$\leq \pm 0.06 \%$
Solder mounting integrity	MIL-PRF-55342, paragraph 4.8.13 2 kg for 30 s	No evidence of mechanical damage
Solderability	MIL-STD-202, method 208	95 % coverage



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.