



## N-Channel 30-V (D-S) MOSFET with Schottky Diode

### PRODUCT SUMMARY


$V_{DS}$ (V)	$r_{DS(on)}$ ( $\Omega$ )	$I_D$ (A)
30	0.0120 @ $V_{GS} = 10$ V	11
	0.0175 @ $V_{GS} = 4.5$ V	9.5

### FEATURES


- LITTLE FOOT® Plus
- 100%  $R_g$  Tested

### SCHOTTKY PRODUCT SUMMARY

$V_{DS}$ (V)	$V_{SD}$ (V) Diode Forward Voltage	$I_F$ (A)
30	0.53 V @ 3 A	4



Ordering Information: Si4852DY  
Si4852DY-T1 (with Tape and Reel)



### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	10 secs	Steady State	Unit
Drain-Source Voltage (MOSFET)		V <sub>DS</sub>	30		V
Reverse Voltage (Schottky)		V <sub>DA</sub>	30		
Gate-Source Voltage		V <sub>GS</sub>	± 20		
Continuous Drain Current (T <sub>J</sub> = 150°C) (MOSFET) <sup>a</sup>	T <sub>A</sub> = 25°C	I <sub>D</sub>	11	8.7	A
	T <sub>A</sub> = 70°C		9.0	7.0	
Pulsed Drain Current (MOSFET)		I <sub>DM</sub>	50		
Continuous Source Current (MOSFET Diode Conduction) <sup>a</sup>		I <sub>S</sub>	2.3	1.3	
Average Foward Current (Schottky)		I <sub>F</sub>	4.0	2.5	
Pulsed Foward Current (Schottky)		I <sub>FM</sub>	50		
Maximum Power Dissipation (MOSFET) <sup>a</sup>	T <sub>A</sub> = 25°C	P <sub>D</sub>	2.5	1.47	W
	T <sub>A</sub> = 70°C		1.6	0.94	
Maximum Power Dissipation (Schottky) <sup>a</sup>	T <sub>A</sub> = 25°C		2.27	1.38	
	T <sub>A</sub> = 70°C		1.45	0.88	
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	-55 to 150		°C

### THERMAL RESISTANCE RATINGS

Parameter		Symbol	MOSFET		Schottky		Unit
			Typ	Max	Typ	Max	
Maximum Junction-to-Ambient <sup>a</sup>	$t \leq 10$ sec	$R_{thJA}$	40	50	45	55	$^\circ\text{C/W}$
	Steady-State		72	85	75	90	
Maximum Junction-to-Foot (Drain)	Steady-State	$R_{thJF}$	18	22	20	25	

Notes

a. Surface Mounted on 1" x 1" FR4 Board.

**MOSFET SPECIFICATIONS ( $T_J = 25^\circ\text{C}$  UNLESS OTHERWISE NOTED).**

Parameter	Symbol	Test Condition	Min	Typ <sup>a</sup>	Max	Unit
Static						
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250 μA	1			V
Gate-Body Leakage	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> = 24 V, V <sub>GS</sub> = 0 V		0.007	0.100	mA
		V <sub>DS</sub> = 24 V, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 100°C		1.5	10	
		V <sub>DS</sub> = 24 V, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 125°C		6.5	20	
On-State Drain Current <sup>b</sup>	I <sub>D(on)</sub>	V <sub>DS</sub> ≥ 5 V, V <sub>GS</sub> = 10 V	20			A
Drain-Source On-State Resistance <sup>b</sup>	r <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 11 A		0.0100	0.0120	Ω
		V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 9.5 A		0.0145	0.0175	
Forward Transconductance <sup>b</sup>	g <sub>fs</sub>	V <sub>DS</sub> = 15 V, I <sub>D</sub> = 11 A		28		S
Schottky Diode Forward Voltage <sup>b</sup>	V <sub>SD</sub>	I <sub>S</sub> = 3.0 A, V <sub>GS</sub> = 0 V		0.485	0.53	V
		I <sub>S</sub> = 3.0 A, V <sub>GS</sub> = 0 V, T <sub>J</sub> = 125°C		0.416	0.47	
Dynamic <sup>a</sup>						
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> = 15 V, V <sub>GS</sub> = 5 V, I <sub>D</sub> = 11 A		24	35	nC
Gate-Source Charge	Q <sub>gs</sub>			9		
Gate-Drain Charge	Q <sub>gd</sub>			7.5		
Gate Resistance	R <sub>g</sub>		0.5		2.6	Ω
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>DD</sub> = 15 V, R <sub>L</sub> = 15 Ω I <sub>D</sub> ≅ 1 A, V <sub>GEN</sub> = 10 V, R <sub>G</sub> = 6 Ω		17	30	ns
Rise Time	t <sub>r</sub>			10	20	
Turn-Off Delay Time	t <sub>d(off)</sub>			60	100	
Fall Time	t <sub>f</sub>			18	30	
Source-Drain Reverse Recovery Time	t <sub>rr</sub>	I <sub>F</sub> = 3.0 A, di/dt = 100 A/μs		40	70	

## Notes

- a. Guaranteed by design, not subject to production testing.  
b. Pulse test; pulse width  $\leq 300\ \mu\text{s}$ , duty cycle  $\leq 2\%$ .


**SCHOTTKY SPECIFICATIONS ( $T_J = 25^\circ\text{C}$  UNLESS OTHERWISE NOTED)**

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Forward Voltage Drop	$V_F$	$I_F = 3.0\ \text{A}$		0.485	0.53	V
		$I_F = 3.0\ \text{A}, T_J = 125^\circ\text{C}$		0.416	0.47	
Maximum Reverse Leakage Current	$I_{rm}$	$V_r = 24\ \text{V}$		0.007	0.100	mA
		$V_r = 24\ \text{V}, T_J = 100^\circ\text{C}$		1.5	10	
		$V_r = -24\ \text{V}, T_J = 125^\circ\text{C}$		6.4	20	
Junction Capacitance	$C_T$	$V_r = 10\ \text{V}$		115		pF




**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)**


**Output Characteristics**




**Transfer Characteristics**




**On-Resistance vs. Drain Current**




**Capacitance**








**Gate Charge**




**On-Resistance vs. Junction Temperature**



**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)**




**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)**





### Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.