

N-Channel 30-V (D-S), 175 °C MOSFET

PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.004	75 ^a


FEATURES

- TrenchFET[®] Power MOSFETs
- 175 °C Rated Maximum Junction Temperature



Available
RoHS*
COMPLIANT

TO-220AB




DRAIN connected to TAB

G D S

Top View
SUP75N03-04


TO-263



DRAIN connected to TAB

G D S

Top View
SUB75N03-04



N-Channel MOSFET

Ordering Information: SUP75N03-04
SUP75N03-04-E3 (Lead (Pb)-free)
SUB75N03-04
SUB75N03-04-E3 (Lead (Pb)-free)

ABSOLUTE MAXIMUM RATINGS $T_C = 25\text{ }^{\circ}\text{C}$, unless otherwise noted

Parameter	Symbol	Limit	Unit
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current ($T_J = 175\text{ }^{\circ}\text{C}$)	I_D	$T_C = 25\text{ }^{\circ}\text{C}$ 75 ^a	A
		$T_C = 125\text{ }^{\circ}\text{C}$ 75 ^a	
Pulsed Drain Current	I_{DM}	250	
Pulse Diode Forward Current	I_{SM}	250	
Continuous Source Current (Diode Conduction)	I_S	75	
Avalanche Current	I_{AR}	75	mJ
Avalanche Energy	E_{AS}	280	
Repetitive Avalanche Energy ^b	E_{AR}	140	
Maximum Power Dissipation	P_D	$T_C = 25\text{ }^{\circ}\text{C}$ (TO-220AB and TO-263) 187 ^c	W
		$T_A = 25\text{ }^{\circ}\text{C}$ (TO-263) ^d 3.7	
Operating Junction and Storage Temperature Range	T_J, T_{stg}	- 55 to 175	$^{\circ}\text{C}$
Lead Temperature ($1/16$ " from case for 10 sec.)	T_L	300	

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Limit	Unit
Junction-to-Ambient	R_{thJA}	PCB Mount (TO-263) ^d 40	$^{\circ}\text{C/W}$
		Free Air (TO-220AB) 62.5	
Junction-to-Case	R_{thJC}	0.6	

Notes:

a. Package limited.

b. Duty cycle $\leq 1\%$.

c. See SOA curve for voltage derating.

d. When Mounted on 1" square PCB (FR-4 material).

For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>.







* Pb containing terminations are not RoHS compliant, exemptions may apply






SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted						
Parameter	Symbol	Test Conditions	Min	Typ ^a	Max	Unit
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}$, $I_D = 250\text{ }\mu\text{A}$	30			V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 250\text{ }\mu\text{A}$	1		3	
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\text{ V}$, $V_{GS} = \pm 20\text{ V}$			± 500	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 30\text{ V}$, $V_{GS} = 0\text{ V}$			1	μA
		$V_{DS} = 30\text{ V}$, $V_{GS} = 0\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$			50	
		$V_{DS} = 30\text{ V}$, $V_{GS} = 0\text{ V}$, $T_J = 175\text{ }^{\circ}\text{C}$			200	
On-State Drain Current ^b	$I_{D(on)}$	$V_{DS} = 5\text{ V}$, $V_{GS} = 10\text{ V}$	120			A
Drain-Source On-State Resistance ^b	$r_{DS(on)}$	$V_{GS} = 10\text{ V}$, $I_D = 75\text{ A}$		0.0034	0.004	Ω
		$V_{GS} = 4.5\text{ V}$, $I_D = 75\text{ A}$		0.005	0.006	
		$V_{GS} = 10\text{ V}$, $I_D = 25\text{ A}$, $T_J = 125\text{ }^{\circ}\text{C}$			0.006	
		$V_{GS} = 10\text{ V}$, $I_D = 25\text{ A}$, $T_J = 175\text{ }^{\circ}\text{C}$			0.008	
Forward Transconductance ^b	g_{fs}	$V_{DS} = 15\text{ V}$, $I_D = 25\text{ A}$	30			S
Dynamic						
Input Capacitance	C_{iss}	$V_{GS} = 0\text{ V}$, $V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$		10742		pF
Output Capacitance	C_{oss}			1811		
Reverse Transfer Capacitance	C_{rss}			775		
Total Gate Charge	Q_g	$V_{DS} = 30\text{ V}$, $V_{GS} = 10\text{ V}$, $I_D = 75\text{ A}$		200	250	nC
Gate-Source Charge	Q_{gs}			40		
Gate-Drain Charge	Q_{gd}			40		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = 30\text{ V}$, $R_L = 0.6\text{ }\Omega$ $I_D \cong 50\text{ A}$, $V_{GEN} = 10\text{ V}$, $R_G = 2.5\text{ }\Omega$		20	40	ns
Rise Time	t_r			40		
Turn-Off Delay Time	$t_{d(off)}$			190		
Fall Time	t_f			95		
Source-Drain Diode Ratings and Characteristics						
Diode Forward Voltage ^b	V_{SD}	$I_F = 75\text{ A}$, $V_{GS} = 0\text{ V}$			1.3	V
Reverse Recovery Time	t_{rr}	$I_F = 50\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$		70	120	ns
Peak Reverse Recovery Current	$I_{RM(rec)}$			2.8	6	A
Reverse Recovery Charge	Q_{rr}			0.1	0.36	μC

Notes:

- a. For design aid only; not subject to production testing.
b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

Output Characteristics

Transfer Characteristics

Transconductance

On-Resistance vs. Drain Current

Capacitance

Gate Charge

TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted**THERMAL RATINGS**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?70745>.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.