


TO-263 (D²PAK): 3- AND 5-LEAD



NOTES:

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 .
2. Camber not to exceed 1 mm in 100 mm.
3. Material: Static dissipative black Advantek polystyrene.
4. A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket.
5. K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
6. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
7. Centerline of the component cavity is to be located midway between a pair of sprocket holes.
8. All sizes in mm unless specified.

$A_0 = 10.6\ mm \pm 0.1$
 $B_0 = 16.5\ mm \pm 0.1$
 $K_0 = 4.9\ mm \pm 0.1$
 $K_1 = 3.4\ mm \pm 0.1$
 $E = 1.75\ mm \pm 0.1$
 $F = 11.5\ mm \pm 0.1$
 $W = 24.0\ mm \pm 0.3$

QUANTITY PER REEL
800
ECN: T-01227—Rev. E, 22-Oct-01 DWG: 90-2342-x