


N- and P-Channel 30 V (D-S) MOSFET



FEATURES


- TrenchFET® power MOSFET
- Ultra low $R_{DS(on)}$ n- and p-channel for high efficiency
- Optimized for high side / low side
- Minimized conduction losses
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



APPLICATIONS

- Portable devices including PDAs, cellular phones, and pagers

PRODUCT SUMMARY		
	N-CHANNEL	P-CHANNEL
V_{DS} (V)	30	-30
$R_{DS(on)}$ (Ω) at $V_{GS} = \pm 4.5$ V	0.077	0.170
$R_{DS(on)}$ (Ω) at $V_{GS} = \pm 2.5$ V	0.120	0.300
Q_g typ. (nC)	3	3.8
I_D (A)	3	-2
Configuration	N- and p-pair	



ORDERING INFORMATION	
Package	TSOP-6
Lead (Pb)-free	Si3590DV-T1-E3
Lead (Pb)-free and halogen-free	Si3590DV-T1-GE3

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)							
PARAMETER	SYMBOL	N-CHANNEL		P-CHANNEL		UNIT	
		10 s	STEADY STATE	10 s	STEADY STATE		
Drain-source voltage	V_{DS}	30		-30		V	
Gate-source voltage	V_{GS}	± 12		± 12			
Continuous drain current ($T_J = 150$ °C) ^a	I_D	$T_A = 25$ °C	3	2.5	-2	-1.7	A
		$T_A = 70$ °C	2.3	2	-1.6	-1.3	
Pulsed drain current	I_{DM}	8		-8		A	
Continuous source current (diode conduction) ^a	I_S	1.05	0.75	-1.05	-0.75		
maximum power dissipation ^a	P_D	$T_A = 25$ °C	1.15	0.83	1.15	0.83	W
		$T_A = 70$ °C	0.70	0.53	0.70	0.53	
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +150				°C	

THERMAL RESISTANCE RATINGS							
PARAMETER	SYMBOL	N-CHANNEL		P-CHANNEL		UNIT	
		TYP.	MAX.	TYP.	MAX.		
Maximum junction-to-ambient ^a	R_{thJA}	$t \leq 10$ s	93	110	93	110	°C/W
		Steady state	130	150	130	150	
Maximum junction-to-foot (drain)	R_{thJF}	75	90	75	90		

Note

a. Surface mounted on 1" x 1" FR4 board



SPECIFICATIONS (T _J = 25°C, unless otherwise noted)								
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT	
Static								
Gate threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	0.6	-	1.5	V	
		V _{DS} = V _{GS} , I _D = -250 μA	P-Ch	-0.6	-	-1.5		
Gate-body leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 12 V	N-Ch	-	-	± 100	nA	
			P-Ch	-	-	± 100		
Zero gate voltage drain current	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V	N-Ch	-	-	1	μA	
			P-Ch	-	-	-1		
			N-Ch	-	-	5		
			P-Ch	-	-	-5		
On-state drain current ^a	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 4.5 V	N-Ch	5	-	-	A	
		V _{DS} ≤ -5 V, V _{GS} = -4.5 V	P-Ch	-5	-	-		
Drain-source on-state resistance ^a	R _{DS(on)}	V _{GS} = 4.5 V, I _D = 3 A	N-Ch	-	0.062	0.077	Ω	
			P-Ch	-	0.135	0.170		
			N-Ch	-	0.095	0.120		
			P-Ch	-	0.235	0.300		
Forward transconductance ^a	g _{fs}	V _{DS} = 5 V, I _D = 3 A	N-Ch	-	10	-	S	
		V _{DS} = -5 V, I _D = -2 A	P-Ch	-	5	-		
Diode forward voltage ^a	V _{SD}	I _S = 1.05 A, V _{GS} = 0 V	N-Ch	-	0.8	1.1	V	
		I _S = -1.05 A, V _{GS} = 0 V	P-Ch	-	-0.83	-1.1		
Dynamic ^b								
Total gate charge	Q _g	N-Channel V _{DS} = 15 V, V _{GS} = 4.5 V, I _D = 2 A P-Channel V _{DS} = -15 V, V _{GS} = -4.5 V, I _D = -2 A	N-Ch	-	3	4.5	nC	
			P-Ch	-	3.8	6		
Gate-source charge	Q _{gs}		N-Ch	-	0.6	-		
			P-Ch	-	0.6	-		
Gate-drain charge	Q _{gd}		N-Ch	-	1	-		
			P-Ch	-	1.5	-		
Turn-on delay time	t _{d(on)}	N-Channel V _{DD} = 15 V, R _L = 15 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _g = 6 Ω P-Channel V _{DD} = -15 V, R _L = 15 Ω I _D ≅ -1 A, V _{GEN} = -10 V, R _g = 6 Ω	N-Ch	-	5	8	ns	
			P-Ch	-	5	8		
Rise time	t _r		N-Ch	-	12	23		
			P-Ch	-	15	23		
Turn-off delay time	t _{d(off)}		N-Ch	-	13	23		
			P-Ch	-	20	30		
Fall time	t _f		N-Ch	-	7	12		
			P-Ch	-	20	30		
Source-drain reverse recovery time	t _{rr}		I _F = 1.05 A, di/dt = 100 A/μs	N-Ch	-	15		25
			I _F = -1.05 A, di/dt = 100 A/μs	P-Ch	-	18		30


Notes

- a. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2 %
b. Guaranteed by design, not subject to production testing


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum ratings conditions for extended periods may affect device reliability.




N-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature




N-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage



Single Pulse Power, Junction-to-Ambient




* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified


Safe Operating Area, Junction-to-Case



N-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)




Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Foot




P-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature




P-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power, Junction-to-Ambient




(1) VGS > minimum VGS at which RDS(on) is specified

Safe Operating Area, Junction-to-Case

P-CHANNEL TYPICAL CHARACTERISTICS (25 °C unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Foot


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?72032.

TSOP: 5/6-LEAD



JEDEC Part Number: MO-193C



5-LEAD TSOP





6-LEAD TSOP



Dim	MILLIMETERS			INCHES		
	Min	Nom	Max	Min	Nom	Max
A	0.91	-	1.10	0.036	-	0.043
A₁	0.01	-	0.10	0.0004	-	0.004
A₂	0.90	-	1.00	0.035	0.038	0.039
b	0.30	0.32	0.45	0.012	0.013	0.018
c	0.10	0.15	0.20	0.004	0.006	0.008
D	2.95	3.05	3.10	0.116	0.120	0.122
E	2.70	2.85	2.98	0.106	0.112	0.117
E₁	1.55	1.65	1.70	0.061	0.065	0.067
e	0.95 BSC			0.0374 BSC		
e₁	1.80	1.90	2.00	0.071	0.075	0.079
L	0.32	-	0.50	0.012	-	0.020
L₁	0.60 Ref			0.024 Ref		
L₂	0.25 BSC			0.010 BSC		
R	0.10	-	-	0.004	-	-
θ	0°	4°	8°	0°	4°	8°
θ₁	7° Nom			7° Nom		
ECN: C-06593-Rev. I, 18-Dec-06						
DWG: 5540						



Recommended Land Pattern For TSOP-5L / TSOP-6L



Note

- All dimensions are in inches (millimeter)

ECN: C22-0860-Rev. B, 24-Oct-2022
 DWG: 3010



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.