



N-CHANNEL ACCELERATED OPERATING LIFE TEST RESULT	
Sample Size	41 117
Equivalent Device Hours	7 370 953 354
Failure Rate in FIT	2.401

Failure Rate in FIT is calculated according to JEDEC Standard JESD85, *Methods for Calculating Failure Rates in Units of FITs*, based on accelerated high temperature operating life test results by using an apparent activation energy of 0.7 eV. The junction temperature of the device at use is assumed to be 55 °C. A constant failure rate distribution is assumed. The upper confidence bound of the failure rate is 60 %.