


## P-Channel 30-V (D-S) MOSFET

PRODUCT SUMMARY				
V <sub>DS</sub> (V)	R <sub>DS(on)</sub> (Ω)	V <sub>GS(th)</sub> (V)	I <sub>D</sub> (mA)	Q <sub>g</sub> (Typ.)
- 30	1.4 at V <sub>GS</sub> = - 10 V	- 1.3 to - 3.0	- 385	1000
	3.5 at V <sub>GS</sub> = - 4.5 V	- 1.3 to - 3.0	- 240	



Marking Code: 2Kw//  
 2K = Part Number Code for TP0202K  
 w = Week Code  
 // = Lot Traceability

Ordering Information: TP0202K-T1-E3 (Lead (Pb)-free)  
 TP0202K-T1-GE3 (Lead (Pb)-free and Halogen-free)

### FEATURES

- Halogen-free According to IEC 61249-2-21 Available
- TrenchFET® Power MOSFET
- High-Side Switching
- Low On-Resistance: 1.2 Ω (typ.)
- Low Threshold: - 2 V (typ.)
- Fast Switching Speed: 14 ns (typ.)
- Low Input Capacitance: 31 pF (typ.)
- 2000 V ESD Protection



### APPLICATIONS

- Drivers: Relays, Solenoids, Lamps, Hammers, Display, Memories, Transistors, etc.
- Battery Operated Systems
- Power Supply Converter Circuits
- Solid-State Relays

### BENEFITS

- Ease in Driving Switches
- Low Offset (Error) Voltage
- Low-Voltage Operation
- High-Speed Circuits
- Easily Driven without Buffer

ABSOLUTE MAXIMUM RATINGS T <sub>A</sub> = 25 °C, unless otherwise noted			
Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DS</sub>	- 30	V
Gate-Source Voltage	V <sub>GS</sub>	± 20	
Continuous Drain Current (T <sub>J</sub> = 150 °C) <sup>a</sup>	I <sub>D</sub>	T <sub>A</sub> = 25 °C	- 385
		T <sub>A</sub> = 85 °C	- 280
Pulsed Drain Current <sup>b</sup>	I <sub>DM</sub>	- 750	mA
Power Dissipation <sup>a</sup>	P <sub>D</sub>	T <sub>A</sub> = 25 °C	350
		T <sub>A</sub> = 85 °C	185
Maximum Junction-to-Ambient <sup>a</sup>	R <sub>thJA</sub>	350	°C/W
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	- 55 to 150	°C

Notes:

- a. Surface Mounted on FR4 board.  
 b. Pulse width limited by maximum junction temperature.

<b>SPECIFICATIONS</b> $T_A = 25\text{ }^\circ\text{C}$ , unless otherwise noted						
Parameter	Symbol	Test Conditions	Limits			Unit
			Min.	Typ.	Max.	
<b>Static</b>						
Drain-Source Breakdown Voltage	$V_{DS}$	$V_{GS} = 0\text{ V}, I_D = -100\text{ }\mu\text{A}$	- 30	- 38		V
Gate-Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\text{ }\mu\text{A}$	- 1.3	- 2	- 3.0	
Gate-Body Leakage	$I_{GSS}$	$V_{DS} = 0\text{ V}, V_{GS} = \pm 5\text{ V}$			$\pm 50$	nA
		$V_{DS} = 0\text{ V}, V_{GS} = \pm 10\text{ V}$			$\pm 300$	
Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS} = -30\text{ V}, V_{GS} = 0\text{ V}$			- 100	
		$V_{DS} = -30\text{ V}, V_{GS} = 0\text{ V}, T_J = 85\text{ }^\circ\text{C}$			- 10	
On-State Drain Current <sup>a</sup>	$I_{D(on)}$	$V_{GS} = -10\text{ V}, V_{DS} = -10\text{ V}$	- 500			mA
Drain-Source On-Resistance <sup>a</sup>	$R_{DS(on)}$	$V_{GS} = -4.5\text{ V}, I_D = -50\text{ mA}$		2.1	3.5	$\Omega$
		$V_{GS} = -10\text{ V}, I_D = -500\text{ mA}$		1.25	1.4	
Forward Transconductance <sup>a</sup>	$g_{fs}$	$V_{DS} = -5\text{ V}, I_D = -200\text{ mA}$		315		mS
Diode Forward Voltage <sup>a</sup>	$V_{SD}$	$I_S = -250\text{ mA}, V_{GS} = 0\text{ V}$			- 1.2	V
<b>Dynamic</b>						
Total Gate Charge	$Q_g$	$V_{DS} = -16\text{ V}, V_{GS} = -10\text{ V}$ $I_D \cong -200\text{ mA}$		1000		pC
Gate-Source Charge	$Q_{gs}$			225		
Gate-Drain Charge	$Q_{gd}$			175		
Input Capacitance	$C_{iss}$	$V_{DS} = -15\text{ V}, V_{GS} = 0\text{ V}$ $f = 1\text{ MHz}$		31		pF
Output Capacitance	$C_{oss}$			11		
Reverse Transfer Capacitance	$C_{rss}$			4		
<b>Switching<sup>b</sup></b>						
Turn-On Time	$t_{d(on)}$	$V_{DD} = -15\text{ V}, R_L = 75\text{ }\Omega$ $I_D \cong -200\text{ mA}, V_{GEN} = -10\text{ V}, R_G = 6\text{ }\Omega$		9		ns
	$t_r$			6		
Turn-Off Time	$t_{d(off)}$			30		
	$t_f$			20		


Notes:

a. Pulse test:  $PW \leq 300\text{ }\mu\text{s}$  duty cycle  $\leq 2\%$ .


b. Switching time is essentially independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted




**Output Characteristics**




**Transfer Characteristics**




**On-Resistance vs. Gate-Source Voltage**



**On-Resistance vs. Drain Current**




**Capacitance**




**Gate Charge**




**TYPICAL CHARACTERISTICS** 25 °C, unless otherwise noted




**On-Resistance vs. Junction Temperature**




**Source-Drain Diode Forward Voltage**



**Threshold Voltage Variance Over Temperature**



**$I_{GSS}$  vs. Temperature**



**Normalized Thermal Transient Impedance, Junction-to-Ambient**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?71609](http://www.vishay.com/ppg?71609).



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.