





PowerPAK® 5 x 9 Triple Case Outline



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	1.15	1.20	1.25	0.045	0.047	0.049
A1	0.00	-	0.05	0.000	-	0.002
A2	0.25 ref.			0.010 ref.		
A3	0.08	-	-	0.003	-	-
b	0.35	0.40	0.45	0.014	0.016	0.018
b1	0.05	0.20	0.25	0.002	0.008	0.010
D	8.90	9.00	9.10	0.350	0.354	0.358
D1	3.85	3.90	3.95	0.152	0.154	0.156
E	4.90	5.00	5.10	0.193	0.197	0.201
E1	1.85	1.90	1.95	0.073	0.075	0.077
E2	2.25	2.30	2.35	0.089	0.091	0.093
e	1.27 BSC			0.050 BSC		
e1	3.81 BSC			0.150 BSC		
K	1.40 ref.			0.055 ref.		
K1	0.76	0.81	0.86	0.030	0.032	0.034
K2	0.60 ref.			0.024 ref.		
L	0.50	0.60	0.70	0.020	0.024	0.028
L1	0.20 ref.			0.008 ref.		
ECN: C18-1128-Rev. A, 27-Aug-2018						
DWG: 6070						

Notes

- (1) Use millimeters as the primary measurement
- (2) Dimensioning and tolerances conform to ASME Y14.5M. - 1994
- (3) N is the number of terminals
- (4) Package warpage max. 0.08 mm
- (5) The pin #1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body
- (6) Exact shape and size of this feature is optional